

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
0.5	30.07	1.04
1.0	30.05	1.04
2.0	30.05	1.04
4.0	30.05	1.04
6.0	30.05	1.04
8.0	30.04	1.04
10.0	30.04	1.04
30.0	30.05	1.04
50.0	30.06	1.04
70.0	30.07	1.04
90.0	30.07	1.04
100.0	30.08	1.04
150.0	30.10	1.04
200.0	30.13	1.04
250.0	30.17	1.05
300.0	30.21	1.06
350.0	30.27	1.07
400.0	30.33	1.08
450.0	30.40	1.08
500.0	30.48	1.09
550.0	30.57	1.10
600.0	30.68	1.11
650.0	30.78	1.11
700.0	30.90	1.12
750.0	31.04	1.13
800.0	31.17	1.14
850.0	31.32	1.14
900.0	31.49	1.15
1000.0	31.87	1.17
1100.0	32.29	1.18
1200.0	32.78	1.20
1300.0	33.32	1.21
1400.0	33.94	1.23
1500.0	34.63	1.24
1600.0	35.32	1.26
1700.0	36.01	1.27
1800.0	36.61	1.29
1900.0	36.94	1.30
2000.0	36.81	1.32