

Ceramic Low Pass Filter

LFCN-225D+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	0.06	0.09	0.01	41.24	40.09	39.13	41.11	40.09	39.30
20	0.15	0.18	0.22	28.90	27.66	26.81	28.33	27.30	26.53
50	0.22	0.26	0.30	30.44	28.34	27.05	28.81	27.42	26.39
100	0.32	0.36	0.41	28.73	28.57	28.33	25.50	25.44	25.23
150	0.42	0.47	0.53	27.15	30.83	33.81	23.41	24.45	24.90
200	0.53	0.60	0.69	27.90	33.23	39.22	23.65	24.65	25.10
225	0.60	0.69	0.79	28.96	32.44	37.27	24.41	24.99	25.44
240	0.65	0.76	0.86	29.20	30.89	33.67	24.89	25.11	25.49
275	0.81	0.94	1.08	26.43	25.23	24.71	24.45	23.60	23.12
350	1.79	2.11	2.45	12.81	12.10	11.34	14.64	14.32	13.86
370	2.56	3.00	3.47	9.60	9.15	8.64	12.82	13.03	13.20
390	4.10	4.78	5.50	6.51	6.21	5.90	11.45	12.06	12.83
412	8.15	9.34	10.58	3.39	3.31	3.22	7.92	8.18	8.35
425	12.60	14.11	15.64	2.19	2.24	2.28	5.57	5.75	5.84
435	17.16	18.86	20.57	1.65	1.77	1.86	4.29	4.48	4.60
450	25.92	27.79	29.56	1.24	1.39	1.51	3.13	3.33	3.48
460	33.09	34.45	35.34	1.09	1.24	1.37	2.67	2.87	3.04
495	37.94	38.38	38.90	0.84	0.97	1.09	1.87	2.06	2.24
510	40.79	41.66	42.51	0.77	0.90	1.02	1.69	1.88	2.06
530	48.08	48.01	47.31	0.70	0.82	0.93	1.52	1.70	1.88
610	38.06	38.03	38.00	0.52	0.63	0.72	1.12	1.27	1.42
700	40.74	41.10	41.49	0.40	0.49	0.58	0.82	0.94	1.06
760	46.55	47.24	47.99	0.36	0.44	0.53	0.68	0.78	0.88
820	59.65	61.06	61.66	0.31	0.39	0.48	0.56	0.65	0.73
900	51.61	51.04	50.55	0.27	0.35	0.43	0.44	0.52	0.59
1050	46.67	46.59	46.67	0.21	0.29	0.37	0.30	0.37	0.42
1400	54.88	55.18	55.61	0.16	0.24	0.33	0.18	0.23	0.27
1600	72.03	72.02	71.96	0.13	0.21	0.30	0.16	0.21	0.24
2500	51.94	51.22	50.98	0.16	0.24	0.30	0.13	0.18	0.22
2660	49.62	49.18	49.07	0.16	0.24	0.30	0.11	0.17	0.21
3220	39.50	39.48	39.26	0.20	0.29	0.37	0.11	0.18	0.25
4430	30.45	30.77	30.26	0.88	1.50	2.48	0.10	0.25	0.41
5500	23.99	24.20	24.16	0.45	0.62	0.85	0.24	0.40	0.57
6500	20.03	19.84	19.86	0.93	1.10	1.36	0.43	0.52	0.68
7200	18.22	18.62	19.02	1.85	2.30	2.89	0.49	0.54	0.65
7600	25.52	25.79	24.58	15.51	11.91	8.52	0.41	0.51	0.58
8920	13.72	13.56	14.04	1.84	2.64	3.27	2.00	2.22	2.59
11000	11.26	12.11	12.72	3.43	4.10	5.30	1.37	1.57	2.00
12840	10.15	9.41	9.39	1.58	2.29	2.98	2.10	2.73	3.15
13200	7.53	6.82	6.83	2.68	4.07	5.48	3.38	4.42	5.14
14000	4.39	4.64	5.27	16.80	17.93	16.75	6.61	7.43	7.66

REV. X1
LFCN-225D+
071008
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

