

Ceramic Low Pass Filter

LFCN-2750

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.06	0.07	0.08	45.62	38.29	34.40	45.41	38.69	34.72
200	0.10	0.12	0.14	33.41	38.62	39.05	32.89	37.70	39.05
500	0.13	0.17	0.21	39.80	45.02	35.36	35.92	34.97	32.27
1000	0.20	0.26	0.33	27.02	26.99	26.82	24.98	24.93	24.42
1500	0.32	0.41	0.49	19.34	19.06	19.05	19.29	18.88	18.72
2000	0.44	0.55	0.65	16.41	16.61	16.88	16.64	16.66	16.79
2500	0.53	0.65	0.79	19.29	20.50	21.23	18.50	19.69	20.49
2700	0.60	0.75	0.90	23.55	23.81	23.27	20.84	21.46	21.60
2750	0.64	0.79	0.96	23.53	23.27	22.39	20.75	21.10	21.00
2900	0.80	0.99	1.20	18.66	18.29	17.50	17.68	17.57	17.18
3150	1.56	1.88	2.26	10.07	9.54	9.07	10.40	9.99	9.59
3260	2.49	2.96	3.49	6.64	6.30	5.98	7.16	6.86	6.58
3370	4.32	4.95	5.69	3.98	3.85	3.71	4.41	4.32	4.20
3540	9.16	10.04	11.06	1.67	1.74	1.80	2.03	2.12	2.18
3660	13.82	14.84	16.02	1.09	1.20	1.30	1.35	1.49	1.61
3775	18.85	20.03	21.39	0.77	0.91	1.04	1.01	1.18	1.34
3850	22.50	23.81	25.30	0.70	0.83	0.97	0.87	1.06	1.24
3900	25.11	26.53	28.14	0.70	0.84	0.96	0.89	1.06	1.24
3950	27.90	29.47	31.22	0.60	0.75	0.88	0.82	1.00	1.19
4000	31.02	32.73	34.65	0.62	0.76	0.89	0.79	0.97	1.15
4070	36.03	37.98	40.14	0.59	0.73	0.86	0.78	0.96	1.15
4150	43.18	45.33	46.81	0.57	0.72	0.84	0.74	0.94	1.16
4200	47.47	48.54	49.18	0.49	0.65	0.78	0.71	0.91	1.11
4700	52.19	50.72	49.65	0.45	0.60	0.73	0.68	0.88	1.11
4900	44.00	42.95	42.17	0.41	0.56	0.68	0.62	0.82	1.04
5150	38.49	38.29	38.14	0.38	0.52	0.65	0.62	0.79	0.96
6000	35.49	35.29	35.17	0.46	0.63	0.85	0.52	0.69	0.84
6800	30.02	29.90	29.81	0.59	0.80	1.03	0.48	0.70	0.92
7500	25.07	25.03	25.21	0.73	0.87	1.07	0.51	0.76	1.06
8400	21.19	21.72	22.24	0.85	0.98	1.08	0.75	0.93	1.22
9900	18.50	18.44	18.41	0.53	0.93	1.18	0.84	1.11	1.22
11000	16.77	16.64	16.56	0.95	1.08	1.26	0.73	0.98	1.15
12100	14.81	14.87	15.02	0.80	1.04	1.24	0.74	0.91	1.18
13000	13.37	13.06	12.82	0.65	1.05	1.54	0.80	1.01	1.34
14000	12.17	12.58	12.73	1.38	1.54	1.90	1.00	1.22	1.53
15200	9.46	9.65	10.44	3.06	3.13	3.04	2.60	2.72	3.05
16300	13.20	13.98	14.24	2.41	2.94	3.30	2.52	2.42	2.66
17400	16.50	16.33	16.67	2.86	3.27	4.46	1.88	2.28	2.30
18500	22.61	20.14	18.82	8.73	6.00	4.93	1.52	2.03	2.35
19400	20.45	20.84	20.94	2.94	3.32	3.46	1.17	1.58	2.21
20000	18.51	17.44	16.26	3.38	4.29	5.55	1.44	2.03	3.10

REV. X1
LFCN-2750
080722
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

