

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
0.3	0.24	1.05
0.5	0.25	1.05
0.7	0.25	1.05
1	0.25	1.05
4	0.25	1.05
7	0.25	1.05
10	0.26	1.05
30	0.33	1.10
50	0.41	1.16
70	0.50	1.22
90	0.59	1.26
110	0.67	1.28
130	0.74	1.26
150	0.80	1.21
170	0.87	1.17
200	1.02	1.22
220	1.16	1.32
240	1.31	1.39
260	1.47	1.39
270	1.56	1.36
290	1.76	1.28
300	1.92	1.28
325	2.67	1.64
350	4.61	2.93
360	5.99	4.00
370	7.75	5.59
380	9.83	7.78
390	12.13	10.60
400	14.52	13.92
410	16.93	17.58
420	19.30	21.46
430	21.58	25.38
440	23.75	29.30
450	25.81	33.20
460	27.74	36.95
470	29.55	40.61
480	31.22	44.05
490	32.77	47.43
500	34.17	50.62
550	39.43	64.49
600	42.27	75.67
650	43.69	81.72
700	44.41	86.59
750	44.88	90.72
800	45.21	93.17
850	45.54	94.07
900	45.91	94.89
965	46.51	95.32
1005	46.95	97.99
1085	48.02	98.22
1125	48.69	99.08
1205	50.29	97.61
1285	52.56	97.07
1325	54.03	98.84
1365	55.88	99.01
1405	58.25	98.63
1445	61.62	99.65
1485	66.49	98.47
1525	69.63	96.37
1550	66.39	97.46
1575	62.95	97.93
1600	60.27	95.96
1625	58.21	94.96
1650	56.52	96.45
1675	55.06	99.55
1700	53.79	99.77
1725	52.67	98.76
1750	51.63	98.18
1775	50.66	98.58
1800	49.79	99.93
1850	48.21	95.71
1900	46.92	96.40
1950	45.76	99.96
2000	44.75	96.93