

Ceramic Low Pass Filter

LFCN-3000+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.06	0.08	0.08	44.91	39.24	35.43	47.95	39.64	35.50
100	0.08	0.09	0.10	39.89	39.89	37.06	41.82	39.92	35.56
500	0.14	0.19	0.23	32.16	30.19	26.92	33.09	30.40	26.96
1000	0.22	0.29	0.34	23.54	22.83	23.16	23.35	22.74	22.88
2000	0.40	0.52	0.61	17.17	17.15	17.02	17.41	17.38	17.28
2500	0.48	0.59	0.70	18.17	19.12	19.50	18.35	19.28	19.61
3000	0.59	0.75	0.90	45.90	42.95	34.73	32.00	30.29	29.08
3240	0.82	1.03	1.23	18.62	17.30	16.43	18.55	17.47	16.76
3580	2.40	2.80	3.21	6.49	6.26	6.07	6.74	6.53	6.29
3600	2.61	3.02	3.45	6.04	5.85	5.67	6.27	6.09	5.87
3720	4.22	4.71	5.23	3.79	3.73	3.67	3.99	3.96	3.86
3940	8.70	9.37	10.08	1.59	1.69	1.76	1.84	1.92	1.96
4120	13.43	14.22	15.04	0.92	1.06	1.17	1.19	1.31	1.41
4280	18.10	19.05	20.03	0.67	0.83	0.95	0.97	1.12	1.25
4350	20.32	21.34	22.38	0.61	0.78	0.90	0.91	1.08	1.22
4410	22.39	23.47	24.53	0.56	0.74	0.86	0.88	1.05	1.20
4530	26.71	27.89	29.10	0.51	0.68	0.81	0.81	1.01	1.20
4550	27.46	28.69	29.93	0.50	0.68	0.81	0.81	1.02	1.21
4710	34.65	36.06	37.62	0.45	0.64	0.76	0.82	1.04	1.24
4780	38.39	39.94	41.67	0.45	0.63	0.76	0.83	1.05	1.26
4910	46.47	48.33	49.33	0.43	0.61	0.73	0.82	1.04	1.27
5020	49.48	48.81	48.39	0.43	0.60	0.72	0.82	1.05	1.28
5450	49.91	50.91	52.11	0.43	0.60	0.72	0.84	1.05	1.23
5900	40.80	40.51	40.51	0.47	0.67	0.82	0.76	0.96	1.08
6410	34.48	34.53	34.08	0.50	0.72	0.96	0.70	0.87	1.01
7000	30.49	30.71	30.30	0.58	0.81	1.07	0.64	0.86	1.06
7500	27.71	27.66	27.72	0.68	0.87	1.07	0.61	0.87	1.11
8000	24.15	24.83	24.69	0.77	0.89	1.06	0.72	0.96	1.24
8500	21.72	22.38	23.15	0.86	0.95	1.05	0.87	1.04	1.27
9000	21.94	21.82	21.90	0.65	0.93	1.10	0.82	1.03	1.26
9500	20.33	19.94	19.78	0.66	1.01	1.22	1.04	1.22	1.36
10000	18.27	18.32	18.23	0.66	1.02	1.26	1.03	1.24	1.30
10500	17.51	17.58	17.26	0.84	1.07	1.32	1.00	1.17	1.24
11000	16.87	17.04	16.95	0.86	1.07	1.26	0.89	1.13	1.21
11500	15.68	16.24	16.32	1.06	1.17	1.27	0.91	1.10	1.21
12000	16.02	16.12	16.35	0.92	1.17	1.39	0.81	1.05	1.21
13000	14.31	13.86	13.71	0.64	1.10	1.54	0.86	1.10	1.33
14000	11.86	12.42	12.57	0.95	1.26	1.76	1.14	1.39	1.68
16000	10.01	10.68	11.39	4.31	4.79	5.42	2.77	2.99	3.29
18000	16.99	18.21	19.77	4.26	4.69	4.96	2.46	2.99	3.24
20000	25.06	25.33	25.98	3.66	4.06	3.99	1.28	1.70	2.19

REV. X1
LFCN-3000+
080722
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

