

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	0.08	42.66
50	0.09	41.82
100	0.10	36.87
200	0.11	30.07
300	0.13	26.30
400	0.14	23.82
500	0.15	21.90
600	0.17	20.43
700	0.19	19.11
800	0.20	18.05
900	0.22	17.15
1000	0.24	16.38
1500	0.35	13.67
2000	0.43	12.28
2500	0.47	11.81
3000	0.44	12.28
3500	0.37	13.82
4000	0.29	17.04
4500	0.22	24.04
5000	0.21	32.62
5500	0.24	22.55
6000	0.27	19.73
6500	0.27	20.67
7000	0.26	26.28
7500	0.26	34.17
8000	0.32	19.49
8500	0.45	14.84
9000	0.61	12.37
9500	0.73	11.55
10000	0.77	11.94
10500	0.74	13.55
11000	0.66	17.16
11500	0.62	25.09
12000	0.68	21.19
12500	0.84	15.38
12750	0.94	13.99
13000	1.02	13.21
13500	1.16	13.97
14000	2.09	8.68
14075	2.32	7.88
14500	6.30	2.67
15000	13.41	1.05
15350	18.94	0.69
15500	21.40	0.66
15950	29.30	0.51
16000	30.21	0.52
16500	40.50	0.43
17000	52.36	0.39
17500	61.96	0.35
18000	62.31	0.30
18500	52.62	0.23
19000	46.80	0.18
19500	42.30	0.17
20000	38.71	0.13