

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	0.06	45.38
50	0.08	35.39
100	0.10	36.52
200	0.11	29.96
300	0.13	26.22
400	0.14	23.74
500	0.16	21.77
600	0.17	20.28
700	0.20	18.93
800	0.21	17.83
900	0.24	16.87
1000	0.26	16.06
1500	0.39	13.05
2000	0.52	11.33
2500	0.60	10.45
3000	0.62	10.37
3500	0.56	11.11
4000	0.44	12.96
4500	0.32	16.54
5000	0.25	23.71
5500	0.23	34.73
6000	0.24	25.42
6500	0.26	24.76
7000	0.26	30.09
7500	0.28	26.32
8000	0.36	18.05
8500	0.50	13.95
9000	0.68	11.55
9500	0.83	10.47
10000	0.89	10.49
10500	0.85	11.62
11000	0.72	14.78
11500	0.62	24.92
12000	0.70	19.69
12500	1.02	11.84
13000	1.35	9.39
13500	1.32	11.68
13800	1.37	17.15
14000	1.94	11.20
14150	2.96	6.79
14500	7.20	2.19
15000	14.91	0.69
15350	20.40	0.43
15500	22.77	0.42
15950	30.12	0.35
16000	30.93	0.37
16500	39.48	0.34
17000	46.58	0.31
17500	49.62	0.29
18000	55.57	0.23
18500	47.59	0.18
19000	40.89	0.25
19500	35.24	0.36
20000	30.03	0.49