

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	0.13	49.71
50	0.01	41.07
100	0.09	36.89
200	0.11	29.98
300	0.12	26.15
400	0.13	23.73
500	0.15	21.79
600	0.17	20.33
700	0.19	18.98
800	0.21	17.92
900	0.23	16.99
1000	0.25	16.20
1500	0.37	13.34
2000	0.48	11.82
2500	0.53	11.18
3000	0.52	11.51
3500	0.44	12.90
4000	0.33	16.02
4500	0.25	22.84
5000	0.24	30.04
5500	0.27	20.83
6000	0.32	18.14
6500	0.33	18.94
7000	0.30	24.08
7500	0.29	36.55
8000	0.37	19.13
8500	0.51	14.34
9000	0.68	12.04
9500	0.79	11.41
10000	0.80	12.16
10500	0.74	14.40
11000	0.65	20.02
11500	0.66	40.79
12000	0.78	19.53
12500	0.96	15.98
12650	1.00	16.18
13000	1.11	20.45
13500	1.99	12.05
13675	2.86	8.00
13800	4.19	5.33
14000	6.64	3.23
14150	8.83	2.30
14500	14.52	1.29
14825	19.77	1.01
15000	23.51	0.89
15325	29.66	0.78
15350	30.81	0.77
15500	34.41	0.76
15950	45.09	0.68
16000	45.72	0.71
16500	48.82	0.63
17000	56.68	0.58
17500	55.51	0.56
18000	46.20	0.48
18500	41.81	0.45
19000	38.57	0.36
19500	35.77	0.35
20000	33.17	0.28