

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
1	0.12	37.10
2	0.11	35.71
3	0.08	28.81
4	0.13	35.15
5	0.14	35.41
6	0.11	28.66
7	0.10	24.37
8	0.11	19.98
9	0.15	17.40
10	0.27	15.54
11	0.36	15.07
12	0.43	16.18
13	0.33	17.31
14	0.31	19.61
15	0.38	31.92
16	0.34	25.24
17	0.60	19.33
18	0.71	15.55
19	0.68	14.49
20	0.76	15.74
21	0.81	17.66
22	0.97	20.05
23	1.26	17.45
24	1.97	12.45
25	5.41	3.97
26	12.41	1.13
27	20.29	0.61
28	28.07	0.49
29	35.78	0.29
30	41.53	0.31
31	42.92	0.39
32	42.74	0.31
33	42.38	0.07
34	42.82	0.29
35	44.15	0.24
36	45.34	0.50
37	46.37	0.64
38	45.00	0.44
39	43.14	0.29
40	41.98	0.20
41	41.50	0.60
42	41.28	0.63
43	40.04	0.43
44	39.16	0.44
45	39.43	0.36
46	39.65	0.19
47	39.71	0.46
48	40.36	0.78
49	42.19	0.63
50	44.17	0.36
51	47.42	0.61
52	46.87	1.14
53	35.46	5.81
54	40.02	2.01
55	49.90	1.69
56	34.71	0.86
57	22.99	0.57
58	16.85	1.65
59	22.73	1.27
60	27.91	1.82