

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	RETURN LOSS		
			IN	OUT	CPL
0.01	0.98	20.01	18.75	18.67	19.96
0.04	0.98	20.10	19.63	19.81	19.44
0.07	0.98	20.10	19.68	19.76	20.04
0.10	0.98	20.10	19.73	19.73	20.10
0.40	0.98	20.10	19.74	19.75	20.13
0.70	0.98	20.09	19.95	19.98	20.12
1.0	0.98	20.07	20.03	20.01	20.12
4.0	0.98	20.07	20.08	20.10	20.13
7.0	0.97	20.06	20.06	20.14	20.13
10	0.97	20.06	20.12	20.18	20.13
40	0.97	20.05	20.28	20.28	20.21
70	0.97	20.05	20.33	20.39	20.30
100	0.97	20.04	20.37	20.35	20.32
200	0.97	20.05	20.54	20.61	20.45
400	0.97	20.08	20.60	20.63	20.42
600	0.98	20.14	20.42	20.47	20.22
800	0.97	20.23	20.07	20.20	20.02
1000	0.98	20.37	19.71	19.82	19.88
1500	0.98	20.81	18.50	18.81	19.95
2000	0.96	21.37	17.70	18.03	20.95
2500	0.97	21.82	18.18	18.65	23.40
3000	0.93	22.10	19.18	19.95	24.92
3500	0.95	21.89	20.01	21.32	23.48
4000	1.01	21.46	19.91	21.70	21.10
4500	1.07	20.92	19.40	21.61	19.50
5000	1.14	20.40	19.13	21.52	18.35
5500	1.22	20.12	19.29	21.59	17.00
5600	1.24	20.04	19.27	21.48	16.65
5700	1.25	19.96	19.12	21.33	16.45
5800	1.28	19.85	19.23	20.96	16.07
5900	1.30	19.72	19.14	20.65	15.75
6000	1.34	19.57	19.08	20.22	15.47
6100	1.39	19.38	19.02	19.76	15.20
6200	1.47	19.09	18.59	19.33	14.89
6300	1.51	18.89	18.27	19.18	14.77
6400	1.55	18.84	17.95	18.83	14.59
6500	1.62	18.72	17.53	18.44	14.40