

Metal Shield Low Pass Filter

LPF-EDU1665

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	0.04	44.81	1	4.35
50	0.17	41.40	10	4.29
150	0.47	32.12	20	4.30
190	0.86	37.24	30	4.31
202	1.39	25.26	40	4.34
210	4.09	6.31	50	4.40
215	9.56	2.41	60	4.47
220	16.66	1.31	70	4.56
225	24.09	0.95	80	4.68
230	31.79	0.79	90	4.81
235	40.23	0.69	100	4.98
240	50.73	0.63	110	5.21
250	63.50	0.54	120	5.50
400	64.09	0.21	130	5.86
500	67.48	0.16	140	6.30
650	77.71	0.14	150	6.84
800	76.97	0.16	155	7.18
1000	72.23	0.18	160	7.52
1300	70.41	0.26	165	8.00
1500	69.47	0.27	170	8.43
1800	64.79	0.30	175	8.85
2000	71.75	0.30	180	9.25
2300	59.17	0.30	185	11.09
2500	53.47	0.30	190	12.44



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



REV. X1
LPF-EDU1665
URJ
120808
Page 1 of 1