

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
1000	0.20	1.32	1.34
1200	0.25	1.36	1.39
1400	0.28	1.39	1.41
1600	0.31	1.39	1.41
1800	0.32	1.37	1.38
2000	0.32	1.32	1.33
2200	0.32	1.24	1.26
2400	0.31	1.13	1.17
2410	0.31	1.13	1.17
2420	0.31	1.12	1.16
2430	0.32	1.12	1.16
2440	0.31	1.11	1.16
2450	0.32	1.11	1.15
2460	0.32	1.10	1.15
2470	0.32	1.10	1.15
2480	0.32	1.09	1.14
2490	0.32	1.09	1.14
2500	0.32	1.08	1.14
2600	0.33	1.05	1.11
2800	0.38	1.12	1.16
3000	0.47	1.24	1.26
3200	0.57	1.32	1.34
3400	0.66	1.27	1.28
3600	0.85	1.08	1.09
3800	1.96	2.06	2.09
4000	5.74	5.94	6.07
4200	11.97	16.59	17.28
4400	19.34	33.97	35.71
4600	28.44	51.71	58.02
4800	45.95	66.16	76.25
4820	49.21	66.61	75.48
4840	50.98	67.70	75.00
4860	49.40	69.28	75.33
4880	46.77	69.71	74.52
4900	44.62	70.01	75.62
4920	42.83	71.21	77.97
4940	41.36	71.83	79.77
4960	40.28	72.02	81.14
4980	39.34	73.26	80.57
5000	38.59	72.76	79.94
7000	44.61	49.94	53.84
7050	43.83	52.23	53.89
7100	43.05	54.48	56.85
7150	42.45	57.73	60.26
7200	41.95	60.18	62.46
7250	41.38	64.54	63.81
7300	41.04	69.18	66.60
7350	40.64	74.78	72.87
7400	40.30	80.31	74.77
7450	40.06	88.36	83.02
7500	39.75	96.20	87.34
7600	39.41	122.29	117.55
7800	38.84	237.99	232.07
8000	38.47	2843.64	2581.25
8200	38.26	293.33	267.23
8400	38.12	154.67	150.68
8600	38.03	107.43	105.86
8800	37.94	88.60	82.62
9000	37.85	77.75	75.28
9200	37.74	72.68	70.30
9400	37.57	72.91	66.98
9600	37.39	76.84	67.45
9650	37.36	79.50	69.95
9700	37.28	80.62	71.96
9750	37.25	83.99	70.47
9800	37.18	88.46	71.99
9850	37.15	92.02	76.15
9900	37.09	97.64	78.04
9950	36.99	104.44	81.20
10000	36.91	110.04	79.41

