

Frequency Mixer

LRMS-2LJ

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)		
		@LO (dBm)		
		0	+3	+6
200.1	230.1	11.55	10.37	9.86
240.1	270.1	10.23	9.20	8.74
280.1	310.1	9.39	8.42	7.96
320.1	350.1	8.56	7.74	7.27
360.1	390.1	8.07	7.23	6.79
400.1	430.1	7.64	6.83	6.39
440.1	470.1	7.19	6.41	6.00
480.1	510.1	7.07	6.27	5.84
520.1	550.1	6.83	6.04	5.65
560.1	590.1	6.76	5.96	5.54
600.1	630.1	6.68	5.84	5.39
640.1	670.1	6.62	5.75	5.26
680.1	710.1	6.60	5.71	5.21
720.1	750.1	6.46	5.60	5.13
760.1	790.1	6.61	5.71	5.22
800.1	830.1	6.69	5.76	5.25
840.1	870.1	7.04	6.04	5.42
880.1	910.1	7.32	6.31	5.65
920.1	950.1	7.59	6.61	5.91
960.1	990.1	7.79	6.88	6.20
1000.1	1030.1	7.82	7.04	6.44
1040.1	1070.1	7.86	7.20	6.68
1080.1	1110.1	7.82	7.21	6.78
1120.1	1150.1	7.83	7.24	6.84
1160.1	1190.1	8.03	7.37	6.98
1200.1	1230.1	8.13	7.44	7.08
1240.1	1270.1	8.21	7.50	7.13
1300.1	1330.1	8.26	7.47	7.11
1340.1	1370.1	8.44	7.52	7.14
1400.1	1430.1	8.41	7.49	7.13
1440.1	1470.1	8.72	7.64	7.19
1500.1	1530.1	8.75	7.66	7.22
1540.1	1570.1	9.07	7.82	7.33
1600.1	1630.1	9.45	8.07	7.59
1640.1	1670.1	9.74	8.27	7.83
1700.1	1730.1	10.81	8.85	8.18
1740.1	1770.1	10.90	8.93	8.23
1800.1	1830.1	12.08	9.47	8.34
1840.1	1870.1	12.21	9.55	8.34
1900.1	1930.1	12.63	9.74	8.31

RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)		
		@LO (dBm)		
		0	+3	+6
200.1	230.1	12.74	16.55	18.07
240.1	270.1	13.97	14.87	18.63
280.1	310.1	12.12	14.02	17.85
320.1	350.1	12.05	14.77	14.93
360.1	390.1	11.12	15.30	13.19
400.1	430.1	9.88	14.40	12.53
440.1	470.1	9.83	14.62	12.36
480.1	510.1	9.49	13.59	11.95
520.1	550.1	11.07	11.52	10.29
560.1	590.1	11.20	10.52	8.86
600.1	630.1	11.76	9.53	7.99
640.1	670.1	10.76	10.40	8.17
680.1	710.1	10.21	11.93	9.05
720.1	750.1	11.27	13.86	9.35
760.1	790.1	10.36	17.92	11.52
800.1	830.1	13.12	14.64	11.66
840.1	870.1	12.34	18.03	13.06
880.1	910.1	8.48	11.35	12.59
920.1	950.1	6.82	8.94	10.71
960.1	990.1	6.00	7.72	9.78
1000.1	1030.1	5.69	7.16	9.16
1040.1	1070.1	5.79	6.75	8.67
1080.1	1110.1	5.68	6.26	7.67
1120.1	1150.1	6.26	6.32	7.27
1160.1	1190.1	6.68	6.27	6.87
1200.1	1230.1	7.24	6.56	6.70
1240.1	1270.1	7.98	7.16	6.84
1300.1	1330.1	7.69	7.53	7.13
1340.1	1370.1	7.25	7.60	7.31
1400.1	1430.1	7.24	7.60	7.46
1440.1	1470.1	6.74	7.31	7.30
1500.1	1530.1	6.34	7.03	6.74
1540.1	1570.1	6.17	6.86	6.48
1600.1	1630.1	5.99	6.47	5.79
1640.1	1670.1	5.75	6.25	5.67
1700.1	1730.1	5.95	6.15	6.54
1740.1	1770.1	5.76	6.47	7.47
1800.1	1830.1	4.90	5.69	7.80
1840.1	1870.1	4.57	5.21	7.15
1900.1	1930.1	4.64	5.08	6.43

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=-3dBm (dB)		
		@LO (dBm)		
		0	+3	+6
200.1	230.1	-0.08	-0.07	-0.05
240.1	270.1	-0.02	-0.04	-0.04
280.1	310.1	0.02	-0.03	-0.03
320.1	350.1	0.14	0.02	0.01
360.1	390.1	0.30	0.12	0.08
400.1	430.1	0.39	0.20	0.16
440.1	470.1	0.54	0.31	0.26
480.1	510.1	0.73	0.44	0.38
520.1	550.1	0.84	0.53	0.45
560.1	590.1	1.06	0.69	0.56
600.1	630.1	1.16	0.80	0.65
640.1	670.1	1.36	0.97	0.79
680.1	710.1	1.37	1.00	0.82
720.1	750.1	1.48	1.10	0.89
760.1	790.1	1.49	1.13	0.92
800.1	830.1	1.49	1.19	0.99
840.1	870.1	1.47	1.22	1.06
880.1	910.1	1.36	1.18	1.06
920.1	950.1	1.22	1.09	1.03
960.1	990.1	1.01	0.89	0.87
1000.1	1030.1	0.87	0.73	0.71
1040.1	1070.1	0.75	0.55	0.52
1080.1	1110.1	0.81	0.54	0.47
1120.1	1150.1	0.85	0.55	0.47
1160.1	1190.1	0.90	0.53	0.44
1200.1	1230.1	0.91	0.52	0.41
1240.1	1270.1	0.85	0.51	0.40
1300.1	1330.1	0.97	0.59	0.47
1340.1	1370.1	1.13	0.73	0.58
1400.1	1430.1	1.03	0.73	0.64
1440.1	1470.1	1.12	0.83	0.71
1500.1	1530.1	1.11	0.87	0.79
1540.1	1570.1	1.10	0.91	0.82
1600.1	1630.1	1.08	0.92	0.81
1640.1	1670.1	1.01	0.86	0.67
1700.1	1730.1	0.83	0.86	0.65
1740.1	1770.1	0.74	0.82	0.63
1800.1	1830.1	0.42	0.84	0.71
1840.1	1870.1	0.37	0.82	0.73
1900.1	1930.1	0.19	0.79	0.74

REV. X2

LRMS-2LJ

100817

Page 1 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Frequency Mixer

LRMS-2LJ

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=900.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=800.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1000.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+3			+3			+3
100.0	800.1	6.38	10.0	810.1	6.11	200.0	800.1	6.89
95.3	804.8	6.45	14.9	815.0	5.98	195.1	805.0	6.97
90.5	809.6	6.50	19.7	819.8	5.86	190.3	809.8	7.00
85.8	814.3	6.51	24.6	824.7	5.79	185.4	814.7	6.98
81.1	819.0	6.47	29.5	829.6	5.75	180.5	819.6	6.93
76.3	823.8	6.40	34.4	834.5	5.73	175.6	824.5	6.89
71.6	828.5	6.32	39.2	839.3	5.75	170.8	829.3	6.87
66.8	833.3	6.28	44.1	844.2	5.78	165.9	834.2	6.88
62.1	838.0	6.30	49.0	849.1	5.80	161.0	839.1	6.92
57.4	842.7	6.35	53.8	853.9	5.83	156.2	843.9	6.99
52.6	847.5	6.43	58.7	858.8	5.86	151.3	848.8	7.05
47.9	852.2	6.50	63.6	863.7	5.85	146.4	853.7	7.11
43.2	856.9	6.52	68.5	868.6	5.81	141.5	858.6	7.15
38.4	861.7	6.50	73.3	873.4	5.77	136.7	863.4	7.14
33.7	866.4	6.44	78.2	878.3	5.70	131.8	868.3	7.11
28.9	871.2	6.38	83.1	883.2	5.69	126.9	873.2	7.05
24.2	875.9	6.33	87.9	888.0	5.72	122.1	878.0	6.98
19.5	880.6	6.35	92.8	892.9	5.77	117.2	882.9	6.96
14.7	885.4	6.41	97.7	897.8	5.83	112.3	887.8	7.00
10.0	890.1	6.51	102.6	902.7	5.86	107.4	892.7	7.07
10.0	910.1	6.59	107.4	907.5	5.84	102.6	897.5	7.13
14.7	914.8	6.41	112.3	912.4	5.76	97.7	902.4	7.17
19.5	919.6	6.31	117.2	917.3	5.69	92.8	907.3	7.13
24.2	924.3	6.24	122.1	922.2	5.62	87.9	912.2	7.04
28.9	929.0	6.21	126.9	927.0	5.61	83.1	917.0	6.94
33.7	933.8	6.24	131.8	931.9	5.67	78.2	921.9	6.87
38.4	938.5	6.31	136.7	936.8	5.76	73.3	926.8	6.85
43.2	943.3	6.38	141.5	941.6	5.84	68.5	931.6	6.89
47.9	948.0	6.44	146.4	946.5	5.90	63.6	936.5	6.96
52.6	952.7	6.47	151.3	951.4	5.91	58.7	941.4	7.02
57.4	957.5	6.44	156.2	956.3	5.89	53.8	946.3	7.05
62.1	962.2	6.38	161.0	961.1	5.85	49.0	951.1	7.07
66.8	966.9	6.32	165.9	966.0	5.82	44.1	956.0	7.05
71.6	971.7	6.29	170.8	970.9	5.81	39.2	960.9	7.01
76.3	976.4	6.31	175.6	975.7	5.83	34.4	965.7	6.99
81.1	981.2	6.38	180.5	980.6	5.89	29.5	970.6	6.97
85.8	985.9	6.47	185.4	985.5	5.95	24.6	975.5	6.96
90.5	990.6	6.54	190.3	990.4	6.01	19.7	980.4	7.00
95.3	995.4	6.58	195.1	995.2	6.04	14.9	985.2	7.08
100.0	1000.1	6.56	200.0	1000.1	6.04	10.0	990.1	7.25

REV. X2
LRMS-2LJ
100817
Page 2 of 5

Frequency Mixer

LRMS-2LJ

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	0	+3	+6	0	+3	+6
200.1	31.44	30.48	29.64	37.20	38.63	36.47
240.1	30.32	29.35	28.50	35.87	38.22	35.81
280.1	29.53	28.59	27.77	34.72	37.45	34.93
320.1	29.04	28.11	27.29	34.46	37.73	34.32
360.1	28.92	28.00	27.18	34.05	37.98	33.94
400.1	28.86	28.02	27.23	33.68	38.43	34.13
440.1	29.21	28.31	27.50	34.02	39.34	33.27
480.1	29.62	28.76	27.95	34.72	39.30	32.14
520.1	30.39	29.43	28.55	35.14	37.96	30.25
560.1	31.49	30.48	29.52	36.26	35.70	28.47
600.1	32.64	31.62	30.52	37.86	34.27	27.18
640.1	34.48	33.42	32.07	41.16	32.58	25.93
680.1	36.85	36.14	34.20	42.12	33.06	26.00
720.1	39.60	40.09	36.71	47.16	31.20	25.16
760.1	40.53	48.04	41.32	41.63	29.03	24.22
800.1	38.66	48.79	45.09	34.54	26.12	22.54
840.1	36.36	40.40	39.77	29.90	23.32	20.43
880.1	33.35	35.54	35.54	27.67	21.72	18.95
920.1	31.26	32.67	32.65	25.97	20.47	17.78
960.1	29.32	30.40	30.45	25.60	20.27	17.44
1000.1	28.00	28.84	28.80	24.73	19.89	17.10
1040.1	27.18	27.93	27.90	23.75	19.43	16.77
1080.1	26.26	27.04	27.05	22.58	18.74	16.25
1120.1	25.76	26.53	26.60	20.89	17.62	15.44
1160.1	24.92	25.72	25.96	19.91	16.99	14.95
1200.1	24.30	25.17	25.56	19.18	16.54	14.59
1240.1	23.78	24.74	25.23	18.38	16.08	14.26
1300.1	23.47	24.52	25.14	16.82	15.02	13.47
1340.1	23.33	24.59	25.39	16.13	14.55	13.12
1400.1	22.89	24.39	25.52	15.28	14.09	12.85
1440.1	22.59	24.27	25.65	14.54	13.52	12.36
1500.1	21.71	23.60	25.36	13.78	13.19	12.20
1540.1	21.48	23.40	25.23	13.16	12.73	11.85
1600.1	20.31	22.02	23.67	12.16	12.18	11.58
1640.1	19.73	21.28	22.79	11.45	11.62	11.14
1700.1	19.09	20.44	21.87	10.15	10.54	10.30
1740.1	19.11	20.35	21.72	9.30	9.74	9.66
1800.1	19.53	20.65	22.00	8.36	8.75	8.74
1840.1	19.94	20.96	22.23	7.76	8.16	8.26
1900.1	21.12	22.09	23.26	7.15	7.47	7.58

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		0	+3	+6
200.1	230.1	22.54	21.24	20.45
240.1	270.1	21.20	19.97	19.26
280.1	310.1	20.01	18.87	18.23
320.1	350.1	18.64	17.73	17.20
360.1	390.1	17.54	16.73	16.30
400.1	430.1	16.62	15.83	15.42
440.1	470.1	16.17	15.38	14.98
480.1	510.1	16.23	15.37	14.94
520.1	550.1	16.62	15.77	15.31
560.1	590.1	17.41	16.68	16.23
600.1	630.1	18.37	17.74	17.36
640.1	670.1	19.72	19.16	18.70
680.1	710.1	21.19	20.52	19.88
720.1	750.1	22.79	21.63	20.62
760.1	790.1	25.26	23.31	21.65
800.1	830.1	26.16	24.28	22.00
840.1	870.1	23.45	23.02	21.83
880.1	910.1	20.41	20.33	19.91
920.1	950.1	18.04	18.08	18.05
960.1	990.1	16.22	16.12	16.07
1000.1	1030.1	14.91	14.70	14.61
1040.1	1070.1	14.07	13.72	13.66
1080.1	1110.1	13.66	13.30	13.23
1120.1	1150.1	13.35	13.20	13.21
1160.1	1190.1	13.08	13.03	13.12
1200.1	1230.1	12.85	12.92	13.12
1240.1	1270.1	12.72	12.87	13.14
1300.1	1330.1	12.93	13.23	13.62
1340.1	1370.1	13.13	13.67	14.14
1400.1	1430.1	13.61	14.43	15.15
1440.1	1470.1	13.82	14.98	15.84
1500.1	1530.1	14.09	15.57	16.64
1540.1	1570.1	13.86	15.56	16.76
1600.1	1630.1	13.11	14.95	16.25
1640.1	1670.1	12.75	14.65	16.08
1700.1	1730.1	11.70	13.64	15.46
1740.1	1770.1	11.75	13.62	15.63
1800.1	1830.1	11.67	13.49	15.53
1840.1	1870.1	12.21	13.95	15.95
1900.1	1930.1	13.28	14.88	16.60

REV. X2
LRMS-2LJ
100817
Page 3 of 5

Frequency Mixer

LRMS-2LJ

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=1000.1MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		0	+3	+6		0	+3	+6		0	+3	+6
200.1	230.1	11.93	10.19	9.38	200.1	1.21	1.68	2.34	10.0	2.25	1.77	1.48
240.1	270.1	8.35	7.28	6.83	240.1	1.25	1.76	2.48	14.9	2.22	1.77	1.45
280.1	310.1	6.32	5.59	5.23	280.1	1.28	1.81	2.54	19.7	2.21	1.76	1.44
320.1	350.1	4.83	4.33	4.10	320.1	1.30	1.83	2.57	24.6	2.21	1.76	1.44
360.1	390.1	3.86	3.50	3.32	360.1	1.32	1.85	2.59	29.5	2.20	1.76	1.43
400.1	430.1	3.17	2.86	2.74	400.1	1.32	1.79	2.44	34.4	2.20	1.76	1.44
440.1	470.1	2.63	2.40	2.31	440.1	1.34	1.83	2.50	39.2	2.20	1.76	1.44
480.1	510.1	2.27	2.06	1.97	480.1	1.37	1.86	2.51	44.1	2.20	1.76	1.44
520.1	550.1	1.98	1.79	1.70	520.1	1.38	1.90	2.59	49.0	2.21	1.76	1.44
560.1	590.1	1.80	1.60	1.50	560.1	1.43	1.98	2.70	53.8	2.20	1.77	1.45
600.1	630.1	1.67	1.45	1.32	600.1	1.47	2.03	2.74	58.7	2.21	1.77	1.45
640.1	670.1	1.62	1.38	1.23	640.1	1.53	2.09	2.79	63.6	2.21	1.77	1.46
680.1	710.1	1.64	1.39	1.22	680.1	1.52	2.04	2.68	68.5	2.20	1.77	1.46
720.1	750.1	1.71	1.45	1.29	720.1	1.56	2.07	2.71	73.3	2.20	1.77	1.46
760.1	790.1	1.88	1.61	1.44	760.1	1.60	2.10	2.73	78.2	2.20	1.77	1.46
800.1	830.1	2.07	1.80	1.61	800.1	1.67	2.19	2.82	83.1	2.20	1.77	1.45
840.1	870.1	2.37	2.08	1.88	840.1	1.76	2.32	2.98	87.9	2.19	1.76	1.45
880.1	910.1	2.66	2.36	2.14	880.1	1.81	2.34	2.98	92.8	2.19	1.76	1.45
920.1	950.1	2.92	2.63	2.40	920.1	1.87	2.41	3.04	97.7	2.18	1.76	1.45
960.1	990.1	3.13	2.88	2.67	960.1	1.87	2.36	2.94	102.6	2.18	1.76	1.45
1000.1	1030.1	3.28	3.07	2.89	1000.1	1.90	2.37	2.94	107.4	2.18	1.76	1.45
1040.1	1070.1	3.37	3.21	3.08	1040.1	1.95	2.41	2.96	112.3	2.18	1.76	1.46
1080.1	1110.1	3.41	3.29	3.19	1080.1	2.01	2.47	3.01	117.2	2.18	1.76	1.46
1120.1	1150.1	3.45	3.33	3.26	1120.1	2.13	2.61	3.16	122.1	2.18	1.77	1.47
1160.1	1190.1	3.54	3.40	3.34	1160.1	2.20	2.67	3.22	126.9	2.18	1.77	1.47
1200.1	1230.1	3.61	3.44	3.38	1200.1	2.23	2.68	3.21	131.8	2.18	1.77	1.47
1240.1	1270.1	3.67	3.49	3.43	1240.1	2.26	2.69	3.19	136.7	2.18	1.77	1.48
1300.1	1330.1	3.76	3.53	3.43	1300.1	2.40	2.80	3.27	141.5	2.18	1.77	1.47
1340.1	1370.1	3.86	3.58	3.43	1340.1	2.46	2.83	3.29	146.4	2.18	1.77	1.47
1400.1	1430.1	3.87	3.51	3.34	1400.1	2.54	2.85	3.26	151.3	2.17	1.76	1.47
1440.1	1470.1	3.99	3.58	3.33	1440.1	2.61	2.92	3.30	156.2	2.17	1.76	1.47
1500.1	1530.1	4.01	3.57	3.26	1500.1	2.67	2.88	3.20	161.0	2.16	1.76	1.47
1540.1	1570.1	4.13	3.64	3.29	1540.1	2.74	2.93	3.25	165.9	2.17	1.76	1.47
1600.1	1630.1	4.22	3.68	3.29	1600.1	2.81	2.92	3.18	170.8	2.16	1.76	1.48
1640.1	1670.1	4.25	3.69	3.30	1640.1	2.91	3.00	3.25	175.6	2.16	1.77	1.48
1700.1	1730.1	4.59	3.95	3.54	1700.1	3.04	3.10	3.30	180.5	2.17	1.77	1.49
1740.1	1770.1	4.69	4.05	3.62	1740.1	3.16	3.18	3.35	185.4	2.17	1.77	1.49
1800.1	1830.1	5.31	4.44	3.90	1800.1	3.34	3.31	3.48	190.3	2.17	1.78	1.50
1840.1	1870.1	5.65	4.67	4.07	1840.1	3.43	3.42	3.51	195.1	2.17	1.78	1.50
1900.1	1930.1	6.37	5.16	4.41	1900.1	3.59	3.56	3.62	200.0	2.16	1.78	1.50

REV. X2
LRMS-2LJ
100817
Page 4 of 5

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	+6	8	5	25	18	40	49	52	47	57
1	-	13	+0	26	21	33	37	39	50	61	72	64
2	>100	43	39	41	38	47	48	55	62	67	>76	68
3	>100	65	59	58	68	63	73	64	>76	70	>76	>76
4	>100	>76	>76	>76	>76	76	>76	>76	>76	>76	>76	>76
5	>100	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76
6	>100	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76
7	>100	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76
8	>100	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76
9	>100	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76
10	>100	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76	>76
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 900.1 MHz; -18.00 dBm.
LO IN: 930.1 MHz; +3.00 dBm
IF OUT: 30 MHz; -24.42 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	3	20	18	40	29	57	75	69	80	>86
1	-	13	+0	26	22	36	42	46	56	76	67	78
2	99	32	30	33	29	40	40	51	59	70	77	75
3	>100	44	40	39	57	47	55	51	62	58	76	82
4	>100	61	58	58	54	50	60	56	59	66	76	82
5	>100	74	65	73	65	58	63	60	74	63	>86	72
6	>100	>86	>86	75	80	73	70	68	73	73	73	84
7	>100	>86	>86	>86	>86	>86	>86	75	76	79	>86	77
8	>100	>86	>86	>86	>86	>86	>86	>86	84	81	83	>86
9	>100	>86	>86	>86	>86	>86	>86	>86	>86	>86	85	>86
10	>100	>86	>86	>86	>86	>86	>86	>86	>86	>86	>86	>86
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 900.1 MHz; -8.00 dBm.
LO IN: 930.1 MHz; +3.00 dBm
IF OUT: 30 MHz; -14.49 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
LRMS-2LJ
100817
Page 5 of 5

