

Frequency Multiplier (X5)

RMK-5-13+

Typical Performance Data

FREQUENCY (MHz)							CONVERSION LOSS (dB)	RF IN = +17 dBm					
								HARMONIC OUTPUT* (-dBc)					
X1 OUTPUT	X2 OUTPUT	X3 OUTPUT	X4 OUTPUT	X5 OUTPUT	X6 OUTPUT	X7 OUTPUT	X5 OUTPUT	X1 OUTPUT	X2 OUTPUT	X3 OUTPUT	X4 OUTPUT	X6 OUTPUT	X7 OUTPUT
130	260	390	520	650	780	910	21.95	6.26	79.83	-0.24	64.11	67.24	4.59
140	280	420	560	700	840	980	22.06	4.91	73.97	-1.09	64.09	74.11	5.39
150	300	450	600	750	900	1050	21.06	4.59	74.17	-1.60	65.07	77.10	5.27
160	320	480	640	800	960	1120	21.21	3.35	74.39	-2.49	64.97	85.69	5.71
170	340	510	680	850	1020	1190	21.64	1.94	75.77	-3.32	63.82	74.36	6.64
180	360	540	720	900	1080	1260	21.27	1.26	74.11	-3.89	64.03	76.02	6.50
190	380	570	760	950	1140	1330	21.35	0.22	71.91	-4.45	64.16	72.50	6.69
200	400	600	800	1000	1200	1400	21.98	-1.20	69.72	-5.23	65.48	67.62	7.51
210	420	630	840	1050	1260	1470	22.10	-2.13	68.35	-5.81	64.91	65.38	7.67
220	440	660	880	1100	1320	1540	22.11	-2.95	66.35	-6.17	65.04	64.84	7.56

* Harmonic Output below power level of X5 Output.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
RMK-5-13+
1/29/2015
Page 1 of 1