

Type-N/BNC Adaptenuator

NM-BF-3

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	BNC-FEMALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
1	2.99	46.06	46.06
5	2.99	46.06	46.06
10	3.01	46.06	46.06
50	3.01	46.06	46.06
100	3.02	40.09	40.09
500	3.09	30.71	29.42
1000	3.16	26.44	24.94
1500	3.24	25.66	24.94
1700	3.24	26.44	26.44
2000	3.28	29.42	30.71

REV. X1
NM-BF-3
061113
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

