

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	SMA-FEMALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
1	19.97	56.33	80.09
10	19.98	56.54	68.32
50	19.99	58.21	63.53
100	20.02	58.52	62.72
150	20.01	57.15	62.87
200	20.00	55.03	63.79
250	20.02	54.20	65.51
300	20.03	53.31	67.72
350	20.05	52.60	69.18
400	20.07	52.79	68.91
450	20.05	50.81	67.97
500	20.06	50.01	63.33
550	20.10	49.13	59.92
600	20.10	47.96	58.03
650	20.10	47.16	56.07
700	20.13	45.65	54.19
750	20.15	44.87	52.39
800	20.16	43.91	51.28
850	20.19	42.95	50.05
900	20.20	42.21	48.70
950	20.22	41.38	47.57
1000	20.24	40.80	46.49
1100	20.28	39.39	44.74
1200	20.34	38.19	43.00
1300	20.37	36.99	41.54
1400	20.42	35.84	40.13
1500	20.47	34.91	38.87
1600	20.53	33.97	37.71
1700	20.57	33.16	36.71
1800	20.60	32.33	35.73
1900	20.63	31.58	34.76
2000	20.72	30.92	33.93
2100	20.72	30.34	33.12
2200	20.80	29.74	32.37
2300	20.82	29.19	31.67
2400	20.90	28.64	31.01
2500	20.93	28.10	30.35
2600	20.98	27.63	29.79
2700	21.01	27.22	29.18
2800	21.07	26.83	28.65
2900	21.11	26.42	28.09
3000	21.14	26.05	27.55