

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10	0.16	30.70	10	1.563
67	0.27	16.40	39	1.282
95	0.37	13.40	67	1.509
124	0.53	11.10	95	1.368
152	0.73	9.40	124	1.468
180	0.99	7.90	125	1.487
200	1.24	7.10	180	1.297
267	2.35	4.90	200	1.351
300	3.06	4.10	234	1.343
400	5.85	2.50	267	1.534
458	7.82	1.80	300	1.427
515	9.91	1.30	400	1.383
543	11.02	1.10	429	1.448
572	12.18	0.90	458	0.984
600	13.35	0.80	486	1.599
700	17.70	0.50	515	1.173
729	18.96	0.50	543	1.140
758	20.25	0.50	572	1.134
773	20.92	0.50	600	0.869
787	21.51	0.50	700	0.878
801	22.10	0.50	715	0.983
900	26.28	0.60	729	0.767
950	28.25	0.70	744	1.244
1000	30.16	0.80	758	0.807
1050	32.02	0.80	773	1.089
1100	33.74	0.90	787	1.144
1125	34.62	0.90	801	0.587
1150	35.50	1.00	900	0.940
1175	36.29	1.00	925	0.980
1200	37.10	1.00	950	0.475