

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	43.12	0.00	11.0	4.430
3.0	43.76	0.00	12.0	27.530
5.0	44.40	0.10	12.5	15.990
7.0	44.36	0.10	13.0	3.880
9.0	45.32	0.10	13.5	10.690
10.0	45.99	0.10	14.0	10.460
11.0	46.57	0.10	15.0	10.210
12.0	49.64	0.10	16.0	9.290
12.5	51.45	0.10	17.0	21.160
13.0	53.51	0.10	17.5	20.410
13.5	58.61	0.10	18.0	21.900
15.0	51.13	0.10	19.0	26.000
17.0	36.08	0.10	19.5	29.470
17.5	33.22	0.10	20.0	31.470
18.0	30.58	0.20	21.0	39.770
19.0	25.70	0.20	22.0	49.670
19.5	23.35	0.20	23.0	64.870
21.0	16.44	0.40	24.0	81.190
23.0	7.62	1.50	24.5	87.110
24.0	4.02	3.50	25.0	87.600
24.5	2.71	5.30	26.0	76.810
25.0	1.76	7.80	26.5	68.460
26.0	0.80	15.40	27.0	60.970
27.0	0.55	20.30	27.5	54.670
27.5	0.52	19.90	117.0	1.850
133.5	0.17	37.70	133.5	1.650
150.0	0.18	33.70	150.0	1.360
167.0	0.20	30.60	167.0	1.290
183.5	0.19	28.40	183.5	1.250
200.0	0.20	26.80	200.0	1.160

REV. X1
PHP-25+
060725

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

