

Typical Performance Data

FREQUENCY	INSERTION LOSS	E-Z Lock SMA-MALE RETURN LOSS	N-MALE RETURN LOSS
(MHz)	(dB)	(dB)	(dB)
10.0	0.07	35.8	36.2
50.0	0.15	48.2	43.7
100.0	0.23	45.9	42.9
200.0	0.33	37.6	36.7
300.0	0.42	31.8	31.9
400.0	0.48	37.4	36.4
500.0	0.54	41.6	41.4
600.0	0.60	29.8	29.4
700.0	0.65	29.5	29.0
800.0	0.69	38.9	38.6
900.0	0.74	28.9	29.2
1000.0	0.79	27.6	27.1
1100.0	0.83	31.5	30.2
1250.0	0.89	27.6	28.1
1750.0	1.06	27.3	27.3
2000.0	1.15	25.0	25.2
2250.0	1.21	27.1	29.3
2500.0	1.28	35.0	42.4
2750.0	1.35	27.8	28.4
3000.0	1.42	29.6	28.6
3250.0	1.48	35.9	40.5
3500.0	1.54	31.8	33.1
3750.0	1.59	31.5	30.2
4000.0	1.64	33.7	36.8
4500.0	1.77	30.3	30.6
5000.0	1.90	28.7	34.6
5500.0	2.00	33.4	34.3
6000.0	2.11	31.8	37.1
6500.0	2.21	29.9	35.9
7000.0	2.32	37.3	36.6
7500.0	2.56	22.2	29.8
8000.0	2.63	33.3	28.5
8500.0	2.58	24.7	25.6
9000.0	2.68	24.7	24.2
9500.0	2.69	28.2	23.9
10000.0	2.83	23.4	22.7
10500.0	2.91	32.0	22.9
11000.0	3.07	22.0	22.0
11500.0	3.33	33.2	20.6
12000.0	3.55	24.7	23.5
12500.0	3.59	22.6	18.0
13000.0	3.40	34.7	23.6
13500.0	3.36	20.8	19.6
14000.0	3.40	30.7	21.2
14500.0	3.54	22.3	25.5
15000.0	3.56	17.8	22.4
15500.0	3.60	24.7	27.7
16000.0	3.73	30.9	28.8
16500.0	3.74	39.5	37.8
17000.0	3.94	36.4	46.4
17500.0	4.09	23.8	30.0
18000.0	4.02	27.0	33.9