

Frequency Mixer

SBL-2LH+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)			RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)			RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+5dBm (dB)		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+7	+10	+13			+7	+10	+13			+7	+10	+13
5.0	35.0	6.35	5.97	5.79	10.1	40.1	18.76	20.04	20.05	10.1	40.1	1.22	0.93	0.74
10.0	40.0	6.27	5.89	5.71	51.1	81.1	18.85	19.34	18.90	51.1	81.1	1.18	0.91	0.78
51.1	81.1	6.09	5.72	5.50	92.0	122.0	15.96	16.91	21.40	92.0	122.0	1.16	0.88	0.73
92.0	122.0	6.05	5.68	5.47	133.0	163.0	16.26	20.27	29.15	133.0	163.0	1.15	0.86	0.68
133.0	163.0	5.95	5.65	5.49	173.9	203.9	15.81	22.72	21.25	173.9	203.9	1.08	0.80	0.62
173.9	203.9	5.97	5.65	5.48	214.9	244.9	20.18	19.21	19.88	214.9	244.9	1.08	0.74	0.57
214.9	244.9	5.83	5.59	5.45	255.8	285.8	25.42	19.54	20.31	255.8	285.8	1.04	0.68	0.54
255.8	285.8	5.85	5.62	5.47	296.8	326.8	18.33	24.35	23.60	296.8	326.8	1.04	0.71	0.56
296.8	326.8	5.73	5.55	5.43	337.7	367.7	13.80	13.84	14.43	337.7	367.7	1.03	0.72	0.59
337.7	367.7	5.74	5.54	5.41	378.7	408.7	12.29	13.97	17.44	378.7	408.7	0.89	0.64	0.55
378.7	408.7	5.76	5.56	5.40	419.6	449.6	15.08	14.39	15.72	419.6	449.6	0.84	0.63	0.56
419.6	449.6	5.83	5.60	5.45	440.1	470.1	20.04	20.21	23.24	440.1	470.1	0.86	0.62	0.55
440.1	470.1	5.86	5.63	5.44	481.1	511.1	18.72	18.41	19.68	481.1	511.1	1.02	0.76	0.64
481.1	511.1	5.87	5.67	5.52	501.5	531.5	22.32	18.83	21.36	501.5	531.5	1.06	0.82	0.67
501.5	531.5	5.84	5.62	5.51	542.5	572.5	15.99	15.77	16.70	542.5	572.5	1.30	1.01	0.84
542.5	572.5	5.91	5.76	5.62	563.0	593.0	15.12	15.72	16.27	563.0	593.0	1.43	1.13	0.92
563.0	593.0	5.95	5.79	5.70	603.9	633.9	10.93	12.73	15.03	603.9	633.9	1.61	1.29	1.03
603.9	633.9	6.12	5.97	5.89	624.4	654.4	9.56	10.64	12.64	624.4	654.4	1.76	1.38	1.12
665.3	695.3	6.40	6.25	6.12	665.3	695.3	8.41	9.47	10.92	665.3	695.3	1.94	1.55	1.32
685.8	715.8	6.44	6.24	6.08	685.8	715.8	9.14	10.89	13.07	685.8	715.8	1.97	1.56	1.36
726.8	756.8	6.72	6.40	6.18	726.8	756.8	9.02	12.23	15.24	726.8	756.8	2.16	1.75	1.50
747.2	777.2	6.94	6.60	6.29	747.2	777.2	6.92	9.44	12.47	747.2	777.2	2.26	1.84	1.56
788.2	818.2	7.30	6.86	6.53	788.2	818.2	6.28	8.20	10.69	788.2	818.2	2.31	1.87	1.64
808.7	838.7	7.39	6.93	6.53	808.7	838.7	6.45	8.68	11.49	808.7	838.7	2.29	1.85	1.63
849.6	879.6	7.54	6.77	6.30	849.6	879.6	7.54	12.49	17.81	849.6	879.6	2.30	1.98	1.76
870.1	900.1	7.61	6.75	6.24	870.1	900.1	8.05	15.25	18.30	870.1	900.1	2.28	2.05	1.77
911.1	941.1	7.95	6.82	6.19	911.1	941.1	6.76	15.67	14.98	911.1	941.1	2.19	2.17	1.91
931.5	961.5	8.19	6.99	6.27	931.5	961.5	5.59	13.15	14.44	931.5	961.5	2.07	2.10	1.88
972.5	1002.5	8.37	7.23	6.33	972.5	1002.5	5.23	10.09	13.79	972.5	1002.5	1.95	2.06	1.98
993.0	1023.0	8.55	7.46	6.52	993.0	1023.0	5.36	9.15	14.46	993.0	1023.0	1.81	1.89	1.91
1033.9	1063.9	8.67	7.67	6.78	1033.9	1063.9	5.98	8.69	13.61	1033.9	1063.9	1.75	1.86	2.02
1054.4	1084.4	8.88	7.94	7.06	1054.4	1084.4	6.26	8.64	12.64	1054.4	1084.4	1.59	1.74	1.93
1095.3	1125.3	9.20	8.37	7.55	1095.3	1125.3	6.55	8.48	11.61	1095.3	1125.3	1.33	1.52	1.75
1115.8	1145.8	9.49	8.67	7.92	1115.8	1145.8	6.54	8.32	11.24	1115.8	1145.8	1.11	1.31	1.55
1156.8	1186.8	9.73	8.96	8.17	1156.8	1186.8	6.99	8.53	11.78	1156.8	1186.8	0.94	1.10	1.41
1177.2	1207.2	9.73	8.89	8.14	1177.2	1207.2	7.73	10.36	15.02	1177.2	1207.2	0.98	1.20	1.47
1218.2	1248.2	9.63	8.98	8.51	1218.2	1248.2	12.81	15.82	20.98	1218.2	1248.2	1.21	1.21	1.27
1238.7	1268.7	9.87	9.34	8.88	1238.7	1268.7	13.80	15.62	19.36	1238.7	1268.7	1.07	1.02	1.02
1279.6	1309.6	10.65	10.14	9.67	1279.6	1309.6	14.99	17.17	17.37	1279.6	1309.6	0.70	0.61	0.57
1300.1	1330.1	10.92	10.41	9.96	1300.1	1330.1	14.95	18.35	19.66	1300.1	1330.1	0.59	0.46	0.42

REV. X2

SBL-2LH+

100818

Page 1 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Frequency Mixer

SBL-2LH+

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=500.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=10.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=1000.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+10			+10			+10
490.0	10.1	6.01	10.0	20.1	5.73	990.0	10.1	8.43
477.7	22.4	5.94	30.0	40.1	5.57	970.0	30.1	8.33
465.4	34.7	5.86	50.0	60.1	5.68	950.0	50.1	8.23
453.1	47.0	5.87	70.0	80.1	5.68	930.0	70.1	8.23
440.8	59.3	5.88	90.0	100.1	5.71	910.0	90.1	8.13
428.5	71.6	5.76	110.0	120.1	5.72	890.0	110.1	8.03
416.2	83.9	5.73	130.0	140.1	5.68	870.0	130.1	7.96
403.8	96.3	5.67	150.0	160.1	5.72	850.0	150.1	8.00
391.5	108.6	5.55	170.0	180.1	5.74	830.0	170.1	7.99
379.2	120.9	5.57	190.0	200.1	5.79	810.0	190.1	7.93
366.9	133.2	5.50	210.0	220.1	5.73	790.0	210.1	7.96
354.6	145.5	5.43	230.0	240.1	5.75	770.0	230.1	7.92
342.3	157.8	5.46	250.0	260.1	5.81	750.0	250.1	7.95
330.0	170.1	5.45	270.0	280.1	5.79	730.0	270.1	8.07
317.7	182.4	5.43	290.0	300.1	5.81	710.0	290.1	8.01
305.4	194.7	5.47	310.0	320.1	5.83	690.0	310.1	7.99
293.1	207.0	5.45	330.0	340.1	5.89	670.0	330.1	7.95
280.8	219.3	5.46	350.0	360.1	5.87	650.0	350.1	8.00
268.5	231.6	5.49	370.0	380.1	5.88	630.0	370.1	7.99
256.2	243.9	5.46	390.0	400.1	5.85	610.0	390.1	7.88
243.8	256.3	5.54	430.0	440.1	5.93	570.0	430.1	7.84
231.5	268.6	5.54	450.0	460.1	5.99	550.0	450.1	7.92
219.2	280.9	5.50	490.0	500.1	6.10	510.0	490.1	7.79
206.9	293.2	5.51	510.0	520.1	6.14	490.0	510.1	7.76
194.6	305.5	5.49	550.0	560.1	6.67	450.0	550.1	7.58
182.3	317.8	5.48	570.0	580.1	6.87	430.0	570.1	7.53
170.0	330.1	5.53	610.0	620.1	6.99	390.0	610.1	7.34
157.7	342.4	5.54	630.0	640.1	7.05	370.0	630.1	7.34
145.4	354.7	5.59	670.0	680.1	6.79	330.0	670.1	7.46
133.1	367.0	5.65	690.0	700.1	6.64	310.0	690.1	7.49
120.8	379.3	5.64	730.0	740.1	6.34	270.0	730.1	6.87
108.5	391.6	5.66	750.0	760.1	6.19	250.0	750.1	6.75
96.2	403.9	5.66	790.0	800.1	6.07	210.0	790.1	6.95
83.8	416.3	5.64	810.0	820.1	5.99	190.0	810.1	6.90
71.5	428.6	5.66	850.0	860.1	5.93	150.0	850.1	6.67
59.2	440.9	5.66	870.0	880.1	5.86	130.0	870.1	6.44
46.9	453.2	5.63	910.0	920.1	5.93	90.0	910.1	6.25
34.6	465.5	5.66	930.0	940.1	5.96	70.0	930.1	6.43
22.3	477.8	5.67	970.0	980.1	6.01	30.0	970.1	6.82
10.0	490.1	5.75	990.0	1000.1	5.98	10.0	990.1	6.90

REV. X2
SBL-2LH+
100818
Page 2 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+7	+10	+13	+7	+10	+13
5.0	50.42	52.74	55.33	92.39	87.33	84.57
10.0	50.26	52.59	55.18	88.15	81.78	79.01
51.1	69.83	72.07	73.62	63.27	63.28	64.03
92.0	65.11	67.13	68.95	59.74	59.83	59.18
133.0	62.03	64.31	66.77	56.06	56.01	56.07
173.9	59.60	61.93	64.27	53.39	53.32	53.98
214.9	58.06	60.59	62.91	51.42	51.77	52.70
255.8	56.84	59.34	61.69	49.92	50.71	51.38
296.8	55.95	58.26	60.45	48.91	50.07	50.46
337.7	55.34	57.91	59.93	47.64	48.71	49.14
378.7	54.44	57.70	60.60	47.63	48.58	48.89
419.6	53.06	55.48	57.86	47.62	48.34	48.35
440.1	52.80	55.10	57.48	46.78	47.24	47.09
481.1	52.96	55.41	57.77	47.45	47.64	46.88
501.5	53.51	57.43	61.63	47.02	47.58	47.46
542.5	53.08	56.05	60.17	45.46	44.52	44.13
563.0	53.28	56.16	59.43	44.89	44.22	43.81
603.9	53.24	57.68	63.37	43.87	42.41	41.95
665.3	55.92	64.81	70.52	44.82	42.39	40.37
685.8	56.56	62.84	60.50	44.76	42.58	40.48
726.8	52.30	54.96	57.61	44.02	41.46	39.41
747.2	51.38	55.04	59.75	42.38	39.55	37.80
788.2	52.05	56.00	58.80	41.75	39.06	36.62
808.7	52.78	57.63	56.62	41.04	38.81	36.73
849.6	50.88	55.86	56.38	39.34	37.95	36.04
870.1	49.32	52.53	54.23	37.94	36.98	35.45
911.1	48.18	52.23	54.44	35.46	34.52	33.64
931.5	47.13	51.88	57.10	34.38	33.31	32.66
972.5	46.19	51.14	57.14	33.85	31.98	31.00
993.0	46.56	53.16	58.01	33.28	31.41	30.25
1033.9	46.19	52.51	56.56	32.80	31.06	29.35
1054.4	44.97	49.40	55.37	32.41	30.75	29.19
1095.3	45.01	49.23	53.67	31.92	30.57	29.19
1115.8	45.10	50.46	57.28	31.59	30.44	29.20
1156.8	45.77	51.43	60.07	30.98	30.29	29.29
1177.2	46.16	52.36	57.93	30.64	30.26	29.18
1218.2	48.94	62.54	47.12	29.60	28.95	26.90
1238.7	52.05	53.57	45.74	28.95	27.67	26.16
1279.6	52.01	50.10	43.71	27.34	26.63	25.30
1300.1	49.50	48.80	42.73	27.03	26.61	25.49

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+7	+10	+13
10.1	40.1	46.43	51.09	56.89
51.1	81.1	38.12	38.16	38.08
92.0	122.0	33.58	33.93	33.71
133.0	163.0	30.80	31.17	31.24
173.9	203.9	29.31	29.71	29.78
214.9	244.9	28.64	28.73	28.84
255.8	285.8	28.45	28.42	28.64
296.8	326.8	28.56	28.83	28.98
337.7	367.7	28.46	29.02	29.28
378.7	408.7	28.08	28.38	28.63
419.6	449.6	27.55	27.52	27.55
440.1	470.1	27.44	27.44	27.45
481.1	511.1	27.00	27.15	27.47
501.5	531.5	26.61	27.07	27.76
542.5	572.5	25.30	25.41	25.69
563.0	593.0	24.69	24.70	24.86
603.9	633.9	23.12	22.94	22.93
624.4	654.4	22.38	22.26	22.25
665.3	695.3	21.46	21.30	21.19
685.8	715.8	20.84	20.61	20.42
726.8	756.8	20.34	20.15	20.17
747.2	777.2	20.27	20.13	20.10
788.2	818.2	20.54	20.59	20.77
808.7	838.7	20.67	20.83	20.98
849.6	879.6	20.90	21.13	21.24
870.1	900.1	20.84	20.95	20.92
911.1	941.1	20.47	20.21	19.98
931.5	961.5	20.38	19.97	19.65
972.5	1002.5	20.08	19.64	19.08
993.0	1023.0	19.72	19.50	18.93
1033.9	1063.9	19.08	18.98	18.75
1054.4	1084.4	18.73	18.71	18.46
1095.3	1125.3	18.03	18.08	18.03
1115.8	1145.8	17.71	17.79	17.82
1156.8	1186.8	17.16	17.34	17.49
1177.2	1207.2	17.01	17.24	17.43
1218.2	1248.2	16.56	16.62	16.51
1238.7	1268.7	16.18	16.20	16.04
1279.6	1309.6	15.49	15.36	15.19
1300.1	1330.1	15.28	15.03	14.84

Frequency Mixer

SBL-2LH+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)		
		@LO (dBm)		
		+7	+10	+13
5.0	35.0	1.19	1.25	1.36
10.0	40.0	1.10	1.18	1.30
51.1	81.1	1.06	1.04	1.10
92.0	122.0	1.08	1.09	1.16
133.0	163.0	1.10	1.13	1.20
173.9	203.9	1.11	1.16	1.23
214.9	244.9	1.13	1.19	1.26
255.8	285.8	1.15	1.20	1.26
296.8	326.8	1.16	1.25	1.32
337.7	367.7	1.13	1.22	1.28
378.7	408.7	1.10	1.17	1.24
419.6	449.6	1.10	1.14	1.18
440.1	470.1	1.12	1.17	1.21
481.1	511.1	1.16	1.23	1.30
501.5	531.5	1.18	1.29	1.37
542.5	572.5	1.19	1.29	1.37
563.0	593.0	1.21	1.32	1.39
603.9	633.9	1.24	1.34	1.41
624.4	654.4	1.26	1.35	1.40
665.3	695.3	1.29	1.35	1.38
685.8	715.8	1.31	1.35	1.38
726.8	756.8	1.32	1.34	1.35
747.2	777.2	1.33	1.34	1.34
788.2	818.2	1.32	1.31	1.28
808.7	838.7	1.31	1.29	1.26
849.6	879.6	1.25	1.19	1.14
870.1	900.1	1.21	1.14	1.09
911.1	941.1	1.16	1.06	1.03
931.5	961.5	1.17	1.08	1.08
972.5	1002.5	1.25	1.21	1.24
993.0	1023.0	1.32	1.29	1.32
1033.9	1063.9	1.55	1.52	1.52
1054.4	1084.4	1.68	1.65	1.63
1095.3	1125.3	2.03	2.00	1.96
1115.8	1145.8	2.25	2.21	2.15
1156.8	1186.8	2.72	2.66	2.60
1177.2	1207.2	2.99	2.93	2.85
1218.2	1248.2	3.60	3.54	3.47
1238.7	1268.7	3.93	3.89	3.83
1279.6	1309.6	4.62	4.61	4.59
1300.1	1330.1	4.95	4.95	4.92

LO (MHz)	LO VSWR (:1)		
	@LO (dBm)		
	+7	+10	+13
5.0	2.01	2.82	3.90
10.0	1.82	2.63	3.70
51.1	1.79	2.65	3.86
92.0	1.67	2.41	3.39
133.0	1.75	2.58	3.68
173.9	1.67	2.40	3.38
214.9	1.71	2.48	3.50
255.8	1.71	2.46	3.45
296.8	1.69	2.43	3.39
337.7	1.75	2.52	3.48
378.7	1.73	2.44	3.35
419.6	1.78	2.54	3.48
440.1	1.80	2.53	3.44
481.1	1.78	2.48	3.36
501.5	1.82	2.52	3.40
542.5	1.85	2.55	3.40
563.0	1.85	2.54	3.38
603.9	1.90	2.59	3.43
624.4	1.92	2.61	3.43
665.3	1.92	2.58	3.39
685.8	1.94	2.59	3.40
726.8	1.96	2.57	3.34
747.2	1.99	2.59	3.35
788.2	2.07	2.69	3.46
808.7	2.09	2.71	3.47
849.6	2.10	2.69	3.40
870.1	2.13	2.70	3.42
911.1	2.20	2.78	3.47
931.5	2.22	2.81	3.50
972.5	2.26	2.88	3.57
993.0	2.28	2.91	3.60
1033.9	2.31	2.93	3.62
1054.4	2.33	2.95	3.65
1095.3	2.35	2.96	3.65
1115.8	2.37	2.96	3.65
1156.8	2.39	2.98	3.65
1177.2	2.38	2.95	3.61
1218.2	2.33	2.87	3.54
1238.7	2.35	2.92	3.61
1279.6	2.55	3.10	3.76
1300.1	2.63	3.17	3.82

IF (OUT) (MHz)	IF VSWR @LO=1000.1MHz (:1)		
	@LO (dBm)		
	+7	+10	+13
5.0	1.73	1.46	1.19
10.0	1.74	1.47	1.19
30.2	2.75	2.17	1.79
50.4	2.82	2.29	1.87
70.6	2.88	2.36	1.94
90.8	2.84	2.29	1.91
111.0	2.89	2.30	1.91
131.2	2.98	2.40	2.01
151.4	3.01	2.45	2.06
171.6	3.00	2.43	2.04
191.8	3.08	2.46	2.10
212.0	3.14	2.51	2.17
232.2	3.14	2.52	2.17
252.4	3.18	2.57	2.20
272.7	3.23	2.61	2.25
292.9	3.26	2.60	2.26
313.1	3.29	2.60	2.27
333.3	3.36	2.67	2.32
353.5	3.43	2.73	2.36
373.7	3.45	2.73	2.34
393.9	3.48	2.73	2.34
434.3	3.62	2.84	2.41
454.5	3.60	2.84	2.38
494.9	3.69	2.91	2.41
515.1	3.67	2.90	2.39
555.5	3.75	2.99	2.44
575.7	3.76	3.01	2.46
616.1	3.74	3.03	2.48
636.3	3.78	3.07	2.52
676.7	3.73	3.07	2.51
696.9	3.77	3.14	2.57
737.3	3.61	3.02	2.49
757.6	3.65	3.07	2.53
798.0	3.51	3.00	2.47
818.2	3.47	2.96	2.45
858.6	3.35	2.86	2.37
878.8	3.31	2.83	2.35
919.2	3.23	2.79	2.31
939.4	3.10	2.68	2.22
979.8	3.11	2.67	2.22
1000.0	2.19	1.91	1.69

REV. X2
SBL-2LH+
100818
Page 4 of 5

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	28	42	39	53	39	63	44	66	57	87
1	-	23	+0	32	11	40	24	52	44	51	56	71
2	90	73	48	62	50	65	50	65	60	65	60	74
3	>100	55	43	69	44	63	39	60	48	64	59	59
4	>100	88	76	80	68	74	70	80	61	77	78	78
5	>100	84	65	61	57	64	57	63	56	61	74	71
6	>100	>94	91	86	85	84	>94	83	88	84	84	94
7	>100	86	82	89	>94	80	79	76	72	79	70	72
8	>100	>94	>94	>94	>94	>94	>94	>94	>94	92	90	>94
9	>100	>94	>94	>94	>94	>94	92	93	81	89	82	92
10	>100	>94	>94	>94	>94	>94	>94	>94	>94	>94	>94	>94
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions:

RF IN: 500.1 MHz; 0.00 dBm.
LO IN: 530.01 MHz; +10.00 dBm
IF OUT: 29.91 MHz; -5.82 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	20	32	24	39	27	45	30	47	40	64
1	-	22	+0	35	11	45	23	46	42	43	49	58
2	>100	72	56	63	58	76	55	71	64	70	66	84
3	>100	66	73	69	66	69	75	67	69	75	73	75
4	>100	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84
5	>100	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84
6	>100	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84
7	>100	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84
8	>100	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84
9	>100	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84
10	>100	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84	>84
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions:

RF IN: 500.1 MHz; -10.00 dBm.
LO IN: 530.01 MHz; +10.00 dBm
IF OUT: 29.91 MHz; -15.74 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
SBL-2LH+
100818
Page 5 of 5

