







Typical Performance Graphs

Test Conditions: Temperature = +25°C.






Typical Performance Graphs

Test Conditions: Temperature = +25°C.






Typical Performance Graphs

Test Conditions: Temperature = +25°C.






Typical Performance Graphs

Test Conditions: Temperature = 0°C.






Typical Performance Graphs

Test Conditions: Temperature = 0°C.






Typical Performance Graphs

Test Conditions: Temperature = 0°C.






Typical Performance Graphs

Test Conditions: Temperature = +50°C.



Typical Performance Graphs

Test Conditions: Temperature = +50°C.



Typical Performance Graphs

Test Conditions: Temperature = +50°C.

