

4 Way-0° Power Splitter/Combiner

SCA-4-10+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
5	6.37	6.22	6.35	6.52	0.30	0.65	29.32	36.36	33.10	1.05	1.33	1.28	1.29	1.34
10	6.37	6.24	6.36	6.52	0.28	0.32	31.21	38.25	34.59	1.04	1.29	1.25	1.25	1.30
15	6.38	6.25	6.36	6.52	0.27	0.22	31.60	38.71	34.87	1.03	1.27	1.24	1.24	1.29
20	6.38	6.25	6.36	6.51	0.27	0.14	31.56	38.76	34.85	1.04	1.27	1.23	1.24	1.28
25	6.38	6.25	6.36	6.52	0.27	0.12	31.41	38.67	34.74	1.04	1.27	1.23	1.24	1.28
30	6.39	6.25	6.37	6.53	0.27	0.13	31.24	38.54	34.57	1.04	1.27	1.23	1.24	1.28
35	6.39	6.26	6.37	6.53	0.27	0.12	31.07	38.42	34.35	1.04	1.27	1.23	1.24	1.28
40	6.40	6.27	6.38	6.54	0.27	0.13	30.91	38.29	34.12	1.04	1.27	1.23	1.23	1.28
45	6.41	6.27	6.38	6.55	0.27	0.13	30.76	38.16	33.87	1.04	1.27	1.23	1.23	1.28
50	6.42	6.28	6.39	6.55	0.27	0.18	30.62	38.05	33.60	1.04	1.27	1.23	1.23	1.27
75	6.45	6.31	6.42	6.58	0.28	0.21	29.95	37.64	32.27	1.05	1.27	1.22	1.23	1.27
100	6.47	6.33	6.45	6.61	0.29	0.27	29.32	37.33	31.00	1.06	1.26	1.22	1.22	1.27
125	6.50	6.35	6.48	6.64	0.29	0.35	28.71	37.11	29.87	1.07	1.26	1.22	1.22	1.26
150	6.52	6.36	6.50	6.66	0.29	0.40	28.13	36.91	28.86	1.08	1.26	1.22	1.22	1.26
175	6.54	6.38	6.52	6.68	0.30	0.47	27.56	36.75	27.95	1.08	1.26	1.21	1.21	1.26
200	6.55	6.40	6.54	6.70	0.30	0.54	27.01	36.61	27.14	1.09	1.25	1.21	1.21	1.25
225	6.57	6.42	6.56	6.72	0.30	0.56	26.48	36.46	26.39	1.10	1.25	1.21	1.20	1.25
250	6.59	6.43	6.57	6.73	0.30	0.65	25.95	36.32	25.71	1.12	1.25	1.20	1.20	1.25
275	6.61	6.45	6.60	6.76	0.31	0.70	25.45	36.16	25.09	1.13	1.25	1.20	1.20	1.24
300	6.62	6.46	6.61	6.77	0.31	0.78	24.94	35.98	24.51	1.14	1.25	1.20	1.19	1.24
325	6.64	6.48	6.63	6.79	0.31	0.83	24.45	35.77	23.97	1.15	1.25	1.19	1.19	1.24
350	6.66	6.49	6.65	6.81	0.31	0.89	23.96	35.52	23.45	1.17	1.24	1.19	1.18	1.23
375	6.67	6.51	6.67	6.83	0.32	0.95	23.48	35.23	22.97	1.18	1.24	1.18	1.18	1.23
400	6.69	6.53	6.69	6.85	0.32	0.99	23.01	34.91	22.50	1.19	1.24	1.18	1.17	1.23
425	6.71	6.55	6.71	6.87	0.33	1.07	22.56	34.56	22.06	1.21	1.24	1.17	1.17	1.22
450	6.73	6.56	6.73	6.89	0.33	1.13	22.11	34.19	21.64	1.22	1.24	1.17	1.16	1.22
500	6.77	6.60	6.78	6.94	0.34	1.22	21.26	33.41	20.87	1.26	1.23	1.16	1.15	1.21
525	6.80	6.62	6.80	6.97	0.34	1.26	20.86	33.00	20.50	1.27	1.23	1.15	1.15	1.21
550	6.82	6.64	6.82	6.99	0.35	1.31	20.47	32.60	20.16	1.29	1.23	1.15	1.14	1.20
575	6.84	6.66	6.85	7.02	0.36	1.38	20.10	32.21	19.83	1.30	1.22	1.14	1.14	1.20
600	6.87	6.68	6.88	7.05	0.37	1.43	19.75	31.81	19.52	1.32	1.22	1.13	1.13	1.19
650	6.92	6.73	6.93	7.10	0.38	1.57	19.11	31.08	18.94	1.35	1.21	1.12	1.12	1.18
675	6.94	6.75	6.96	7.13	0.39	1.62	18.82	30.73	18.69	1.36	1.20	1.11	1.11	1.17
700	6.97	6.77	6.99	7.16	0.39	1.68	18.55	30.41	18.44	1.38	1.19	1.10	1.10	1.17
725	7.00	6.79	7.02	7.19	0.40	1.75	18.30	30.10	18.22	1.39	1.19	1.09	1.10	1.16
750	7.02	6.81	7.04	7.22	0.40	1.84	18.07	29.83	18.01	1.40	1.18	1.08	1.09	1.15
800	7.07	6.86	7.11	7.28	0.42	1.98	17.67	29.34	17.65	1.42	1.16	1.07	1.08	1.14
825	7.11	6.89	7.14	7.31	0.43	2.02	17.51	29.13	17.49	1.43	1.15	1.06	1.07	1.13
850	7.13	6.91	7.17	7.35	0.44	2.11	17.36	28.92	17.35	1.44	1.14	1.05	1.07	1.12
875	7.16	6.94	7.20	7.38	0.44	2.17	17.24	28.76	17.22	1.44	1.13	1.05	1.07	1.11
900	7.19	6.96	7.23	7.41	0.45	2.25	17.14	28.62	17.12	1.45	1.12	1.05	1.06	1.10
950	7.24	7.00	7.30	7.47	0.47	2.45	17.00	28.39	16.96	1.45	1.10	1.06	1.07	1.09
975	7.27	7.03	7.33	7.50	0.48	2.51	16.96	28.31	16.90	1.46	1.08	1.07	1.07	1.08
1000	7.30	7.05	7.37	7.54	0.48	2.56	16.94	28.25	16.86	1.45	1.07	1.08	1.08	1.06
1025	7.33	7.08	7.40	7.58	0.50	2.66	16.96	28.20	16.83	1.45	1.07	1.09	1.08	1.06
1050	7.36	7.10	7.44	7.61	0.51	2.74	16.98	28.17	16.82	1.45	1.06	1.10	1.09	1.04
1100	7.43	7.15	7.51	7.69	0.54	2.95	17.10	28.14	16.83	1.44	1.06	1.12	1.11	1.03
1200	7.57	7.27	7.68	7.85	0.59	3.35	17.55	28.12	16.96	1.40	1.09	1.17	1.15	1.02
1300	7.74	7.42	7.89	8.05	0.63	3.75	18.23	27.94	17.16	1.35	1.15	1.22	1.19	1.06
1400	7.96	7.62	8.14	8.29	0.68	4.31	19.00	27.44	17.34	1.32	1.21	1.26	1.23	1.10
1500	8.24	7.87	8.44	8.60	0.72	4.96	19.68	26.60	17.45	1.31	1.26	1.29	1.27	1.14
1600	8.59	8.20	8.82	8.97	0.76	5.85	20.11	25.71	17.64	1.32	1.31	1.31	1.31	1.18

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

SCA-4-10+

100627

Page 1 of 3

Mini-Circuits®

RF/MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

SCA-4-10+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
5	6.40	6.21	6.38	6.63	0.42	1.86	24.97	32.87	23.69	1.09	1.46	1.39	1.49	1.59
10	6.34	6.19	6.30	6.50	0.30	1.27	29.24	37.33	26.93	1.06	1.30	1.25	1.32	1.39
15	6.33	6.19	6.29	6.46	0.26	0.92	31.87	39.90	29.37	1.05	1.24	1.21	1.25	1.31
20	6.32	6.19	6.27	6.43	0.24	0.73	33.35	41.19	31.22	1.05	1.22	1.19	1.22	1.28
25	6.31	6.19	6.26	6.42	0.23	0.58	34.12	41.75	32.68	1.05	1.21	1.18	1.20	1.26
30	6.31	6.19	6.26	6.42	0.23	0.49	34.51	41.97	33.78	1.05	1.20	1.17	1.19	1.24
35	6.32	6.19	6.27	6.42	0.23	0.44	34.67	42.02	34.61	1.05	1.19	1.16	1.18	1.23
40	6.32	6.20	6.27	6.42	0.22	0.40	34.68	41.95	35.26	1.05	1.19	1.16	1.17	1.22
45	6.33	6.20	6.28	6.42	0.22	0.35	34.59	41.84	35.74	1.05	1.19	1.16	1.17	1.22
50	6.33	6.20	6.28	6.43	0.22	0.33	34.45	41.72	36.05	1.05	1.18	1.15	1.16	1.21
75	6.36	6.23	6.31	6.45	0.22	0.35	33.46	41.00	35.60	1.07	1.19	1.15	1.15	1.20
100	6.39	6.25	6.34	6.47	0.22	0.36	32.41	40.36	33.96	1.09	1.20	1.15	1.16	1.19
125	6.40	6.26	6.36	6.50	0.23	0.40	31.40	39.83	32.39	1.10	1.19	1.16	1.16	1.19
150	6.42	6.28	6.38	6.51	0.23	0.43	30.48	39.36	31.01	1.11	1.18	1.16	1.16	1.20
175	6.43	6.29	6.39	6.53	0.24	0.48	29.63	38.90	29.83	1.11	1.19	1.15	1.15	1.21
200	6.45	6.30	6.41	6.55	0.24	0.57	28.84	38.48	28.79	1.12	1.20	1.15	1.15	1.21
225	6.46	6.32	6.43	6.57	0.25	0.62	28.10	38.08	27.87	1.13	1.19	1.15	1.15	1.21
250	6.47	6.33	6.44	6.58	0.25	0.64	27.39	37.64	27.04	1.13	1.19	1.15	1.16	1.20
275	6.49	6.35	6.46	6.60	0.25	0.72	26.73	37.23	26.29	1.14	1.20	1.15	1.16	1.20
300	6.50	6.36	6.47	6.61	0.26	0.75	26.09	36.78	25.60	1.15	1.20	1.15	1.15	1.20
325	6.52	6.37	6.49	6.64	0.27	0.82	25.48	36.31	24.96	1.16	1.20	1.15	1.15	1.20
350	6.53	6.38	6.50	6.65	0.26	0.89	24.89	35.84	24.36	1.18	1.20	1.15	1.15	1.21
375	6.55	6.40	6.52	6.67	0.27	0.96	24.33	35.35	23.79	1.20	1.21	1.15	1.15	1.21
400	6.56	6.41	6.54	6.69	0.27	0.99	23.78	34.85	23.25	1.21	1.21	1.15	1.15	1.20
425	6.57	6.43	6.56	6.71	0.28	1.05	23.26	34.33	22.74	1.22	1.21	1.15	1.15	1.20
450	6.59	6.44	6.57	6.72	0.28	1.13	22.76	33.83	22.26	1.23	1.21	1.14	1.15	1.20
500	6.63	6.47	6.61	6.76	0.29	1.25	21.82	32.84	21.37	1.26	1.21	1.14	1.14	1.20
525	6.65	6.49	6.63	6.79	0.30	1.30	21.39	32.36	20.97	1.28	1.21	1.13	1.14	1.20
550	6.66	6.50	6.65	6.80	0.30	1.34	20.96	31.89	20.57	1.29	1.21	1.12	1.13	1.20
575	6.69	6.52	6.68	6.83	0.31	1.37	20.57	31.44	20.20	1.31	1.20	1.12	1.12	1.19
600	6.71	6.54	6.70	6.86	0.32	1.46	20.19	31.00	19.85	1.33	1.20	1.11	1.12	1.18
650	6.75	6.58	6.75	6.91	0.33	1.56	19.51	30.22	19.21	1.36	1.19	1.10	1.11	1.17
675	6.77	6.59	6.77	6.93	0.34	1.63	19.20	29.86	18.93	1.37	1.17	1.09	1.10	1.17
700	6.79	6.61	6.80	6.96	0.35	1.65	18.91	29.53	18.66	1.39	1.17	1.08	1.09	1.16
725	6.82	6.63	6.83	6.99	0.35	1.71	18.65	29.23	18.41	1.40	1.17	1.07	1.08	1.15
750	6.84	6.65	6.85	7.01	0.36	1.73	18.41	28.95	18.18	1.42	1.16	1.07	1.07	1.14
800	6.88	6.69	6.90	7.06	0.38	1.85	18.00	28.47	17.77	1.44	1.13	1.05	1.06	1.13
825	6.91	6.71	6.93	7.10	0.39	1.88	17.83	28.26	17.60	1.45	1.13	1.05	1.05	1.12
850	6.93	6.73	6.96	7.12	0.39	1.93	17.68	28.08	17.45	1.46	1.12	1.04	1.05	1.12
875	6.95	6.75	6.98	7.15	0.40	2.00	17.54	27.93	17.31	1.46	1.11	1.04	1.04	1.11
900	6.97	6.76	7.01	7.17	0.41	2.03	17.44	27.80	17.20	1.46	1.10	1.05	1.05	1.10
950	7.02	6.80	7.06	7.23	0.43	2.12	17.29	27.60	17.02	1.47	1.08	1.07	1.06	1.08
975	7.04	6.82	7.09	7.26	0.44	2.22	17.25	27.52	16.95	1.47	1.07	1.08	1.06	1.07
1000	7.07	6.84	7.12	7.29	0.45	2.24	17.22	27.47	16.91	1.47	1.06	1.08	1.07	1.06
1025	7.10	6.86	7.15	7.32	0.46	2.27	17.22	27.45	16.88	1.47	1.05	1.10	1.08	1.05
1050	7.12	6.88	7.19	7.35	0.47	2.24	17.24	27.43	16.85	1.47	1.05	1.11	1.09	1.04
1100	7.17	6.91	7.25	7.41	0.50	2.51	17.34	27.42	16.85	1.46	1.05	1.14	1.11	1.02
1200	7.28	7.01	7.38	7.55	0.55	2.99	17.75	27.48	16.97	1.41	1.09	1.19	1.16	1.03
1300	7.42	7.12	7.56	7.72	0.60	3.60	18.35	27.37	17.15	1.37	1.16	1.24	1.20	1.07
1400	7.60	7.28	7.77	7.92	0.64	4.31	19.02	26.95	17.30	1.33	1.22	1.28	1.25	1.11
1500	7.83	7.50	8.02	8.18	0.68	5.16	19.54	26.17	17.39	1.31	1.28	1.31	1.29	1.16
1600	8.14	7.79	8.34	8.50	0.71	6.31	19.82	25.29	17.53	1.31	1.32	1.34	1.32	1.19

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

SCA-4-10+

100627

Page 2 of 3

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0066 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

SCA-4-10+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
5	6.48	6.28	6.46	6.68	0.39	0.54	27.68	34.34	30.89	1.04	1.40	1.34	1.36	1.42
10	6.49	6.30	6.47	6.68	0.38	0.24	28.26	35.31	31.25	1.03	1.38	1.32	1.33	1.39
15	6.51	6.32	6.48	6.69	0.37	0.16	28.25	35.48	31.36	1.03	1.37	1.32	1.33	1.38
20	6.51	6.32	6.48	6.69	0.37	0.12	28.13	35.47	31.37	1.03	1.38	1.32	1.32	1.38
25	6.51	6.32	6.48	6.69	0.36	0.11	28.02	35.41	31.33	1.03	1.38	1.32	1.32	1.38
30	6.52	6.33	6.49	6.69	0.36	0.14	27.91	35.34	31.25	1.04	1.38	1.32	1.32	1.38
35	6.53	6.33	6.49	6.70	0.37	0.18	27.81	35.28	31.14	1.04	1.39	1.32	1.33	1.38
40	6.54	6.34	6.50	6.71	0.36	0.22	27.71	35.22	31.00	1.04	1.39	1.32	1.33	1.38
45	6.54	6.35	6.51	6.72	0.37	0.25	27.63	35.17	30.85	1.04	1.39	1.33	1.33	1.38
50	6.55	6.36	6.52	6.72	0.37	0.28	27.55	35.13	30.67	1.04	1.39	1.33	1.33	1.38
75	6.57	6.39	6.55	6.76	0.37	0.38	27.16	34.94	29.72	1.03	1.37	1.33	1.33	1.38
100	6.59	6.41	6.57	6.79	0.38	0.41	26.77	34.82	28.75	1.03	1.35	1.31	1.31	1.38
125	6.62	6.42	6.59	6.81	0.39	0.51	26.41	34.76	27.83	1.03	1.35	1.29	1.29	1.36
150	6.65	6.44	6.62	6.82	0.38	0.71	26.06	34.75	26.99	1.04	1.36	1.28	1.28	1.35
175	6.66	6.46	6.64	6.84	0.38	0.86	25.67	34.78	26.23	1.05	1.35	1.28	1.28	1.33
200	6.68	6.49	6.67	6.86	0.37	0.93	25.29	34.84	25.55	1.06	1.33	1.29	1.28	1.32
225	6.70	6.51	6.68	6.88	0.38	0.97	24.90	34.88	24.92	1.08	1.33	1.28	1.27	1.31
250	6.72	6.52	6.70	6.90	0.38	1.09	24.49	34.91	24.34	1.09	1.34	1.27	1.26	1.31
275	6.74	6.54	6.72	6.92	0.39	1.25	24.08	34.92	23.80	1.11	1.32	1.25	1.24	1.31
300	6.75	6.56	6.74	6.94	0.38	1.37	23.65	34.90	23.29	1.12	1.31	1.25	1.23	1.30
325	6.78	6.58	6.77	6.96	0.39	1.46	23.24	34.88	22.83	1.14	1.31	1.24	1.23	1.29
350	6.79	6.59	6.78	6.98	0.39	1.56	22.82	34.83	22.38	1.15	1.31	1.24	1.23	1.28
375	6.82	6.62	6.81	7.01	0.39	1.69	22.41	34.73	21.96	1.16	1.30	1.23	1.22	1.27
400	6.83	6.63	6.83	7.03	0.39	1.78	22.00	34.61	21.57	1.17	1.29	1.22	1.21	1.26
425	6.86	6.66	6.85	7.05	0.39	1.86	21.61	34.43	21.19	1.19	1.28	1.21	1.20	1.26
450	6.88	6.68	6.88	7.07	0.39	1.96	21.22	34.22	20.84	1.21	1.28	1.20	1.19	1.25
500	6.93	6.73	6.93	7.13	0.40	2.18	20.48	33.75	20.20	1.24	1.27	1.19	1.18	1.24
525	6.96	6.75	6.96	7.16	0.41	2.31	20.14	33.47	19.90	1.26	1.26	1.18	1.17	1.23
550	6.98	6.77	6.98	7.18	0.41	2.38	19.80	33.17	19.61	1.27	1.25	1.17	1.16	1.22
575	7.01	6.80	7.02	7.21	0.42	2.49	19.49	32.86	19.35	1.29	1.25	1.16	1.15	1.22
600	7.04	6.82	7.04	7.24	0.42	2.57	19.19	32.54	19.10	1.30	1.24	1.15	1.14	1.21
650	7.10	6.88	7.10	7.30	0.42	2.76	18.64	31.91	18.63	1.33	1.22	1.13	1.13	1.19
675	7.13	6.90	7.13	7.33	0.43	2.87	18.40	31.62	18.42	1.35	1.22	1.13	1.12	1.19
700	7.16	6.93	7.16	7.36	0.43	2.98	18.17	31.32	18.22	1.36	1.21	1.12	1.12	1.18
725	7.19	6.96	7.20	7.40	0.44	3.11	17.96	31.04	18.04	1.37	1.20	1.11	1.11	1.17
750	7.22	6.98	7.22	7.43	0.45	3.22	17.76	30.80	17.86	1.38	1.19	1.10	1.10	1.16
800	7.28	7.04	7.30	7.49	0.46	3.47	17.44	30.33	17.56	1.40	1.17	1.08	1.09	1.15
825	7.32	7.06	7.33	7.53	0.46	3.57	17.31	30.13	17.43	1.41	1.16	1.07	1.08	1.14
850	7.35	7.09	7.36	7.56	0.47	3.69	17.18	29.97	17.31	1.41	1.15	1.06	1.08	1.14
875	7.38	7.13	7.40	7.60	0.48	3.79	17.09	29.81	17.21	1.42	1.14	1.06	1.07	1.13
900	7.41	7.15	7.43	7.63	0.48	3.93	17.01	29.69	17.12	1.42	1.13	1.05	1.07	1.12
950	7.48	7.21	7.51	7.70	0.50	4.19	16.91	29.46	16.99	1.43	1.11	1.05	1.06	1.10
975	7.52	7.24	7.55	7.74	0.51	4.28	16.90	29.38	16.95	1.43	1.10	1.05	1.06	1.09
1000	7.55	7.27	7.59	7.78	0.51	4.42	16.90	29.34	16.92	1.43	1.09	1.06	1.07	1.08
1025	7.59	7.29	7.63	7.82	0.53	4.60	16.92	29.30	16.91	1.43	1.08	1.07	1.07	1.08
1050	7.63	7.33	7.67	7.86	0.53	4.71	16.96	29.28	16.90	1.42	1.07	1.08	1.08	1.07
1100	7.71	7.40	7.76	7.95	0.56	4.98	17.10	29.26	16.93	1.42	1.07	1.10	1.09	1.05
1200	7.89	7.55	7.97	8.15	0.60	5.61	17.59	29.22	17.12	1.38	1.09	1.15	1.13	1.03
1300	8.10	7.74	8.20	8.38	0.64	6.14	18.35	28.99	17.41	1.34	1.14	1.19	1.17	1.05
1400	8.35	7.97	8.48	8.66	0.69	6.83	19.27	28.38	17.71	1.31	1.19	1.22	1.22	1.09
1500	8.67	8.27	8.82	9.00	0.73	7.62	20.20	27.44	18.00	1.31	1.25	1.26	1.26	1.13
1600	9.05	8.63	9.23	9.40	0.77	8.67	20.95	26.49	18.34	1.33	1.31	1.29	1.30	1.18

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

SCA-4-10+

100627

Page 3 of 3

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see

