

Surface Mount High Pass Filter

SCHF-17+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
1	98.96	99.88	101.49	0.00	0.00	0.00	0.00	0.00	0.00
10	43.99	43.96	43.80	0.08	0.09	0.10	0.08	0.08	0.10
40	0.17	0.19	0.20	20.03	20.19	20.53	20.01	20.17	20.48
100	0.13	0.14	0.15	26.02	27.29	28.57	25.99	27.18	28.44
200	0.16	0.18	0.21	22.19	21.18	20.44	22.15	21.14	20.39
300	0.16	0.23	0.27	19.70	18.12	16.67	19.59	18.08	16.60
400	0.24	0.29	0.36	16.53	15.94	14.75	16.46	15.91	14.70
500	0.31	0.37	0.44	14.32	14.23	13.40	14.32	14.26	13.42
600	0.36	0.43	0.50	13.15	12.94	12.26	13.15	13.01	12.29
700	0.39	0.48	0.56	12.22	11.83	11.25	12.23	11.89	11.27
800	0.48	0.59	0.69	11.49	10.95	10.49	11.50	11.00	10.53
900	0.58	0.72	0.83	10.93	10.27	9.91	10.96	10.30	9.95
1000	0.66	0.84	0.94	10.42	9.71	9.41	10.47	9.76	9.46
1100	0.72	0.91	1.01	9.99	9.28	9.01	10.04	9.35	9.06
1200	0.78	0.98	1.10	9.66	8.99	8.72	9.70	9.04	8.77
1300	0.86	1.08	1.20	9.45	8.87	8.59	9.51	8.93	8.67
1400	0.96	1.17	1.30	9.45	8.91	8.65	9.56	9.04	8.77
1500	1.66	1.83	1.93	8.96	8.44	8.19	9.05	8.59	8.36
1600	1.04	1.30	1.45	8.93	8.41	8.22	9.25	8.79	8.61
1700	1.16	1.42	1.56	8.98	8.44	8.31	9.65	9.16	9.03
1800	1.29	1.54	1.65	8.94	8.38	8.38	9.95	9.37	9.31
1900	1.37	1.63	1.75	9.07	8.49	8.62	10.14	9.52	9.61
2000	1.39	1.70	1.81	9.31	8.67	8.93	10.46	9.79	10.07
2100	1.53	1.88	2.00	9.63	8.93	9.32	10.96	10.25	10.69
2200	1.79	2.17	2.30	9.92	9.21	9.70	11.69	10.89	11.51
2300	2.14	2.53	2.65	10.18	9.57	10.13	12.33	11.47	12.16
2400	2.50	2.81	2.90	10.37	10.03	10.62	12.66	11.82	12.54
2500	2.66	2.86	2.93	10.70	10.71	11.35	12.41	11.89	12.65
2900	1.99	2.08	2.21	11.96	12.47	13.19	11.32	12.00	12.90
3000	1.89	1.99	2.16	11.14	11.86	12.47	10.75	11.68	12.49
3100	1.70	1.86	2.03	10.44	11.17	11.94	10.36	11.34	12.31
3200	1.75	1.95	2.11	9.89	10.73	11.47	10.06	11.23	12.17
3300	1.67	1.84	2.02	9.51	10.67	11.43	9.71	11.13	12.11
3400	1.78	1.94	2.12	9.32	10.70	11.57	9.55	11.18	12.27
3500	1.92	2.15	2.36	9.71	11.35	12.12	10.01	11.96	12.98
3600	2.14	2.42	2.57	10.19	12.07	12.78	10.48	12.72	13.64
3700	2.13	2.33	2.56	10.87	13.68	14.47	10.85	13.51	14.51
4000	2.52	2.93	3.20	24.89	25.37	23.76	15.93	21.64	22.51
4100	2.87	3.20	3.48	25.51	16.53	16.61	19.63	24.83	25.41
4600	3.57	4.09	4.33	6.95	6.70	7.01	11.49	11.25	12.12
4700	3.84	4.29	4.55	6.33	6.37	6.67	10.28	10.76	11.80
4800	4.22	4.61	4.82	5.89	6.20	6.52	9.66	10.81	12.14
4900	4.57	4.92	5.16	5.74	6.29	6.67	9.50	11.63	13.42
5000	4.80	5.11	5.41	5.82	6.63	7.02	9.98	13.54	15.93
5100	4.84	5.27	5.66	6.17	7.03	7.34	11.32	16.56	19.44
5200	5.11	5.75	6.30	6.64	7.05	7.19	14.61	20.18	18.66
5300	5.26	6.14	6.85	6.78	6.84	6.57	17.59	14.66	12.71
5400	5.71	6.88	7.72	6.54	6.00	5.66	15.67	10.44	9.08
5500	6.32	7.89	8.87	5.91	5.00	4.54	10.32	7.27	6.46
5600	7.58	9.36	10.56	4.58	3.72	3.50	6.90	5.14	4.84
5700	8.85	10.85	12.03	3.38	2.78	2.71	4.71	3.78	3.74
5800	10.40	12.36	13.62	2.44	2.18	2.16	3.33	2.93	3.04
5900	11.87	13.87	14.96	1.78	1.67	1.77	2.44	2.35	2.55
6000	13.52	15.26	16.31	1.36	1.38	1.49	1.85	1.92	2.23

REV. X2

SCHF-17+

101101

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

