

*Typical Performance Data*

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | RETURN<br>LOSS<br>(dB) |
|--------------------|---------------------------|------------------------|
| 5.00               | 0.51                      | 22.24                  |
| 6.38               | 0.51                      | 22.58                  |
| 7.75               | 0.52                      | 22.88                  |
| 9.13               | 0.53                      | 23.14                  |
| 10.50              | 0.54                      | 23.41                  |
| 11.88              | 0.55                      | 23.66                  |
| 13.25              | 0.56                      | 23.93                  |
| 14.63              | 0.57                      | 24.18                  |
| 16.00              | 0.58                      | 24.45                  |
| 17.38              | 0.59                      | 24.71                  |
| 18.75              | 0.60                      | 25.00                  |
| 20.13              | 0.61                      | 25.27                  |
| 21.50              | 0.61                      | 25.56                  |
| 22.88              | 0.63                      | 25.82                  |
| 24.25              | 0.63                      | 26.11                  |
| 25.63              | 0.64                      | 26.36                  |
| 27.00              | 0.65                      | 26.61                  |
| 28.38              | 0.66                      | 26.88                  |
| 29.75              | 0.67                      | 27.04                  |
| 31.13              | 0.68                      | 27.20                  |
| 32.50              | 0.69                      | 27.29                  |
| 33.88              | 0.69                      | 27.33                  |
| 35.25              | 0.71                      | 27.29                  |
| 36.63              | 0.71                      | 27.17                  |
| 38.00              | 0.72                      | 27.00                  |
| 39.38              | 0.73                      | 26.73                  |
| 40.75              | 0.75                      | 26.41                  |
| 42.13              | 0.75                      | 26.03                  |
| 43.50              | 0.76                      | 25.60                  |
| 44.88              | 0.78                      | 25.15                  |
| 46.25              | 0.79                      | 24.67                  |
| 47.63              | 0.80                      | 24.16                  |
| 49.00              | 0.81                      | 23.67                  |
| 50.38              | 0.82                      | 23.14                  |
| 51.75              | 0.84                      | 22.64                  |
| 53.13              | 0.86                      | 22.13                  |
| 54.50              | 0.86                      | 21.63                  |
| 55.88              | 0.88                      | 21.14                  |
| 57.25              | 0.90                      | 20.66                  |
| 58.63              | 0.91                      | 20.19                  |
| 60.00              | 0.93                      | 19.72                  |