

Surface Mount Low Pass Filter

SCLF-420

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
10	0.03	0.05	0.04	50.73	47.43	48.43	50.98	46.99	48.03
12	0.02	0.05	0.03	49.29	47.11	47.80	49.37	46.66	47.40
13	0.03	0.05	0.04	48.69	46.99	47.81	48.94	46.66	47.27
14	0.03	0.05	0.04	48.02	46.69	47.58	48.33	46.21	47.05
15	0.03	0.04	0.05	47.34	46.67	47.43	47.66	46.30	46.93
20	0.02	0.05	0.04	45.15	45.99	46.97	45.45	45.18	45.60
30	0.04	0.05	0.06	41.67	45.31	47.27	41.93	43.80	44.67
40	0.06	0.07	0.07	39.50	44.06	47.80	39.86	42.05	43.42
50	0.05	0.07	0.07	38.04	42.36	45.65	38.21	39.98	41.52
60	0.06	0.07	0.08	36.87	40.22	41.51	36.94	37.83	39.04
70	0.04	0.07	0.08	35.94	37.84	37.68	35.88	35.84	36.14
80	0.07	0.08	0.10	35.05	35.48	34.46	34.82	33.80	33.53
90	0.06	0.09	0.10	33.93	33.14	31.77	33.66	31.73	31.24
100	0.06	0.09	0.10	32.83	31.01	29.42	32.54	29.89	29.07
150	0.10	0.16	0.16	25.62	23.17	21.48	25.53	22.78	21.37
170	0.12	0.18	0.19	22.86	21.00	19.61	22.84	20.72	19.56
200	0.16	0.20	0.23	19.34	18.61	17.84	19.41	18.45	17.81
250	0.24	0.27	0.28	16.27	16.91	17.09	16.32	16.86	17.15
300	0.25	0.28	0.29	17.56	18.85	20.16	17.64	19.07	20.51
330	0.20	0.27	0.28	21.46	22.62	23.90	22.00	23.49	25.18
350	0.22	0.28	0.31	23.52	23.49	22.85	24.62	24.49	23.92
370	0.25	0.33	0.38	20.35	20.08	19.23	20.79	20.33	19.52
400	0.37	0.44	0.48	15.78	15.91	15.69	15.85	15.79	15.64
420	0.42	0.48	0.53	14.99	15.21	15.35	14.83	14.89	15.04
450	0.41	0.52	0.57	18.95	19.37	19.94	17.19	17.23	17.29
470	0.64	0.76	0.88	14.97	15.00	14.23	13.54	13.38	12.66
500	3.03	3.23	3.43	4.23	4.30	4.18	4.00	4.00	3.87
550	12.65	12.88	13.03	0.66	0.76	0.78	0.58	0.64	0.65
570	16.53	16.77	16.88	0.43	0.54	0.54	0.37	0.43	0.45
600	21.98	22.19	22.33	0.28	0.38	0.40	0.24	0.33	0.33
650	30.11	30.40	30.52	0.20	0.30	0.32	0.17	0.25	0.26
700	38.45	38.64	38.95	0.15	0.26	0.28	0.13	0.20	0.23
750	46.41	46.89	46.83	0.12	0.24	0.25	0.13	0.19	0.23
800	57.30	57.97	55.59	0.11	0.22	0.25	0.12	0.18	0.23
850	65.56	63.91	65.27	0.09	0.21	0.24	0.10	0.18	0.23
900	64.35	60.99	63.57	0.08	0.20	0.24	0.11	0.19	0.23
950	61.20	59.99	61.30	0.09	0.19	0.25	0.10	0.19	0.24
1000	60.76	60.87	60.30	0.06	0.19	0.23	0.09	0.19	0.24
1100	62.03	61.78	62.85	0.06	0.20	0.24	0.10	0.19	0.25
1200	67.19	68.23	68.78	0.06	0.19	0.25	0.10	0.20	0.26
1300	73.23	73.72	75.69	0.07	0.21	0.27	0.11	0.20	0.29
1400	66.53	65.19	64.60	0.07	0.22	0.28	0.10	0.21	0.29
1500	59.99	60.37	58.06	0.08	0.21	0.29	0.09	0.21	0.29
1600	59.06	58.20	57.59	0.08	0.21	0.30	0.08	0.21	0.28
1700	56.17	55.50	55.08	0.08	0.23	0.29	0.08	0.22	0.29
1800	54.56	54.18	53.72	0.10	0.22	0.30	0.07	0.22	0.29
1900	53.10	53.70	52.71	0.10	0.23	0.31	0.08	0.21	0.28
2000	53.88	52.72	52.08	0.11	0.24	0.32	0.07	0.23	0.27
2100	51.16	50.51	50.40	0.12	0.24	0.33	0.07	0.22	0.26
2200	52.12	51.00	51.35	0.12	0.25	0.31	0.08	0.23	0.25
2300	50.18	49.84	48.99	0.11	0.24	0.31	0.08	0.25	0.25
2400	49.00	47.72	49.79	0.13	0.26	0.34	0.08	0.25	0.26
2500	48.33	49.93	47.99	0.12	0.25	0.32	0.06	0.24	0.23
2600	49.40	48.15	49.66	0.14	0.25	0.34	0.06	0.23	0.24

REV. X2

SCLF-420

101116

Page 1 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Surface Mount Low Pass Filter

SCLF-420

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
0.1	6.07	2.98	5.11
1	0.82	1.90	0.96
10	1.14	1.07	1.17
20	1.27	1.32	1.39
30	1.19	1.23	1.22
40	1.34	1.22	1.28
50	1.28	1.24	1.22
60	1.27	1.23	1.17
70	1.26	1.33	1.37
80	1.20	1.22	1.23
90	1.36	1.21	1.25
100	1.28	1.35	1.31
110	1.30	1.39	1.32
120	1.24	1.28	1.28
130	1.40	1.28	1.41
140	1.25	1.34	1.19
150	1.34	1.29	1.34
160	1.45	1.24	1.26
170	1.34	1.39	1.37
180	1.39	1.43	1.37
190	1.36	1.41	1.33
200	1.34	1.24	1.31
210	1.51	1.35	1.40
220	1.41	1.44	1.27
230	1.26	1.32	1.39
240	1.47	1.34	1.36
250	1.40	1.28	1.41
260	1.47	1.52	1.44
270	1.71	1.60	1.57
280	1.57	1.49	1.47
290	1.59	1.60	1.61
300	1.59	1.48	1.64
310	1.70	1.66	1.76
320	1.76	1.72	1.78
330	1.75	1.65	1.77
340	1.88	1.76	1.73
350	1.85	1.89	1.88
360	1.88	1.96	1.83
370	1.99	2.00	1.96
380	2.14	2.02	2.17
390	2.01	2.13	2.05
400	2.28	2.35	2.22
410	2.19	2.17	2.28
420	2.43	2.35	2.42
430	2.50	2.54	2.57
440	2.78	2.80	2.91
450	3.16	3.22	3.28
460	3.46	3.52	3.55
470	3.96	3.93	3.95
480	4.28	4.33	4.37
490	4.32	4.34	4.34
500	4.18	4.21	4.14
600	0.77	0.74	0.82
700	0.12	0.16	0.47
800	2.93	2.83	2.65

REV. X2

SCLF-420

101116

Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

