

RF Transformer

TRS1-ED13381/1

Typical Performance Data

FREQUENCY MHz	INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	OUTPUT RETURN LOSS (dB)
50.0	0.18	40.67	40.14
60.0	0.19	40.10	39.35
70.0	0.19	39.74	38.47
80.0	0.20	39.29	37.75
90.0	0.20	38.82	37.07
100.0	0.20	38.31	36.50
150.0	0.22	36.37	34.16
200.0	0.22	34.96	32.40
250.0	0.24	34.03	31.22
300.0	0.25	32.97	30.03
350.0	0.26	32.10	29.14
400.0	0.27	31.47	28.42
450.0	0.28	30.60	27.61
500.0	0.29	30.18	27.15
550.0	0.30	29.37	26.53
600.0	0.31	28.78	26.10
650.0	0.32	28.11	25.64
700.0	0.34	27.44	25.18
750.0	0.35	26.79	24.77
800.0	0.36	25.99	24.28
850.0	0.38	25.36	23.95
900.0	0.39	24.56	23.30
950.0	0.41	23.93	22.95
1000.0	0.42	23.18	22.33



P.O. Box 350188, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. X1
TRS1-ED13381/1
10/14/2009
Page 1 of 1