

Typical Performance Data

FREQ.	ATTENUATION	VSWR
(MHz)	(dB)	(:1)
10	8.96	1.12
20	8.96	1.12
50	8.97	1.12
100	8.98	1.12
200	8.99	1.12
300	9.00	1.12
400	9.01	1.12
500	9.02	1.12
600	9.03	1.12
700	9.04	1.12
800	9.04	1.12
900	9.05	1.13
1000	9.06	1.13
1100	9.07	1.13
1200	9.07	1.13
1300	9.08	1.13
1400	9.09	1.13
1500	9.10	1.13
1600	9.10	1.14
1700	9.11	1.14
1800	9.12	1.14
1900	9.13	1.14
2000	9.13	1.14
2100	9.14	1.15
2200	9.15	1.15
2300	9.16	1.15
2400	9.16	1.15
2500	9.17	1.15
2600	9.18	1.15
2700	9.19	1.15
2800	9.20	1.15
2900	9.20	1.15
3000	9.21	1.15
3100	9.22	1.15
3200	9.22	1.16
3300	9.23	1.15
3400	9.24	1.15
3500	9.25	1.15
3600	9.26	1.15
3700	9.26	1.15
3800	9.27	1.15
3900	9.28	1.15
4000	9.29	1.15
4100	9.30	1.15
4200	9.31	1.15
4300	9.32	1.15
4400	9.33	1.15
4500	9.33	1.15
4600	9.34	1.15
4700	9.35	1.15
4800	9.36	1.15
4900	9.37	1.15
5000	9.38	1.15
5100	9.39	1.15
5200	9.40	1.15
5300	9.41	1.16
5400	9.42	1.16
5500	9.43	1.16
5800	9.46	1.18
6000	9.48	1.18