

Coaxial High Pass Filter

VHF-1200+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
1	117.74	104.60	114.38	0.00	0.01	0.00	0.00	0.01	0.00
50	72.98	59.82	69.64	0.01	0.00	0.00	0.01	0.00	0.01
100	88.13	70.14	70.06	0.00	0.00	0.02	0.01	0.00	0.01
300	71.68	70.35	69.76	0.01	0.06	0.07	0.01	0.02	0.02
510	78.27	80.18	98.65	0.08	0.13	0.16	0.07	0.11	0.14
690	58.53	57.55	56.78	0.17	0.25	0.30	0.15	0.24	0.27
750	49.71	49.00	48.30	0.22	0.31	0.35	0.19	0.28	0.32
780	45.65	44.95	44.42	0.25	0.34	0.40	0.22	0.30	0.34
825	39.85	39.23	38.67	0.31	0.42	0.47	0.27	0.35	0.40
865	34.91	34.30	33.72	0.34	0.46	0.53	0.30	0.40	0.45
905	30.24	29.62	29.04	0.41	0.53	0.64	0.36	0.45	0.55
910	29.65	29.02	28.45	0.41	0.54	0.65	0.38	0.48	0.57
940	26.17	25.59	24.99	0.51	0.64	0.76	0.40	0.55	0.63
995	20.02	19.45	18.84	0.74	0.90	1.09	0.62	0.77	0.92
1040	15.05	14.53	13.96	1.04	1.29	1.55	0.83	1.05	1.24
1090	9.83	9.40	8.92	1.85	2.28	2.73	1.54	1.88	2.22
1150	4.76	4.57	4.39	4.49	5.40	6.25	3.80	4.44	5.07
1180	3.10	3.08	3.06	6.94	8.13	9.22	5.85	6.65	7.37
1190	2.73	2.73	2.73	7.95	9.26	10.37	6.66	7.48	8.21
1200	2.36	2.40	2.44	9.00	10.37	11.51	7.48	8.31	9.02
1210	2.07	2.16	2.22	10.12	11.50	12.66	8.37	9.19	9.88
1220	1.87	1.98	2.06	11.16	12.55	13.67	9.23	9.98	10.63
1280	1.18	1.35	1.46	15.20	15.73	16.25	13.02	13.44	13.94
1300	1.07	1.24	1.37	15.36	15.73	16.16	13.69	14.07	14.56
1320	1.00	1.15	1.26	15.32	15.63	16.01	14.12	14.49	15.03
1340	0.92	1.08	1.20	15.28	15.58	15.95	14.51	14.97	15.52
1380	0.83	0.97	1.07	15.46	15.77	16.11	15.32	15.87	16.48
1410	0.76	0.90	1.02	15.96	16.27	16.54	16.03	16.66	17.22
1590	0.53	0.66	0.75	18.33	18.31	18.14	19.23	19.56	19.76
2000	0.39	0.51	0.59	17.22	17.22	17.33	17.13	17.11	17.21
2500	0.23	0.34	0.44	23.78	25.05	26.81	23.17	23.31	23.34
3200	0.32	0.46	0.57	14.88	15.01	14.72	14.66	14.69	14.35
3500	0.48	0.63	0.75	11.51	11.60	11.60	11.52	11.44	11.37
4000	0.88	1.04	1.17	8.07	8.15	8.25	8.03	8.04	8.05
4300	1.19	1.37	1.51	6.76	6.79	6.86	6.73	6.71	6.69
4600	1.49	1.72	1.91	5.81	5.73	5.78	5.76	5.67	5.64
5000	1.91	2.21	2.41	4.82	4.69	4.72	4.75	4.67	4.64
5500	2.57	2.82	3.05	3.71	3.79	3.88	3.65	3.74	3.82
6000	3.24	3.45	3.65	2.96	3.13	3.30	2.93	3.08	3.24
6500	3.92	4.03	4.23	2.43	2.67	2.86	2.38	2.62	2.81
7000	4.38	4.66	4.96	2.19	2.31	2.39	2.11	2.26	2.40
7500	4.94	5.44	5.96	1.94	1.96	1.94	1.84	1.88	1.96
8030	8.43	9.66	7.36	2.12	4.13	7.33	1.32	1.78	2.81
9000	11.16	12.58	10.85	0.99	1.58	2.58	1.89	2.94	4.70

REV. X1
VHF-1200+
080723
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

