

Coaxial High Pass Filter

VHF-3800

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS @ +25° C (dB)	INPUT RETURN LOSS @ +25° C (dB)	OUTPUT RETURNLOSS @ +25° C (dB)
40	59.29	0.00	0.01
50	60.64	0.02	0.02
100	50.99	0.01	0.01
200	45.91	0.01	0.02
500	38.35	0.01	0.04
1000	33.89	0.06	0.07
1500	33.98	0.13	0.13
2000	43.63	0.21	0.20
2500	34.18	0.27	0.36
3000	30.77	0.47	0.55
3100	34.40	0.51	0.58
3200	37.60	0.62	0.71
3400	18.33	0.96	1.11
3500	12.86	1.41	1.51
3550	10.69	1.77	1.97
3800	2.87	7.86	8.10
3950	1.44	16.11	16.76
4000	1.24	20.46	21.77
4250	0.87	24.22	25.58
4500	0.76	24.61	27.42
5000	0.65	21.19	21.86
5500	0.69	15.13	15.38
6000	0.70	13.44	13.43
6500	0.72	13.55	13.31
7000	0.75	15.71	14.54
7500	0.60	19.23	18.91
8000	0.52	25.08	27.46
8500	0.55	20.69	21.11
9000	0.69	15.00	14.94
9500	0.88	11.74	11.61
10000	1.15	9.61	9.57
10500	1.42	8.47	8.24
11000	1.80	8.52	7.47
11330	2.72	11.16	6.61
11500	3.91	19.59	6.08
12000	3.59	13.57	10.91
12500	5.71	5.24	4.15
13000	2.97	7.50	5.73
13500	2.13	17.50	8.86
14000	3.22	8.77	6.35
14500	6.95	3.14	2.54

REV. X1
VHF-3800
071011
Page 1 of 1



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

