

Coaxial High Pass Filter

VHF-8400

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS @ +25° C (dB)	INPUT RETURN LOSS @ +25° C (dB)	OUTPUT RETURNLOSS @ +25° C (dB)
38	59.86	0.08	0.01
50	58.86	0.01	0.03
290	46.41	0.03	0.01
500	41.63	0.03	0.04
1000	35.89	0.03	0.04
1500	32.69	0.07	0.05
2000	30.76	0.13	0.09
2500	29.68	0.15	0.13
3000	29.37	0.16	0.17
3500	29.92	0.24	0.19
4000	31.45	0.26	0.22
4500	34.99	0.25	0.26
5000	46.58	0.25	0.22
5700	32.89	0.38	0.32
6000	28.58	0.43	0.32
6500	23.87	0.58	0.39
7500	27.70	0.99	0.72
8020	9.25	2.83	2.32
8400	2.32	10.31	9.35
8600	1.43	15.25	14.22
9000	0.97	18.26	18.80
9500	0.86	15.18	15.68
10000	0.89	13.06	13.30
10500	0.84	12.94	13.15
11000	0.80	14.48	14.63
11500	0.66	19.01	18.03
12000	0.62	28.36	21.73
12500	0.72	17.03	16.06
13000	1.12	10.91	10.70
13500	1.75	7.12	7.23
14000	2.56	4.90	4.92
14500	3.32	3.73	3.92
15000	3.92	3.02	3.14
15500	4.20	2.80	2.84
16000	4.17	2.93	2.95
16500	3.68	3.46	3.48
17000	2.83	4.87	4.85
17500	1.73	8.35	8.38
18000	1.17	23.58	18.38
18500	1.96	9.50	8.51
19300	5.31	3.12	2.82

REV. X1
VHF-8400
071011
Page 1 of 1



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

