

Coaxial Low Pass Filter

VLF-1200+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.06	0.07	0.08	47.31	44.57	42.43	44.97	41.64	39.81
100	0.07	0.10	0.11	40.05	41.64	41.71	39.18	38.58	38.13
200	0.07	0.11	0.14	36.86	34.62	33.30	33.56	32.13	31.40
500	0.19	0.24	0.29	27.20	25.90	24.91	24.92	23.83	22.84
1000	0.38	0.49	0.58	25.64	25.80	25.93	24.78	24.55	24.25
1200	0.53	0.69	0.82	33.17	30.61	28.65	29.57	27.65	25.91
1250	0.61	0.81	0.94	25.62	24.11	22.91	24.42	22.92	21.65
1300	0.72	0.93	1.11	21.05	19.98	19.20	19.89	18.80	17.86
1315	0.77	0.99	1.17	19.80	18.87	18.16	18.71	17.75	16.86
1350	0.89	1.14	1.36	17.39	16.74	16.18	16.45	15.63	14.86
1400	1.14	1.45	1.72	14.57	14.21	13.88	13.46	12.84	12.18
1450	1.56	1.95	2.32	12.22	12.10	11.93	10.82	10.29	9.73
1500	2.27	2.81	3.35	9.98	9.96	9.90	8.27	7.79	7.30
1505	2.33	2.92	3.48	9.73	9.72	9.66	8.03	7.56	7.08
1530	2.92	3.63	4.35	8.52	8.52	8.44	6.74	6.29	5.87
1560	3.96	4.92	5.83	7.02	6.98	6.90	5.24	4.86	4.54
1600	6.11	7.44	8.69	5.03	5.02	4.96	3.51	3.33	3.18
1630	8.43	10.04	11.51	3.79	3.85	3.88	2.56	2.52	2.51
1675	12.91	14.77	16.41	2.54	2.69	2.78	1.73	1.86	1.97
1700	15.70	17.61	19.28	2.09	2.27	2.40	1.49	1.68	1.82
1720	18.01	19.91	21.57	1.83	2.02	2.14	1.38	1.57	1.74
1780	24.40	26.01	27.27	1.33	1.52	1.66	1.16	1.38	1.57
1800	26.12	27.51	28.57	1.24	1.43	1.56	1.11	1.35	1.54
1830	28.11	29.16	29.88	1.09	1.28	1.42	1.08	1.31	1.49
1865	30.99	31.12	31.23	0.93	1.09	1.27	0.93	1.11	1.31
2000	30.51	30.80	31.08	0.74	0.91	1.03	0.88	1.07	1.24
2350	40.32	41.76	43.25	0.46	0.66	0.81	0.53	0.68	0.77
2495	57.72	54.94	52.03	0.42	0.62	0.77	0.43	0.55	0.62
3000	37.13	37.20	37.16	0.37	0.55	0.66	0.25	0.36	0.43
3500	37.08	37.28	37.38	0.28	0.45	0.55	0.18	0.29	0.36
4000	37.70	37.86	38.01	0.21	0.38	0.47	0.14	0.26	0.34
4500	37.47	37.66	37.77	0.19	0.35	0.47	0.12	0.26	0.38
5000	37.60	37.80	38.09	0.18	0.38	0.50	0.13	0.28	0.42
5610	48.45	51.65	51.68	0.14	0.35	0.54	0.10	0.28	0.46
5780	43.02	39.65	37.25	0.15	0.39	0.59	0.10	0.31	0.49
5940	32.05	30.02	28.34	0.18	0.43	0.66	0.13	0.35	0.55
6120	22.86	20.87	19.08	0.34	0.69	1.03	0.27	0.56	0.90
6200	18.63	16.43	14.44	0.54	1.05	1.72	0.43	0.87	1.46
6330	10.59	8.53	8.05	2.19	4.46	5.63	1.88	3.78	4.82
6490	7.91	9.97	11.56	2.83	1.88	1.60	2.51	1.70	1.45
7000	15.60	15.93	16.18	0.27	0.54	0.76	0.27	0.48	0.69

REV. X1
VLF-1200+
080720
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

