

Coaxial Low Pass Filter

VLF-2750+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.06	0.08	0.07	44.14	38.02	34.78	44.89	38.48	35.07
200	0.10	0.13	0.14	35.82	39.27	38.86	34.96	38.30	38.59
500	0.12	0.18	0.21	44.67	39.75	33.22	36.88	34.25	30.76
1000	0.20	0.28	0.32	26.73	26.24	26.24	24.71	24.37	24.04
1500	0.31	0.41	0.48	19.61	19.39	19.42	19.56	19.21	19.05
2000	0.42	0.54	0.63	17.07	17.31	17.53	17.35	17.39	17.41
2500	0.52	0.66	0.77	19.63	20.57	21.28	18.93	20.01	20.77
2700	0.58	0.74	0.88	23.33	23.02	22.76	20.97	21.38	21.71
2750	0.61	0.79	0.93	23.55	22.68	22.09	21.03	21.15	21.28
2900	0.76	0.96	1.14	19.50	18.62	17.90	18.32	18.10	17.85
3150	1.47	1.83	2.15	10.42	9.70	9.29	10.66	10.14	9.81
3260	2.43	2.92	3.39	6.79	6.37	6.09	7.16	6.85	6.59
3370	4.29	4.97	5.63	3.98	3.83	3.72	4.35	4.26	4.13
3540	9.26	10.21	11.14	1.63	1.71	1.79	1.96	2.05	2.09
3660	14.08	15.18	16.23	1.05	1.18	1.30	1.29	1.43	1.52
3775	19.25	20.54	21.77	0.74	0.91	1.04	0.96	1.13	1.26
3850	23.03	24.45	25.81	0.68	0.84	0.97	0.84	1.02	1.16
3900	25.76	27.28	28.74	0.68	0.83	0.96	0.84	1.01	1.15
3950	28.62	30.26	31.85	0.58	0.74	0.88	0.76	0.95	1.11
4000	31.81	33.61	35.34	0.60	0.75	0.88	0.74	0.93	1.09
4070	36.87	38.96	41.01	0.57	0.74	0.85	0.73	0.93	1.09
4150	43.18	45.33	46.81	0.57	0.72	0.84	0.74	0.94	1.16
4200	49.82	53.15	56.52	0.46	0.63	0.76	0.68	0.87	1.06
4700	45.73	44.52	43.70	0.39	0.55	0.66	0.69	0.91	1.11
4900	40.77	40.27	40.02	0.31	0.48	0.58	0.65	0.86	1.05
5150	39.34	39.36	39.34	0.28	0.43	0.55	0.62	0.80	0.95
6000	56.41	55.34	52.90	0.31	0.38	0.54	0.43	0.60	0.71
6800	32.77	32.46	32.16	0.42	0.37	0.58	0.25	0.47	0.64
7500	27.00	26.91	26.86	0.23	0.37	0.57	0.20	0.44	0.66
8400	22.70	22.87	23.00	0.22	0.37	0.51	0.23	0.45	0.69
9900	18.86	18.62	18.58	0.08	0.58	0.78	0.32	0.53	0.67
11000	16.78	16.74	16.58	0.34	0.55	0.71	0.35	0.61	0.77
12100	14.41	14.49	14.51	0.38	0.65	0.89	0.33	0.52	0.69
13000	12.55	12.14	11.98	0.51	0.94	1.41	0.53	0.82	1.09
14000	11.58	11.98	12.17	1.27	1.44	1.80	0.91	1.15	1.43
15200	9.32	9.98	10.83	1.93	1.77	1.76	1.91	1.93	2.15
16300	14.72	15.51	16.12	0.63	0.91	1.15	0.73	0.90	1.08
17400	19.48	19.98	20.33	0.59	0.86	1.47	0.38	0.76	0.89
18500	21.76	19.66	19.77	5.81	3.65	2.51	0.25	0.67	1.00
19400	18.32	18.56	19.10	0.63	1.09	1.48	0.46	0.94	1.44
20000	16.39	16.35	16.27	1.07	1.90	2.88	0.98	1.69	2.66

REV. X1
VLF-2750+
080720
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

