

Coaxial Low Pass Filter

VLF-6700+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.02	0.03	0.06	48.70	43.66	40.77	48.47	42.65	40.18
100	0.02	0.04	0.05	44.58	41.06	38.79	46.25	41.11	38.39
200	0.05	0.06	0.09	38.68	38.86	39.29	39.06	39.50	40.39
300	0.04	0.07	0.09	35.69	37.07	38.24	35.27	37.23	41.54
400	0.05	0.09	0.12	34.32	35.94	37.38	34.92	36.82	41.93
500	0.07	0.10	0.14	32.16	33.79	36.00	33.11	35.29	39.50
600	0.08	0.12	0.16	31.97	33.46	36.15	32.41	34.68	38.89
700	0.10	0.13	0.18	31.32	32.65	35.02	31.77	33.97	37.86
800	0.10	0.13	0.18	31.51	32.73	34.81	32.23	34.35	38.28
900	0.09	0.15	0.21	31.65	32.84	34.82	32.04	33.75	37.27
1000	0.10	0.17	0.21	31.02	32.48	34.20	32.60	34.61	38.43
1100	0.12	0.18	0.23	30.57	32.23	33.81	32.32	34.67	38.01
1200	0.13	0.19	0.24	30.93	32.45	33.65	32.82	35.42	38.37
1300	0.13	0.18	0.25	31.54	32.89	33.93	33.27	35.79	38.29
1400	0.12	0.19	0.25	31.75	32.92	33.93	33.86	36.35	38.78
1500	0.13	0.19	0.26	32.04	33.19	34.29	34.63	37.40	40.44
1600	0.11	0.19	0.26	32.29	33.33	34.13	35.64	38.65	42.08
1700	0.13	0.20	0.28	32.99	33.89	34.14	35.60	38.46	41.49
1800	0.13	0.21	0.29	32.85	33.46	33.47	35.32	37.28	40.24
1900	0.12	0.20	0.28	32.91	32.64	32.54	35.87	36.42	39.62
2000	0.13	0.22	0.30	32.81	31.85	31.79	35.38	34.69	37.57
2100	0.14	0.24	0.31	32.56	31.04	31.06	33.88	32.70	34.88
2200	0.14	0.22	0.30	31.96	30.22	30.30	32.25	31.08	32.73
2300	0.13	0.23	0.31	30.19	29.08	29.22	30.02	29.47	30.72
2400	0.14	0.24	0.33	28.76	28.04	28.23	28.57	28.37	29.32
2500	0.15	0.25	0.35	27.97	27.22	27.33	27.54	27.23	27.85
2600	0.16	0.25	0.34	27.10	26.32	26.37	26.68	26.18	26.63
2700	0.17	0.26	0.36	26.48	25.67	25.79	26.17	25.54	25.95
2800	0.16	0.27	0.38	25.55	24.81	24.93	25.37	24.69	24.95
2900	0.16	0.28	0.38	24.75	24.09	24.21	24.78	24.12	24.22
3000	0.18	0.29	0.41	24.04	23.52	23.60	23.80	23.23	23.28
3500	0.22	0.35	0.48	21.94	21.86	22.05	21.64	21.22	20.95
4000	0.23	0.37	0.53	20.81	20.75	20.66	20.43	20.11	19.47
4500	0.24	0.42	0.59	21.01	20.31	19.01	20.32	19.60	18.28
5000	0.28	0.46	0.66	21.18	20.12	18.31	20.33	19.46	18.24
5500	0.32	0.52	0.71	20.12	19.86	18.64	19.88	19.73	19.37
6000	0.38	0.59	0.79	19.73	20.81	21.23	19.88	21.20	22.67
6700	0.51	0.75	1.01	25.94	26.16	25.02	30.47	32.03	30.95
7000	0.67	0.97	1.28	19.98	18.50	16.70	21.20	19.84	18.53
7600	2.22	2.77	3.39	6.69	6.35	5.89	6.86	6.52	6.18
8000	5.71	6.63	7.57	2.55	2.62	2.70	2.71	2.62	2.52
9000	23.47	25.20	26.82	0.56	0.91	1.38	0.53	0.73	0.90
10000	39.31	39.24	39.46	0.34	0.64	0.99	0.27	0.54	0.84
11000	42.20	43.18	44.46	0.23	0.51	0.76	0.12	0.36	0.65
12000	44.96	43.65	42.57	0.11	0.37	0.58	0.14	0.36	0.57
13000	34.09	34.52	34.56	0.04	0.33	0.56	0.18	0.39	0.52
14000	30.93	30.91	30.89	0.08	0.38	0.84	0.15	0.33	0.44
15000	29.65	29.24	28.98	0.00	0.54	1.26	0.11	0.29	0.43
16000	24.79	24.71	24.61	0.54	1.26	2.35	0.07	0.31	0.54
17000	28.00	27.45	27.09	0.83	1.08	1.60	0.03	0.33	0.66
18000	23.48	23.68	23.96	0.27	0.73	1.30	0.15	0.51	0.89
19000	22.37	23.02	23.78	0.38	0.82	1.14	0.18	0.55	0.91
19980	23.33	23.47	23.75	0.44	1.01	1.55	0.15	0.55	1.06
20000	23.49	23.58	23.83	0.44	1.02	1.58	0.16	0.59	1.09

REV. X2
VLF-6700+
110926
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

