

Waveguide WR12 UG387/U to 1.0mm-F

WR12-10+

Typical Performance Data (+25 °C)

FREQ.	INSERTION LOSS	1.0mm-FEMALE VSWR
(GHz)	(dB)	(:1)
60	-0.45	1.10
61	-0.46	1.08
62	-0.46	1.09
63	-0.43	1.08
64	-0.44	1.09
65	-0.45	1.11
66	-0.46	1.11
67	-0.47	1.12
68	-0.48	1.13
69	-0.48	1.14
70	-0.49	1.14
71	-0.49	1.11
72	-0.47	1.09
73	-0.47	1.07
74	-0.49	1.09
75	-0.49	1.10
76	-0.51	1.15
77	-0.52	1.20
78	-0.52	1.27
79	-0.55	1.31
80	-0.60	1.36
81	-0.61	1.38
82	-0.64	1.39
83	-0.66	1.38
84	-0.67	1.38
85	-0.65	1.35
86	-0.65	1.33
87	-0.65	1.28
88	-0.65	1.23
89	-0.64	1.20
90	-0.63	1.17



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS