

Fixed Attenuator

WR19-ATT-3+

Typical Performance Data (+25°C)

| FREQ. | ATTENUATION | WR19 INPUT VSWR | WR19 OUTPUT VSWR |
|-------|-------------|-----------------|------------------|
| (GHz) | (dB) | (:1) | (:1) |
| 40.0 | 3.44 | 1.04 | 1.05 |
| 40.5 | 3.35 | 1.04 | 1.04 |
| 41.0 | 3.34 | 1.04 | 1.04 |
| 41.5 | 3.35 | 1.03 | 1.04 |
| 42.0 | 3.37 | 1.05 | 1.07 |
| 42.5 | 3.32 | 1.04 | 1.06 |
| 43.0 | 3.28 | 1.04 | 1.04 |
| 43.5 | 3.28 | 1.07 | 1.05 |
| 44.0 | 3.29 | 1.04 | 1.04 |
| 44.5 | 3.31 | 1.06 | 1.07 |
| 45.0 | 3.32 | 1.08 | 1.08 |
| 45.5 | 3.26 | 1.04 | 1.05 |
| 46.0 | 3.25 | 1.10 | 1.09 |
| 46.5 | 3.27 | 1.10 | 1.10 |
| 47.0 | 3.30 | 1.06 | 1.04 |
| 47.5 | 3.33 | 1.10 | 1.09 |
| 48.0 | 3.31 | 1.11 | 1.10 |
| 48.5 | 3.27 | 1.05 | 1.04 |
| 49.0 | 3.29 | 1.12 | 1.12 |
| 49.5 | 3.32 | 1.13 | 1.13 |
| 50.0 | 3.34 | 1.05 | 1.08 |
| 50.5 | 3.38 | 1.12 | 1.15 |
| 51.0 | 3.37 | 1.14 | 1.16 |
| 51.5 | 3.34 | 1.05 | 1.10 |
| 52.0 | 3.37 | 1.15 | 1.14 |
| 52.5 | 3.39 | 1.16 | 1.15 |
| 53.0 | 3.41 | 1.07 | 1.05 |
| 53.5 | 3.45 | 1.12 | 1.12 |
| 54.0 | 3.45 | 1.15 | 1.15 |
| 54.5 | 3.43 | 1.09 | 1.07 |
| 55.0 | 3.45 | 1.12 | 1.11 |
| 55.5 | 3.49 | 1.18 | 1.18 |
| 56.0 | 3.52 | 1.12 | 1.14 |
| 56.5 | 3.55 | 1.06 | 1.10 |
| 57.0 | 3.59 | 1.18 | 1.20 |
| 57.5 | 3.58 | 1.15 | 1.18 |
| 58.0 | 3.58 | 1.06 | 1.11 |
| 58.5 | 3.63 | 1.18 | 1.18 |
| 59.0 | 3.67 | 1.17 | 1.18 |
| 59.5 | 3.68 | 1.08 | 1.08 |
| 60.0 | 3.71 | 1.12 | 1.17 |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
WR19-ATT-3+
2/18/2026
Page 1 of 1