

Fixed Attenuator**WR28-ATT-10+***Typical Performance Data (+25°C)*

FREQ.	ATTENUATION	WR28 INPUT VSWR	WR28 OUTPUT VSWR
(GHz)	(dB)	(:1)	(:1)
26.5	9.68	1.10	1.10
27.0	9.66	1.11	1.09
27.5	9.67	1.11	1.08
28.0	9.69	1.10	1.07
28.5	9.71	1.09	1.08
29.0	9.68	1.07	1.09
29.5	9.78	1.08	1.10
30.0	9.84	1.08	1.09
30.5	9.91	1.08	1.07
31.0	9.98	1.08	1.07
31.5	10.06	1.08	1.06
32.0	10.13	1.07	1.05
32.5	10.18	1.06	1.06
33.0	10.26	1.06	1.07
33.5	10.38	1.06	1.08
34.0	10.49	1.06	1.08
34.5	10.60	1.05	1.08
35.0	10.70	1.05	1.08
35.5	10.80	1.06	1.08
36.0	10.88	1.07	1.06
36.5	10.94	1.07	1.06
37.0	11.07	1.07	1.06
37.5	11.21	1.07	1.06
38.0	11.34	1.07	1.07
38.5	11.47	1.06	1.07
39.0	11.58	1.05	1.07
39.5	11.68	1.04	1.07
40.0	11.77	1.05	1.08



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS