

Fixed Attenuator**WR28-ATT-3+***Typical Performance Data (+25°C)*

FREQ.	ATTENUATION	WR28 INPUT VSWR	WR28 OUTPUT VSWR
(GHz)	(dB)	(:1)	(:1)
26.5	3.4	1.1	1.1
27	3.4	1.0	1.1
27.5	3.4	1.1	1.1
28	3.4	1.0	1.0
28.5	3.3	1.0	1.0
29	3.3	1.1	1.0
29.5	3.3	1.1	1.1
30	3.4	1.1	1.1
30.5	3.4	1.0	1.1
31	3.4	1.0	1.1
31.5	3.4	1.0	1.1
32	3.4	1.1	1.1
32.5	3.4	1.1	1.1
33	3.5	1.0	1.1
33.5	3.5	1.1	1.1
34	3.5	1.1	1.1
34.5	3.5	1.1	1.1
35	3.6	1.1	1.1
35.5	3.6	1.1	1.0
36	3.7	1.1	1.1
36.5	3.7	1.1	1.1
37	3.8	1.1	1.1
37.5	3.8	1.1	1.0
38	3.9	1.1	1.1
38.5	3.9	1.1	1.1
39	3.9	1.1	1.1
39.5	4.0	1.1	1.1
40	4.0	1.1	1.1



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS