

Fixed Attenuator**WR28-ATT-30+***Typical Performance Data (+25°C)*

FREQ.	ATTENUATION	WR28 INPUT VSWR	WR28 OUTPUT VSWR
(GHz)	(dB)	(:1)	(:1)
26.5	28.76	1.09	1.13
27.0	28.83	1.09	1.12
27.5	28.97	1.10	1.12
28.0	29.13	1.10	1.11
28.5	29.29	1.08	1.09
29.0	29.42	1.07	1.09
29.5	29.48	1.07	1.08
30.0	29.52	1.05	1.06
30.5	29.64	1.05	1.07
31.0	29.80	1.05	1.06
31.5	29.99	1.05	1.05
32.0	30.14	1.06	1.05
32.5	30.26	1.06	1.05
33.0	30.21	1.05	1.06
33.5	30.30	1.06	1.06
34.0	30.47	1.04	1.05
34.5	30.67	1.03	1.05
35.0	30.83	1.04	1.05
35.5	30.96	1.03	1.04
36.0	31.08	1.04	1.04
36.5	31.14	1.04	1.03
37.0	31.12	1.04	1.04
37.5	31.20	1.04	1.05
38.0	31.36	1.03	1.04
38.5	31.51	1.03	1.04
39.0	31.65	1.03	1.04
39.5	31.75	1.03	1.04
40.0	31.83	1.04	1.04



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS