

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
10	0.57	1.03	1.03
50	0.58	1.03	1.04
100	0.59	1.04	1.04
200	0.61	1.05	1.06
300	0.64	1.07	1.08
400	0.66	1.10	1.10
500	0.69	1.12	1.13
600	0.73	1.15	1.16
700	0.73	1.15	1.16
800	0.79	1.20	1.21
900	0.79	1.20	1.21
1000	0.85	1.23	1.25
1500	0.97	1.26	1.29
2000	1.10	1.22	1.24
2500	1.18	1.14	1.17
3000	1.30	1.07	1.08
3500	1.40	1.14	1.12
4000	1.58	1.24	1.21
4500	1.70	1.28	1.24
5000	1.88	1.26	1.22
5500	2.02	1.21	1.17
6000	2.31	1.10	1.06
6500	2.62	1.04	1.03
6740	2.83	1.06	1.07
7000	3.37	1.12	1.13
7500	4.22	1.14	1.13
8000	6.73	1.12	1.03
8500	10.52	1.14	1.10
9000	24.42	1.04	1.05
9200	27.64	1.13	1.01
9500	25.92	1.23	1.03
10000	29.11	1.42	1.08
10500	38.02	1.45	1.09
11000	32.89	1.41	1.11
11500	30.09	1.36	1.14
12000	28.51	1.29	1.21
12500	28.22	1.26	1.26
13000	28.66	1.26	1.32
13500	29.31	1.30	1.36
14000	30.75	1.39	1.39
14500	31.90	1.47	1.41
15000	33.47	1.61	1.41
15500	34.29	1.70	1.41
16000	35.08	1.85	1.36
16500	35.32	1.93	1.31
17000	35.66	2.01	1.21
17500	35.79	2.02	1.13
18000	36.22	1.95	1.01
18500	36.55	1.86	1.11
19000	37.06	1.65	1.29
19500	37.36	1.50	1.43
20000	37.47	1.27	1.64
20500	37.57	1.14	1.78
21000	37.86	1.11	1.96
21500	38.24	1.21	2.06
22000	37.73	1.38	2.18
22500	37.22	1.51	2.25
23000	36.11	1.68	2.32
23500	35.75	1.79	2.35
24000	34.98	1.93	2.34
24500	34.54	1.99	2.29
25000	33.78	2.04	2.21
25500	33.29	2.02	2.12
26000	32.78	1.93	2.00

