

Typical Performance Data

| FREQUENCY (GHz) | ATTENUATION (dB) | VSWR (:1) |
|--------------------|---------------------|--------------|
| 0.01 | 4.00 | 1.04 |
| 0.02 | 3.99 | 1.03 |
| 0.04 | 4.00 | 1.03 |
| 0.06 | 3.99 | 1.04 |
| 0.08 | 4.00 | 1.04 |
| 0.10 | 4.00 | 1.04 |
| 0.20 | 3.99 | 1.04 |
| 0.40 | 3.99 | 1.04 |
| 0.60 | 3.99 | 1.04 |
| 0.80 | 3.99 | 1.04 |
| 1.00 | 3.99 | 1.04 |
| 1.20 | 3.99 | 1.04 |
| 1.40 | 3.99 | 1.04 |
| 1.60 | 4.00 | 1.04 |
| 1.80 | 3.99 | 1.05 |
| 2.00 | 3.99 | 1.05 |
| 3.00 | 4.00 | 1.06 |
| 4.00 | 4.00 | 1.08 |
| 5.00 | 4.02 | 1.09 |
| 6.00 | 4.00 | 1.12 |
| 7.00 | 4.03 | 1.13 |
| 8.00 | 4.06 | 1.15 |
| 9.00 | 4.07 | 1.17 |
| 10.0 | 4.08 | 1.19 |
| 11.0 | 4.11 | 1.20 |
| 12.0 | 4.14 | 1.21 |
| 13.0 | 4.10 | 1.24 |
| 14.0 | 4.17 | 1.27 |
| 15.0 | 4.12 | 1.29 |
| 16.0 | 4.12 | 1.30 |
| 17.0 | 4.22 | 1.31 |
| 18.0 | 4.26 | 1.33 |
| 19.0 | 4.27 | 1.35 |
| 20.0 | 4.26 | 1.37 |
| 21.0 | 4.31 | 1.37 |
| 22.0 | 4.31 | 1.39 |
| 23.0 | 4.42 | 1.41 |
| 24.0 | 4.37 | 1.42 |
| 25.0 | 4.38 | 1.43 |
| 26.0 | 4.44 | 1.44 |
| 27.0 | 4.46 | 1.46 |
| 28.0 | 4.68 | 1.46 |
| 29.0 | 4.61 | 1.46 |
| 30.0 | 4.41 | 1.48 |
| 31.0 | 4.51 | 1.48 |
| 32.0 | 4.96 | 1.47 |
| 33.0 | 4.63 | 1.47 |
| 34.0 | 4.59 | 1.48 |
| 35.0 | 4.73 | 1.47 |
| 36.0 | 4.93 | 1.47 |
| 37.0 | 4.91 | 1.48 |
| 38.0 | 4.69 | 1.48 |
| 39.0 | 4.92 | 1.50 |
| 40.0 | 5.55 | 1.51 |