

Digital Step Attenuator

TOAT-4816+

Typical Performance Data

FREQUENCY (MHz)	STEP ATTENUATION* AT TTL CONTROL STATE							
	(dB)							
	000 THRU LOSS	001 4 dB	010 8 dB	011 12 dB	100 16 dB	101 20 dB	110 24 dB	111 28 dB
10.0	2.58	4.08	7.97	12.05	16.09	20.15	23.88	28.02
49.6	2.19	4.07	8.01	12.07	16.20	20.22	24.12	28.16
148.6	2.20	4.05	8.05	12.12	16.14	20.12	24.07	28.26
208.0	2.23	4.08	8.02	12.13	16.19	20.34	24.10	28.37
247.6	2.28	4.06	8.05	12.08	16.14	20.20	24.19	28.31
346.6	2.36	4.05	7.99	12.06	16.17	20.14	23.99	28.29
406.0	2.41	4.02	8.00	12.08	16.14	20.21	23.98	27.93
445.6	2.45	4.07	8.00	11.99	16.09	20.16	24.21	28.32
544.6	2.48	4.02	7.99	11.97	16.16	20.26	24.46	28.32
604.0	2.55	4.03	8.03	12.01	16.13	20.17	24.10	28.34
703.0	2.55	4.01	8.02	12.00	16.17	20.15	24.22	27.91
762.4	2.58	4.02	8.08	12.12	16.20	20.30	24.12	28.39
821.8	2.56	4.06	8.14	12.09	16.24	20.26	24.15	27.99
881.2	2.61	4.07	8.15	12.11	16.28	20.25	24.17	28.06
940.6	2.64	4.09	8.13	12.16	16.24	20.36	24.33	28.22
1000.0	2.65	4.06	8.12	12.13	16.16	20.34	24.16	28.02

* Step Attenuation above Thru Loss (TTL Logic 000).

FREQUENCY (MHz)	INPUT VSWR AT TTL CONTROL STATE						
	(:1)						
	001 4 dB	010 8 dB	011 12 dB	100 16 dB	101 20 dB	110 24 dB	111 28 dB
10.0	1.24	1.27	1.17	1.38	1.21	1.25	1.17
49.6	1.07	1.08	1.05	1.12	1.06	1.08	1.05
148.6	1.08	1.09	1.05	1.13	1.06	1.08	1.05
208.0	1.09	1.10	1.06	1.15	1.08	1.10	1.06
247.6	1.10	1.11	1.07	1.16	1.08	1.11	1.07
346.6	1.13	1.15	1.09	1.21	1.11	1.14	1.09
406.0	1.14	1.17	1.11	1.24	1.13	1.16	1.10
445.6	1.15	1.18	1.11	1.26	1.14	1.17	1.11
544.6	1.16	1.21	1.13	1.30	1.16	1.20	1.14
604.0	1.16	1.22	1.15	1.32	1.16	1.22	1.15
703.0	1.16	1.24	1.16	1.34	1.18	1.24	1.17
762.4	1.16	1.25	1.17	1.36	1.19	1.26	1.18
821.8	1.15	1.25	1.18	1.36	1.19	1.26	1.19
881.2	1.14	1.26	1.19	1.37	1.19	1.28	1.20
940.6	1.13	1.26	1.20	1.37	1.19	1.28	1.21
1000.0	1.12	1.26	1.21	1.37	1.19	1.30	1.23

FREQUENCY (MHz)	OUTPUT VSWR AT TTL CONTROL STATE						
	(:1)						
	001 4 dB	010 8 dB	011 12 dB	100 16 dB	101 20 dB	110 24 dB	111 28 dB
10.0	1.42	1.29	1.29	1.11	1.11	1.10	1.11
49.6	1.14	1.09	1.10	1.05	1.05	1.05	1.06
148.6	1.11	1.07	1.06	1.05	1.04	1.04	1.04
208.0	1.12	1.06	1.05	1.02	1.02	1.02	1.01
247.6	1.15	1.08	1.07	1.05	1.04	1.04	1.04
346.6	1.22	1.20	1.12	1.09	1.07	1.07	1.08
406.0	1.29	1.19	1.18	1.12	1.13	1.11	1.12
445.6	1.29	1.19	1.18	1.13	1.13	1.13	1.12
544.6	1.35	1.26	1.26	1.19	1.20	1.19	1.20
604.0	1.31	1.24	1.23	1.19	1.19	1.18	1.20
703.0	1.31	1.25	1.26	1.21	1.23	1.23	1.21
762.4	1.28	1.25	1.26	1.23	1.23	1.23	1.24
821.8	1.26	1.22	1.23	1.20	1.19	1.20	1.19
881.2	1.26	1.22	1.23	1.20	1.21	1.21	1.21
940.6	1.29	1.23	1.25	1.19	1.19	1.21	1.22
1000.0	1.28	1.28	1.30	1.26	1.25	1.27	1.26

REV. X1
TOAT-4816+
061207
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

