

# Bi-Directional Coupler

# ZABDC20-322H-S+

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS		COUPLING		DIRECTIVITY		RETURN LOSS			
	(dB)		(dB)		(dB)		(dB)			
	IN-OUT	FWD-REV	IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
1500	0.21	0.25	20.66	20.64	19.58	18.76	23.71	24.23	20.19	22.43
1600	0.22	0.26	20.33	20.32	20.49	19.37	23.39	23.90	20.02	21.58
1700	0.22	0.27	20.05	20.04	21.29	19.91	23.26	23.56	19.99	20.76
1800	0.23	0.28	19.81	19.81	22.02	20.38	23.21	23.40	20.04	20.29
1900	0.23	0.29	19.62	19.63	22.51	20.77	23.18	23.59	20.19	19.85
2000	0.24	0.29	19.47	19.48	23.08	21.04	23.24	23.71	20.57	19.53
2100	0.24	0.29	19.36	19.38	23.56	21.40	23.46	23.96	21.09	19.35
2200	0.24	0.28	19.29	19.31	24.38	22.01	23.93	24.34	21.77	19.30
2300	0.24	0.28	19.26	19.29	25.54	23.05	24.61	24.85	22.90	19.35
2400	0.24	0.27	19.28	19.30	27.14	24.56	25.51	25.56	24.17	19.49
2500	0.23	0.27	19.33	19.35	29.28	26.72	26.57	26.55	26.12	19.67
2600	0.23	0.26	19.43	19.45	31.77	29.60	27.98	27.90	28.39	20.11
2700	0.23	0.25	19.57	19.59	33.12	33.66	29.40	29.40	31.50	20.73
2800	0.22	0.26	19.76	19.79	32.31	39.70	31.54	31.12	36.29	21.55
2900	0.22	0.25	20.01	20.04	29.94	40.52	34.90	33.15	41.55	22.69
3000	0.22	0.26	20.31	20.34	27.45	35.13	41.94	36.96	35.41	24.07
3100	0.22	0.26	20.66	20.68	25.57	30.96	43.15	39.96	30.15	26.05
3200	0.22	0.27	21.08	21.09	23.91	27.62	35.44	34.81	26.71	28.65
3300	0.22	0.28	21.56	21.58	22.49	25.52	31.57	30.68	24.15	31.98
3400	0.22	0.28	22.12	22.13	21.06	23.91	28.96	28.52	22.22	37.25
3500	0.22	0.29	22.77	22.77	19.65	21.67	27.18	27.81	20.83	40.12



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. OR  
ZABDC20-322H-S+  
12/28/2018  
Page 1 of 1