

Bi-Directional Coupler

ZABDC20-ED13198

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS		COUPLING		DIRECTIVITY		RETURN LOSS			
	(dB)		(dB)		(dB)		(dB)			
	IN-OUT	FWD-REV	IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
500.0	0.13	0.12	24.35	24.36	26.01	26.12	34.59	35.75	34.77	34.15
600.0	0.14	0.13	22.99	23.01	26.23	26.25	32.88	33.81	32.63	32.00
700.0	0.16	0.15	21.92	21.94	26.27	26.35	31.61	32.26	30.98	30.09
800.0	0.17	0.17	21.08	21.10	26.48	26.19	30.98	31.61	29.43	28.43
900.0	0.19	0.19	20.42	20.44	26.46	25.78	30.60	31.10	28.26	27.24
1000.0	0.20	0.20	19.91	19.93	26.39	25.90	30.35	30.95	27.18	26.13
1100.0	0.21	0.22	19.55	19.57	26.67	25.96	30.39	30.81	26.42	25.28
1200.0	0.22	0.23	19.30	19.32	27.18	26.55	30.40	30.67	25.87	24.71
1300.0	0.22	0.24	19.17	19.19	27.96	27.47	30.69	30.65	25.48	24.35
1400.0	0.23	0.24	19.15	19.17	29.44	28.79	31.13	30.80	25.20	24.09
1500.0	0.23	0.25	19.24	19.25	31.56	29.96	32.22	31.59	25.11	24.02
1600.0	0.23	0.25	19.44	19.46	34.00	31.28	34.08	32.70	25.11	24.09
1700.0	0.23	0.25	19.75	19.77	34.30	30.63	36.77	34.05	25.28	24.21
1800.0	0.23	0.25	20.20	20.22	32.66	29.13	41.59	35.13	25.53	24.47
1900.0	0.23	0.25	20.80	20.82	30.27	27.70	47.55	35.92	25.93	24.76
2000.0	0.23	0.25	21.57	21.59	28.19	26.21	43.27	36.15	26.57	25.27
2100.0	0.22	0.24	22.55	22.57	26.26	24.44	38.36	34.71	27.27	25.95
2200.0	0.22	0.24	23.81	23.83	24.33	22.63	34.93	33.32	28.12	26.71
2300.0	0.22	0.24	25.44	25.47	21.60	20.27	33.02	32.36	28.76	27.39
2400.0	0.22	0.24	27.67	27.68	17.92	16.88	32.21	32.13	29.47	28.04
2500.0	0.22	0.24	30.98	30.99	12.55	11.88	31.20	32.13	29.91	28.26



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine. Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

RF/MICROWAVE COMPONENTS



REV. X1

ZABDC20-ED13198

12/31/2008

Page 1 of 1