

Coaxial Fixed Attenuator

UNAT-15A+

Typical Performance Data

FREQ.	ATTENUATION	VSWR
(MHz)	(dB)	(:1)
10	15.00	1.18
20	15.01	1.18
50	15.01	1.18
100	15.02	1.18
200	15.04	1.18
300	15.05	1.18
400	15.06	1.17
500	15.07	1.17
600	15.08	1.17
700	15.09	1.17
800	15.10	1.17
900	15.11	1.17
1000	15.12	1.17
1100	15.13	1.17
1200	15.14	1.17
1300	15.14	1.17
1400	15.15	1.18
1500	15.16	1.18
1600	15.17	1.18
1700	15.19	1.18
1800	15.19	1.18
1900	15.20	1.18
2000	15.22	1.18
2100	15.23	1.18
2200	15.24	1.18
2300	15.25	1.18
2400	15.26	1.18
2500	15.27	1.18
2600	15.28	1.18
2700	15.29	1.18
2800	15.30	1.18
2900	15.32	1.18
3000	15.33	1.18
3100	15.34	1.18
3200	15.35	1.18
3300	15.36	1.17
3400	15.37	1.17
3500	15.39	1.17
3600	15.40	1.17
3700	15.42	1.17
3800	15.43	1.16
3900	15.45	1.16
4000	15.46	1.16
4100	15.48	1.15
4200	15.49	1.15
4300	15.51	1.15
4400	15.53	1.14
4500	15.54	1.14
4600	15.56	1.13
4700	15.58	1.13
4800	15.59	1.12
4900	15.61	1.12
5000	15.63	1.11
5100	15.64	1.11
5200	15.66	1.10
5300	15.68	1.10
5400	15.70	1.10
5500	15.71	1.10
5800	15.76	1.10
6000	15.79	1.10