

Typical Performance Data

FREQ.	ATTENUATION	VSWR
(MHz)	(dB)	(:1)
10	4.92	1.07
20	4.92	1.07
50	4.93	1.07
100	4.94	1.07
200	4.96	1.07
300	4.97	1.07
400	4.97	1.07
500	4.98	1.07
600	4.99	1.07
700	5.00	1.07
800	5.00	1.08
900	5.01	1.08
1000	5.01	1.08
1100	5.02	1.08
1200	5.03	1.08
1300	5.03	1.08
1400	5.04	1.09
1500	5.04	1.09
1600	5.05	1.09
1700	5.06	1.09
1800	5.06	1.09
1900	5.07	1.10
2000	5.07	1.10
2100	5.08	1.10
2200	5.08	1.10
2300	5.09	1.10
2400	5.09	1.10
2500	5.10	1.10
2600	5.10	1.10
2700	5.11	1.10
2800	5.11	1.10
2900	5.12	1.10
3000	5.12	1.10
3100	5.12	1.10
3200	5.13	1.09
3300	5.13	1.09
3400	5.14	1.09
3500	5.14	1.08
3600	5.15	1.08
3700	5.15	1.07
3800	5.15	1.07
3900	5.16	1.06
4000	5.17	1.06
4100	5.17	1.05
4200	5.17	1.05
4300	5.18	1.04
4400	5.18	1.04
4500	5.19	1.03
4600	5.19	1.03
4700	5.20	1.02
4800	5.20	1.01
4900	5.21	1.01
5000	5.21	1.00
5100	5.22	1.01
5200	5.22	1.02
5300	5.23	1.02
5400	5.23	1.03
5500	5.23	1.04
5800	5.24	1.06
6000	5.25	1.07