

Xtra Long Life

USB RF SPDT Switch

USB-1SPDT-A18XL

Typical Performance Data

TEST CONDITIONS: @Temperature = 0degC

FREQUENCY (MHz)	INSERTION LOSS ON (dB)		ISOLATION OFF (dB)		VSWR IN (:1)		VSWR ENERGIZED (:1)		VSWR DE-ENERGIZED (:1)	
	IN-J1	IN-J2	IN-J1	IN-J2	ON	OFF	J1	J2	J1	J2
10	0.02	0.02	62.69	56.49	1.01	1.01	1.00	1.00	1.01	1.01
20	0.02	0.01	76.06	67.87	1.01	1.01	1.00	1.00	1.01	1.01
30	0.03	0.02	78.50	80.42	1.01	1.00	1.00	1.01	1.00	1.01
40	0.03	0.02	87.99	76.57	1.01	1.01	1.00	1.01	1.01	1.01
50	0.00	0.00	85.58	85.20	1.01	1.01	1.00	1.01	1.01	1.01
60	0.01	0.01	82.17	82.75	1.01	1.01	1.00	1.01	1.01	1.01
70	0.01	0.01	111.04	86.47	1.01	1.01	1.00	1.01	1.01	1.01
80	0.01	0.00	93.25	86.40	1.01	1.01	1.01	1.01	1.01	1.01
90	0.01	0.00	84.68	86.35	1.01	1.01	1.01	1.01	1.01	1.02
100	0.01	0.00	91.27	91.27	1.01	1.01	1.01	1.01	1.01	1.02
200	0.01	0.00	91.56	97.21	1.01	1.01	1.02	1.01	1.01	1.03
300	0.00	0.00	94.03	104.54	1.01	1.01	1.02	1.02	1.01	1.03
400	0.01	0.01	95.48	99.11	1.02	1.02	1.02	1.02	1.02	1.03
500	0.01	0.01	103.50	102.97	1.01	1.01	1.02	1.01	1.01	1.02
600	0.01	0.02	96.73	98.55	1.01	1.01	1.01	1.01	1.01	1.02
700	0.02	0.02	99.74	102.52	1.01	1.01	1.02	1.01	1.01	1.02
800	0.02	0.02	105.65	100.78	1.01	1.01	1.02	1.01	1.01	1.02
900	0.02	0.02	99.56	102.99	1.01	1.02	1.02	1.02	1.02	1.03
1000	0.02	0.03	105.33	97.50	1.01	1.01	1.02	1.02	1.02	1.03
1200	0.02	0.03	95.06	104.12	1.01	1.01	1.03	1.01	1.01	1.03
1400	0.02	0.03	104.83	110.41	1.02	1.01	1.03	1.01	1.01	1.03
1600	0.03	0.03	94.89	99.77	1.02	1.02	1.03	1.02	1.02	1.03
1800	0.03	0.03	103.10	103.23	1.02	1.03	1.04	1.02	1.02	1.03
2000	0.03	0.04	103.84	103.70	1.02	1.03	1.04	1.02	1.02	1.04
2200	0.03	0.04	93.08	102.31	1.02	1.02	1.05	1.02	1.02	1.04
2400	0.04	0.05	102.45	104.45	1.03	1.04	1.05	1.03	1.03	1.05
2600	0.04	0.05	111.34	96.36	1.03	1.05	1.06	1.04	1.04	1.06
2800	0.04	0.05	105.47	103.64	1.03	1.04	1.07	1.04	1.04	1.06
3000	0.05	0.05	101.65	98.86	1.03	1.04	1.08	1.04	1.04	1.07
3200	0.05	0.06	97.59	105.83	1.04	1.06	1.08	1.06	1.06	1.08
3400	0.06	0.07	99.40	102.61	1.06	1.09	1.10	1.08	1.09	1.10
3600	0.06	0.06	105.16	112.37	1.07	1.08	1.10	1.08	1.08	1.11
4000	0.07	0.07	100.12	102.42	1.10	1.13	1.12	1.12	1.12	1.13
4500	0.08	0.09	110.61	104.60	1.14	1.14	1.13	1.15	1.15	1.14
5000	0.10	0.12	101.66	99.14	1.19	1.22	1.14	1.23	1.21	1.17
5500	0.12	0.13	104.68	106.94	1.24	1.21	1.13	1.23	1.21	1.15
6000	0.12	0.14	102.68	99.55	1.26	1.23	1.13	1.27	1.23	1.17
6500	0.12	0.14	101.00	95.07	1.26	1.19	1.10	1.24	1.19	1.15
7000	0.12	0.13	97.32	97.36	1.23	1.14	1.08	1.20	1.16	1.13
7500	0.12	0.13	92.52	93.66	1.19	1.13	1.06	1.16	1.12	1.11
8000	0.12	0.13	100.57	96.16	1.17	1.08	1.06	1.13	1.09	1.11
8500	0.15	0.14	95.34	93.74	1.12	1.08	1.07	1.11	1.08	1.11
9000	0.15	0.14	94.67	91.78	1.08	1.06	1.05	1.05	1.04	1.10
9500	0.16	0.15	92.17	93.77	1.06	1.02	1.07	1.10	1.04	1.11
10000	0.17	0.17	92.10	91.45	1.07	1.05	1.08	1.06	1.02	1.11
12000	0.21	0.18	91.26	86.33	1.03	1.06	1.12	1.04	1.07	1.05
13000	0.26	0.20	87.46	84.59	1.06	1.08	1.21	1.06	1.10	1.14
14000	0.29	0.22	87.80	81.01	1.12	1.11	1.27	1.14	1.15	1.25
15000	0.36	0.28	83.73	78.00	1.27	1.25	1.31	1.25	1.25	1.32
16000	0.46	0.34	82.49	75.43	1.19	1.31	1.27	1.23	1.27	1.26
17000	0.38	0.28	81.40	72.40	1.09	1.11	1.22	1.04	1.10	1.12
18000	0.43	0.33	80.97	69.69	1.27	1.08	1.26	1.20	1.05	1.18

REV. X1
USB-1SPDT-A18XL
110105

Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Xtra Long Life USB RF SPDT Switch

USB-1SPDT-A18XL

Typical Performance Data

TEST CONDITIONS: @Temperature = +25degC

FREQUENCY (MHz)	INSERTION LOSS ON (dB)		ISOLATION OFF (dB)		VSWR IN (:1)		VSWR ENERGIZED (:1)		VSWR DE-ENERGIZED (:1)	
	IN-J1	IN-J2	IN-J1	IN-J2	ON	OFF	J1	J2	J1	J2
10	0.00	0.00	64.43	63.17	1.00	1.00	1.00	1.02	1.02	1.01
20	0.02	0.02	73.42	80.43	1.00	1.00	1.00	1.01	1.01	1.01
30	0.02	0.02	82.26	73.81	1.00	1.00	1.00	1.00	1.00	1.01
40	0.03	0.03	91.18	77.61	1.00	1.01	1.00	1.00	1.00	1.01
50	0.00	0.00	91.95	80.50	1.00	1.00	1.00	1.00	1.00	1.01
60	0.00	0.00	92.97	83.43	1.00	1.00	1.00	1.00	1.00	1.01
70	0.01	0.01	81.69	88.95	1.00	1.00	1.00	1.00	1.00	1.01
80	0.01	0.01	106.34	84.65	1.00	1.00	1.00	1.00	1.00	1.01
90	0.01	0.00	89.91	98.42	1.00	1.00	1.00	1.00	1.00	1.01
100	0.00	0.01	92.71	86.88	1.00	1.00	1.00	1.00	1.00	1.01
200	0.01	0.01	94.79	97.05	1.00	1.00	1.01	1.01	1.01	1.01
300	0.02	0.02	109.88	90.43	1.00	1.00	1.01	1.01	1.01	1.01
400	0.02	0.02	102.23	99.10	1.01	1.01	1.01	1.01	1.01	1.01
500	0.02	0.02	97.52	101.30	1.01	1.00	1.01	1.01	1.01	1.01
600	0.03	0.03	100.41	100.25	1.01	1.00	1.01	1.01	1.01	1.01
700	0.03	0.03	98.46	100.26	1.01	1.01	1.01	1.01	1.01	1.01
800	0.03	0.03	107.02	108.08	1.01	1.01	1.01	1.01	1.01	1.01
900	0.03	0.03	98.13	102.59	1.01	1.01	1.02	1.01	1.01	1.01
1000	0.03	0.04	106.26	108.06	1.01	1.01	1.02	1.01	1.01	1.02
1200	0.04	0.04	105.64	118.05	1.01	1.01	1.02	1.00	1.01	1.02
1400	0.04	0.04	113.89	108.14	1.01	1.01	1.03	1.00	1.01	1.02
1600	0.05	0.05	109.89	113.36	1.01	1.01	1.03	1.01	1.01	1.02
1800	0.04	0.05	101.11	105.12	1.02	1.02	1.04	1.01	1.01	1.03
2000	0.05	0.06	98.50	108.08	1.03	1.02	1.04	1.01	1.01	1.03
2200	0.05	0.06	109.01	102.61	1.04	1.02	1.05	1.02	1.02	1.04
2400	0.06	0.06	97.17	103.88	1.05	1.03	1.05	1.02	1.02	1.04
2600	0.06	0.07	102.67	99.87	1.06	1.03	1.06	1.03	1.03	1.05
2800	0.06	0.07	102.17	101.90	1.07	1.04	1.07	1.03	1.04	1.06
3000	0.06	0.07	102.72	102.95	1.08	1.04	1.08	1.04	1.04	1.06
3200	0.06	0.07	108.07	100.45	1.08	1.06	1.09	1.05	1.06	1.07
3400	0.07	0.08	101.22	103.70	1.09	1.07	1.09	1.06	1.07	1.08
3600	0.08	0.08	106.01	102.58	1.09	1.09	1.10	1.08	1.08	1.09
4000	0.09	0.09	105.56	107.81	1.10	1.11	1.11	1.11	1.11	1.10
4500	0.10	0.11	96.22	96.80	1.11	1.15	1.13	1.15	1.15	1.12
5000	0.12	0.13	98.62	100.46	1.15	1.18	1.13	1.18	1.18	1.14
5500	0.13	0.14	105.56	102.08	1.21	1.20	1.13	1.22	1.20	1.15
6000	0.14	0.16	96.57	94.10	1.26	1.20	1.12	1.23	1.21	1.15
6500	0.14	0.16	96.21	107.68	1.27	1.19	1.11	1.23	1.19	1.15
7000	0.13	0.16	99.56	100.96	1.24	1.16	1.10	1.21	1.17	1.14
7500	0.15	0.17	94.50	101.70	1.18	1.14	1.08	1.20	1.15	1.13
8000	0.14	0.16	93.06	95.68	1.12	1.13	1.07	1.17	1.13	1.12
8500	0.15	0.16	92.44	95.29	1.06	1.09	1.07	1.13	1.09	1.12
9000	0.14	0.16	92.53	92.00	1.06	1.06	1.06	1.09	1.06	1.10
9500	0.14	0.16	90.69	98.64	1.09	1.04	1.06	1.07	1.03	1.10
10000	0.14	0.16	90.46	93.90	1.10	1.02	1.07	1.06	1.03	1.10
12000	0.16	0.17	86.14	90.83	1.12	1.10	1.14	1.04	1.10	1.08
13000	0.17	0.19	82.24	89.32	1.10	1.13	1.19	1.07	1.15	1.14
14000	0.18	0.20	77.92	83.48	1.22	1.15	1.25	1.10	1.18	1.24
15000	0.21	0.22	74.68	81.86	1.33	1.19	1.27	1.14	1.19	1.30
16000	0.22	0.24	71.05	79.37	1.20	1.19	1.25	1.13	1.19	1.28
17000	0.19	0.21	67.00	78.15	1.18	1.11	1.23	1.09	1.14	1.17
18000	0.17	0.21	64.13	77.52	1.20	1.13	1.27	1.06	1.14	1.17

REV. X1
USB-1SPDT-A18XL
110105

Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Xtra Long Life USB RF SPDT Switch

USB-1SPDT-A18XL

Typical Performance Data

TEST CONDITIONS: @Temperature = +45degC

FREQUENCY (MHz)	INSERTION LOSS ON (dB)		ISOLATION OFF (dB)		VSWR IN (:1)		VSWR ENERGIZED (:1)		VSWR DE-ENERGIZED (:1)	
	IN-J1	IN-J2	IN-J1	IN-J2	ON	OFF	J1	J2	J1	J2
10	0.01	0.01	63.16	54.04	1.00	1.01	1.00	1.03	1.03	1.01
20	0.02	0.01	66.95	73.71	1.00	1.01	1.00	1.01	1.01	1.01
30	0.01	0.01	81.55	86.33	1.00	1.00	1.00	1.01	1.01	1.01
40	0.01	0.02	84.27	75.48	1.01	1.01	1.00	1.01	1.01	1.01
50	0.04	0.04	99.67	97.07	1.00	1.01	1.00	1.01	1.01	1.01
60	0.04	0.04	90.09	91.49	1.00	1.00	1.00	1.00	1.00	1.01
70	0.03	0.03	96.24	90.53	1.01	1.00	1.00	1.00	1.00	1.01
80	0.03	0.03	89.09	87.33	1.01	1.00	1.00	1.00	1.00	1.01
90	0.04	0.03	87.46	90.96	1.01	1.01	1.00	1.01	1.00	1.01
100	0.04	0.03	108.00	93.23	1.01	1.01	1.00	1.01	1.01	1.01
200	0.04	0.03	91.04	110.98	1.00	1.00	1.00	1.01	1.00	1.01
300	0.02	0.02	112.96	96.74	1.01	1.00	1.00	1.00	1.01	1.01
400	0.02	0.01	93.21	101.96	1.01	1.01	1.00	1.01	1.01	1.01
500	0.02	0.01	101.11	107.60	1.01	1.01	1.01	1.01	1.01	1.01
600	0.01	0.00	98.77	102.27	1.01	1.01	1.01	1.01	1.01	1.01
700	0.00	0.00	100.18	99.09	1.01	1.01	1.01	1.01	1.01	1.01
800	0.00	0.00	106.15	102.47	1.01	1.01	1.01	1.00	1.01	1.01
900	0.00	0.00	99.25	102.98	1.01	1.01	1.01	1.00	1.01	1.01
1000	0.00	0.01	99.90	105.39	1.01	1.01	1.02	1.01	1.01	1.02
1200	0.01	0.01	100.12	107.89	1.01	1.00	1.02	1.01	1.01	1.02
1400	0.01	0.02	100.50	102.06	1.01	1.01	1.02	1.00	1.01	1.02
1600	0.01	0.02	99.87	117.53	1.01	1.01	1.03	1.01	1.00	1.03
1800	0.01	0.02	102.17	97.27	1.01	1.01	1.04	1.01	1.01	1.04
2000	0.02	0.02	96.89	109.32	1.02	1.02	1.05	1.01	1.02	1.04
2200	0.02	0.03	102.64	101.47	1.02	1.02	1.05	1.01	1.01	1.04
2400	0.03	0.04	101.33	93.50	1.03	1.03	1.05	1.03	1.03	1.04
2600	0.03	0.04	106.77	100.51	1.03	1.04	1.07	1.04	1.04	1.06
2800	0.03	0.04	112.14	102.63	1.03	1.05	1.08	1.05	1.05	1.07
3000	0.03	0.04	113.00	99.01	1.04	1.06	1.08	1.05	1.05	1.07
3200	0.04	0.04	107.61	105.71	1.05	1.07	1.08	1.06	1.07	1.07
3400	0.05	0.06	107.98	114.40	1.07	1.09	1.09	1.08	1.09	1.08
3600	0.05	0.06	114.87	100.87	1.08	1.11	1.10	1.10	1.11	1.10
4000	0.06	0.07	98.83	101.56	1.11	1.13	1.11	1.11	1.13	1.10
4500	0.08	0.09	104.39	112.46	1.15	1.18	1.13	1.17	1.18	1.13
5000	0.09	0.10	97.43	101.23	1.19	1.19	1.12	1.18	1.18	1.13
5500	0.10	0.12	105.16	97.84	1.22	1.20	1.13	1.21	1.20	1.16
6000	0.10	0.12	99.05	98.10	1.24	1.19	1.12	1.21	1.19	1.15
6500	0.10	0.13	101.27	95.61	1.23	1.17	1.11	1.21	1.17	1.16
7000	0.10	0.14	95.68	94.61	1.22	1.15	1.11	1.20	1.15	1.16
7500	0.12	0.15	95.39	101.97	1.19	1.14	1.07	1.19	1.13	1.13
8000	0.12	0.15	93.75	92.47	1.16	1.14	1.08	1.20	1.14	1.15
8500	0.12	0.15	93.50	94.53	1.13	1.09	1.06	1.13	1.09	1.11
9000	0.12	0.15	95.48	90.98	1.08	1.08	1.05	1.11	1.08	1.11
9500	0.12	0.14	93.48	91.28	1.04	1.06	1.06	1.06	1.03	1.11
10000	0.13	0.15	93.06	92.02	1.03	1.06	1.05	1.03	1.05	1.09
12000	0.15	0.17	87.31	85.88	1.08	1.13	1.14	1.06	1.13	1.06
13000	0.18	0.21	86.93	83.67	1.12	1.18	1.21	1.10	1.19	1.11
14000	0.18	0.22	85.23	79.47	1.12	1.16	1.26	1.12	1.15	1.19
15000	0.17	0.22	81.58	75.73	1.11	1.07	1.24	1.07	1.06	1.24
16000	0.17	0.25	80.35	72.22	1.06	1.06	1.22	1.11	1.10	1.22
17000	0.16	0.24	78.82	68.49	1.04	1.09	1.30	1.14	1.15	1.19
18000	0.23	0.24	76.92	66.23	1.06	1.35	1.38	1.17	1.37	1.22

REV. X1
USB-1SPDT-A18XL
110105

Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

