

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
0.3	6.98	1.00
0.5	6.98	1.00
0.7	6.98	1.00
0.9	6.98	1.00
1.0	6.99	1.00
2.0	6.99	1.00
3.0	6.99	1.00
4.0	6.98	1.00
5.0	6.99	1.00
6.0	6.99	1.00
7.0	6.99	1.00
8.0	6.99	1.00
9.0	6.99	1.00
10.0	6.99	1.00
15.0	6.99	1.00
20.0	6.99	1.00
25.0	6.99	1.00
30.0	7.00	1.00
35.0	7.00	1.00
40.0	7.00	1.00
45.0	7.00	1.00
50.0	7.00	1.00
55.0	7.00	1.00
60.0	7.00	1.00
65.0	7.00	1.00
70.0	7.00	1.00
75.0	7.00	1.00
80.0	7.00	1.00
85.0	7.01	1.00
90.0	7.01	1.00
95.0	7.01	1.00
100.0	7.01	1.00
105.0	7.01	1.00
110.0	7.01	1.00
115.0	7.01	1.00
120.0	7.01	1.00
125.0	7.01	1.00
130.0	7.02	1.00
135.0	7.02	1.00
140.0	7.02	1.00
145.0	7.02	1.00
150.0	7.02	1.00
155.0	7.02	1.00
160.0	7.02	1.00
165.0	7.02	1.01
170.0	7.02	1.01
175.0	7.02	1.01
180.0	7.02	1.01
185.0	7.03	1.01
190.0	7.03	1.01
195.0	7.03	1.01
200.0	7.03	1.01