

4 Way-0° Power Splitter/Combiner

ZB4PD-232-50W+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹				AMP. UNBAL. (dB)	ISOLATION			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR				
	S-1	S-2	S-3	S-4		1-2	1-3	3-4			S	1	2	3	4
600.0	6.54	6.56	6.55	6.57	0.03	18.75	23.68	18.88	0.83	600.0	1.64	1.04	1.04	1.04	1.04
640.0	6.53	6.55	6.54	6.56	0.03	19.79	25.11	19.95	0.88	640.0	1.61	1.04	1.03	1.04	1.03
660.0	6.51	6.53	6.53	6.54	0.03	20.44	25.87	20.60	0.92	660.0	1.58	1.04	1.03	1.04	1.03
680.0	6.50	6.52	6.51	6.52	0.03	21.19	26.68	21.36	0.94	680.0	1.54	1.04	1.03	1.05	1.04
700.0	6.47	6.49	6.49	6.50	0.03	22.07	27.52	22.25	0.97	700.0	1.50	1.05	1.04	1.05	1.04
720.0	6.45	6.47	6.46	6.48	0.02	23.10	28.39	23.29	1.00	720.0	1.45	1.05	1.04	1.05	1.05
740.0	6.43	6.44	6.44	6.45	0.02	24.31	29.29	24.49	1.03	740.0	1.40	1.05	1.05	1.06	1.05
760.0	6.41	6.42	6.42	6.43	0.02	25.71	30.20	25.87	1.06	760.0	1.35	1.05	1.05	1.06	1.05
780.0	6.39	6.41	6.41	6.42	0.02	27.30	31.10	27.41	1.09	780.0	1.30	1.05	1.05	1.05	1.06
800.0	6.38	6.39	6.39	6.40	0.02	29.02	31.94	29.02	1.12	800.0	1.25	1.05	1.05	1.05	1.05
900.0	6.38	6.39	6.39	6.40	0.03	29.96	33.46	29.57	1.26	900.0	1.15	1.01	1.02	1.01	1.02
1000.0	6.44	6.45	6.45	6.46	0.02	25.87	31.39	26.04	1.39	1000.0	1.23	1.05	1.04	1.05	1.04
1100.0	6.47	6.47	6.48	6.49	0.03	24.50	29.84	24.93	1.56	1100.0	1.23	1.10	1.09	1.11	1.09
1200.0	6.47	6.48	6.48	6.50	0.03	24.01	29.45	24.35	1.76	1200.0	1.11	1.15	1.14	1.15	1.13
1300.0	6.51	6.52	6.53	6.54	0.03	24.49	30.17	24.51	1.99	1300.0	1.08	1.20	1.19	1.18	1.18
1400.0	6.58	6.58	6.61	6.62	0.04	26.91	31.97	26.54	2.24	1400.0	1.21	1.23	1.24	1.23	1.23
1500.0	6.62	6.63	6.66	6.68	0.05	31.54	35.00	30.74	2.50	1500.0	1.27	1.23	1.24	1.23	1.24
1600.0	6.64	6.65	6.71	6.70	0.07	34.73	39.50	34.09	2.74	1600.0	1.23	1.18	1.19	1.18	1.20
1700.0	6.68	6.71	6.78	6.76	0.10	35.32	43.37	33.57	2.74	1700.0	1.16	1.12	1.12	1.12	1.14
1800.0	6.70	6.70	6.79	6.79	0.09	30.26	40.54	29.21	2.91	1800.0	1.09	1.09	1.09	1.09	1.11
1900.0	6.76	6.75	6.85	6.85	0.10	25.15	36.58	25.25	3.13	1900.0	1.11	1.09	1.08	1.07	1.08
2000.0	6.81	6.80	6.91	6.91	0.11	23.76	33.07	24.33	3.44	2000.0	1.20	1.11	1.08	1.09	1.07
2100.0	6.87	6.86	6.99	6.98	0.13	26.18	30.25	26.88	3.79	2100.0	1.23	1.15	1.12	1.13	1.11
2200.0	6.92	6.91	7.07	7.06	0.16	28.58	27.88	27.28	4.26	2200.0	1.18	1.16	1.15	1.14	1.14
2220.0	6.93	6.92	7.09	7.08	0.17	26.71	27.49	25.50	4.37	2220.0	1.17	1.15	1.15	1.13	1.14
2240.0	6.94	6.94	7.12	7.09	0.18	24.64	27.12	23.65	4.48	2240.0	1.15	1.15	1.15	1.12	1.13
2260.0	6.95	6.95	7.14	7.12	0.19	22.67	26.78	21.88	4.59	2260.0	1.13	1.13	1.14	1.11	1.12
2280.0	6.97	6.97	7.17	7.15	0.20	20.89	26.49	20.26	4.71	2280.0	1.12	1.12	1.14	1.09	1.11
2300.0	6.99	6.99	7.21	7.18	0.22	19.30	26.23	18.78	4.83	2300.0	1.11	1.10	1.12	1.07	1.09

¹Total Loss = Insertion Loss + 6dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site www.minicircuits.com



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. X2

ZB4PD-232-50W+

6/29/2010

Page 1 of 1