


Typical Performance Curves


GAIN vs. TEMPERATURE

INPUT POWER = -20, VOLTAGE = 3.9V




GAIN vs. VOLTAGE

INPUT POWER = -20, Temperature = +25°C




ISOLATION vs. TEMPERATURE

INPUT POWER = -20, VOLTAGE = 3.9V




ISOLATION vs. VOLTAGE

INPUT POWER = -20, Temperature = +25°C




INPUT RETURN LOSS vs. TEMPERATURE

INPUT POWER = -20, VOLTAGE = 3.9V




INPUT RETURN LOSS vs. VOLTAGE

INPUT POWER = -20, Temperature = +25°C




OUTPUT RETURN LOSS vs. TEMPERATURE

INPUT POWER = -20, VOLTAGE = 3.9V



OUTPUT RETURN LOSS vs. VOLTAGE

INPUT POWER = -20, Temperature = +25°C



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Typical Performance Curves


OUTPUT IP3 vs. TEMPERATURE

INPUT POWER = -20, VOLTAGE = 3.9V




OUTPUT IP-3 vs. VOLTAGE

INPUT POWER = -20, Temperature = +25°C




OUTPUT POWER at 1dB Compression vs. TEMPERATURE

VOLTAGE = 3.9V




OUTPUT POWER at 1dB Compression vs. VOLTAGE

Temperature = +25°C



Noise Figure vs. TEMPERATURE

VOLTAGE = 3.9V



Noise Figure vs. VOLTAGE

Temperature = +25°C

