

4 Way-0° Power Splitter/Combiner

WP4C+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION			VSWR				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
600	9.67	9.87	9.79	9.60	0.27	1.37	16.05	15.52	16.13	4.23	1.63	1.62	1.62	1.63
625	9.10	9.31	9.22	9.04	0.27	1.23	16.88	16.29	16.97	3.63	1.62	1.61	1.61	1.61
650	8.61	8.81	8.73	8.55	0.26	1.08	17.83	17.17	17.95	3.13	1.60	1.59	1.59	1.59
675	8.19	8.38	8.29	8.12	0.26	0.99	18.91	18.17	19.04	2.71	1.58	1.57	1.57	1.57
700	7.82	8.01	7.93	7.75	0.26	0.85	20.12	19.26	20.28	2.36	1.55	1.55	1.54	1.55
710	7.70	7.88	7.80	7.62	0.26	0.84	20.62	19.72	20.80	2.24	1.54	1.54	1.54	1.54
720	7.58	7.77	7.68	7.51	0.26	0.74	21.15	20.21	21.33	2.13	1.53	1.53	1.53	1.53
730	7.47	7.65	7.57	7.40	0.25	0.71	21.68	20.69	21.89	2.03	1.52	1.52	1.52	1.52
740	7.37	7.55	7.47	7.30	0.25	0.67	22.22	21.18	22.45	1.94	1.51	1.51	1.51	1.51
750	7.28	7.46	7.38	7.21	0.25	0.62	22.76	21.67	23.02	1.85	1.50	1.50	1.50	1.50
760	7.19	7.37	7.29	7.12	0.25	0.55	23.32	22.18	23.58	1.77	1.49	1.49	1.49	1.49
770	7.11	7.29	7.21	7.05	0.25	0.51	23.88	22.67	24.13	1.69	1.48	1.48	1.48	1.48
780	7.05	7.22	7.14	6.98	0.25	0.50	24.37	23.15	24.64	1.62	1.48	1.47	1.47	1.47
790	6.98	7.16	7.07	6.91	0.24	0.44	24.85	23.59	25.11	1.56	1.47	1.46	1.46	1.46
800	6.93	7.10	7.01	6.85	0.24	0.37	25.23	23.98	25.50	1.50	1.46	1.46	1.45	1.45
810	6.87	7.05	6.96	6.80	0.24	0.37	25.55	24.29	25.80	1.44	1.45	1.45	1.44	1.44
820	6.83	6.99	6.92	6.76	0.24	0.29	25.72	24.54	26.01	1.40	1.44	1.44	1.43	1.43
830	6.79	6.96	6.88	6.72	0.23	0.28	25.82	24.70	26.12	1.35	1.43	1.43	1.43	1.43
840	6.75	6.92	6.84	6.68	0.24	0.27	25.82	24.80	26.09	1.32	1.43	1.42	1.42	1.42
850	6.72	6.89	6.80	6.65	0.24	0.30	25.73	24.84	26.01	1.29	1.42	1.42	1.41	1.41
860	6.70	6.86	6.78	6.63	0.23	0.32	25.56	24.79	25.81	1.26	1.41	1.41	1.40	1.41
870	6.67	6.84	6.75	6.61	0.23	0.33	25.36	24.66	25.54	1.24	1.41	1.40	1.40	1.40
880	6.65	6.82	6.73	6.59	0.23	0.34	25.07	24.46	25.24	1.22	1.40	1.40	1.39	1.39
890	6.64	6.80	6.72	6.57	0.23	0.36	24.76	24.23	24.90	1.21	1.40	1.39	1.38	1.39
900	6.62	6.78	6.70	6.56	0.23	0.41	24.44	23.96	24.55	1.21	1.39	1.38	1.38	1.38
910	6.62	6.77	6.69	6.55	0.22	0.45	24.06	23.65	24.16	1.22	1.39	1.38	1.37	1.38
920	6.61	6.77	6.68	6.54	0.22	0.50	23.69	23.36	23.79	1.23	1.38	1.37	1.37	1.37
930	6.60	6.76	6.68	6.54	0.22	0.53	23.34	23.04	23.42	1.25	1.38	1.37	1.36	1.37
940	6.60	6.75	6.68	6.54	0.22	0.58	22.99	22.72	23.07	1.27	1.38	1.37	1.36	1.36
950	6.60	6.75	6.67	6.53	0.22	0.61	22.66	22.43	22.73	1.29	1.37	1.36	1.35	1.36
960	6.60	6.75	6.67	6.53	0.22	0.65	22.36	22.13	22.38	1.31	1.37	1.36	1.35	1.36
970	6.61	6.75	6.67	6.54	0.21	0.70	22.06	21.85	22.07	1.33	1.37	1.36	1.35	1.36
980	6.61	6.76	6.68	6.55	0.21	0.76	21.76	21.56	21.75	1.36	1.37	1.35	1.35	1.35
990	6.62	6.76	6.67	6.55	0.21	0.79	21.48	21.28	21.46	1.38	1.36	1.35	1.34	1.35
1000	6.62	6.76	6.68	6.55	0.21	0.84	21.22	21.02	21.19	1.41	1.36	1.35	1.34	1.35
1025	6.65	6.79	6.70	6.58	0.21	0.93	20.57	20.35	20.55	1.48	1.36	1.34	1.33	1.35
1050	6.67	6.81	6.72	6.60	0.21	1.04	20.01	19.78	19.98	1.56	1.36	1.34	1.33	1.34
1075	6.71	6.84	6.75	6.64	0.20	1.15	19.54	19.28	19.48	1.62	1.36	1.34	1.33	1.35
1100	6.74	6.86	6.78	6.67	0.19	1.24	19.10	18.84	19.03	1.69	1.36	1.34	1.33	1.35
1125	6.78	6.90	6.82	6.71	0.19	1.35	18.69	18.41	18.63	1.76	1.36	1.34	1.33	1.35
1150	6.82	6.94	6.86	6.75	0.18	1.45	18.34	18.01	18.27	1.83	1.37	1.34	1.33	1.35
1175	6.86	6.98	6.90	6.80	0.18	1.54	18.04	17.68	17.95	1.90	1.37	1.35	1.33	1.35
1200	6.90	7.01	6.93	6.83	0.18	1.64	17.77	17.38	17.66	1.96	1.38	1.35	1.34	1.36
1300	7.06	7.15	7.07	6.99	0.16	2.01	16.88	16.35	16.74	2.20	1.40	1.37	1.36	1.38
1400	7.22	7.29	7.20	7.14	0.15	2.38	16.24	15.56	16.07	2.41	1.44	1.40	1.38	1.41
1500	7.36	7.41	7.32	7.28	0.13	2.71	15.77	14.91	15.58	2.59	1.47	1.43	1.41	1.44
1600	7.48	7.51	7.42	7.40	0.11	3.06	15.40	14.37	15.20	2.74	1.51	1.47	1.44	1.47
1700	7.60	7.60	7.50	7.50	0.10	3.40	15.12	13.89	14.90	2.87	1.54	1.50	1.47	1.50
1800	7.69	7.68	7.57	7.59	0.12	3.70	14.88	13.46	14.66	2.99	1.57	1.54	1.51	1.53
1900	7.79	7.75	7.64	7.67	0.15	4.02	14.69	13.04	14.46	3.09	1.60	1.57	1.53	1.56
2000	7.86	7.81	7.69	7.74	0.18	4.33	14.53	12.66	14.29	3.17	1.63	1.60	1.56	1.59
2200	8.01	7.92	7.79	7.90	0.22	4.99	14.24	11.90	14.01	3.34	1.68	1.65	1.61	1.64
2400	8.14	8.02	7.88	8.04	0.26	5.59	14.01	11.21	13.76	3.49	1.72	1.70	1.65	1.69
2500	8.20	8.06	7.93	8.11	0.27	5.88	13.88	10.90	13.64	3.54	1.74	1.71	1.67	1.71

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4C+

100627

Page 1 of 3

Mini-Circuits®

RF/MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

WP4C+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS ¹				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION			VSWR				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
600	9.66	9.86	9.78	9.60	0.26	1.80	15.86	15.33	15.94	4.51	1.63	1.62	1.62	1.63
625	9.08	9.28	9.20	9.02	0.26	1.62	16.69	16.10	16.78	3.85	1.61	1.60	1.60	1.61
650	8.57	8.77	8.69	8.52	0.25	1.47	17.64	16.98	17.74	3.30	1.59	1.59	1.59	1.60
675	8.14	8.33	8.24	8.07	0.25	1.31	18.73	17.98	18.83	2.84	1.57	1.57	1.57	1.57
700	7.76	7.95	7.87	7.70	0.25	1.13	19.94	19.09	20.04	2.46	1.55	1.55	1.55	1.55
710	7.63	7.82	7.73	7.56	0.25	1.11	20.46	19.57	20.57	2.33	1.54	1.54	1.54	1.54
720	7.51	7.70	7.61	7.44	0.25	1.08	20.99	20.05	21.11	2.21	1.53	1.53	1.53	1.53
730	7.40	7.59	7.50	7.33	0.26	1.03	21.54	20.55	21.67	2.11	1.52	1.52	1.52	1.52
740	7.30	7.48	7.40	7.23	0.25	0.99	22.10	21.05	22.24	2.01	1.51	1.51	1.51	1.51
750	7.20	7.38	7.30	7.14	0.25	0.96	22.67	21.56	22.83	1.91	1.50	1.50	1.51	1.50
760	7.12	7.30	7.21	7.05	0.25	0.90	23.24	22.09	23.38	1.83	1.49	1.49	1.50	1.49
770	7.04	7.22	7.13	6.97	0.25	0.84	23.82	22.60	23.96	1.74	1.49	1.48	1.49	1.49
780	6.97	7.15	7.06	6.89	0.25	0.82	24.36	23.12	24.49	1.67	1.48	1.48	1.48	1.48
790	6.90	7.07	6.99	6.83	0.24	0.76	24.88	23.57	24.98	1.60	1.47	1.47	1.47	1.47
800	6.85	7.02	6.93	6.77	0.25	0.74	25.26	23.99	25.42	1.53	1.46	1.46	1.46	1.46
810	6.79	6.97	6.88	6.72	0.25	0.70	25.59	24.33	25.78	1.48	1.45	1.45	1.45	1.45
820	6.75	6.92	6.83	6.67	0.25	0.65	25.80	24.62	26.03	1.43	1.44	1.44	1.44	1.44
830	6.71	6.88	6.79	6.63	0.24	0.64	25.94	24.81	26.15	1.38	1.43	1.43	1.43	1.43
840	6.67	6.84	6.75	6.60	0.24	0.58	25.95	24.91	26.19	1.34	1.43	1.43	1.42	1.42
850	6.64	6.81	6.72	6.56	0.24	0.56	25.84	24.94	26.09	1.31	1.42	1.42	1.41	1.42
860	6.61	6.78	6.69	6.54	0.24	0.52	25.69	24.89	25.92	1.27	1.41	1.41	1.41	1.41
870	6.59	6.75	6.67	6.52	0.24	0.50	25.46	24.75	25.68	1.25	1.41	1.40	1.40	1.40
880	6.57	6.73	6.65	6.50	0.24	0.49	25.14	24.54	25.37	1.23	1.40	1.40	1.39	1.40
890	6.55	6.71	6.63	6.48	0.24	0.48	24.81	24.29	25.03	1.22	1.40	1.39	1.38	1.39
900	6.54	6.70	6.61	6.47	0.23	0.51	24.47	23.99	24.67	1.22	1.39	1.39	1.38	1.38
910	6.53	6.69	6.60	6.46	0.23	0.50	24.06	23.68	24.28	1.22	1.39	1.38	1.37	1.38
920	6.53	6.68	6.60	6.46	0.23	0.55	23.69	23.36	23.90	1.23	1.38	1.37	1.36	1.37
930	6.52	6.68	6.59	6.45	0.23	0.64	23.32	23.03	23.52	1.25	1.38	1.37	1.36	1.37
940	6.52	6.67	6.59	6.45	0.22	0.67	22.97	22.70	23.16	1.27	1.37	1.37	1.35	1.36
950	6.52	6.67	6.58	6.44	0.23	0.67	22.64	22.41	22.80	1.29	1.37	1.36	1.35	1.36
960	6.52	6.68	6.58	6.45	0.23	0.73	22.32	22.10	22.44	1.31	1.37	1.36	1.35	1.36
970	6.53	6.67	6.59	6.45	0.22	0.74	22.02	21.81	22.12	1.33	1.37	1.35	1.34	1.35
980	6.53	6.68	6.59	6.46	0.22	0.79	21.73	21.54	21.81	1.36	1.36	1.35	1.34	1.35
990	6.54	6.68	6.59	6.46	0.22	0.87	21.45	21.25	21.51	1.38	1.36	1.35	1.34	1.35
1000	6.54	6.69	6.60	6.47	0.22	0.93	21.19	20.99	21.23	1.41	1.36	1.35	1.34	1.34
1025	6.57	6.71	6.62	6.49	0.21	1.02	20.54	20.35	20.56	1.48	1.36	1.34	1.33	1.34
1050	6.59	6.73	6.64	6.52	0.21	1.11	20.00	19.78	19.99	1.55	1.35	1.34	1.33	1.34
1075	6.62	6.75	6.67	6.55	0.21	1.23	19.55	19.30	19.48	1.61	1.35	1.34	1.33	1.34
1100	6.66	6.78	6.69	6.58	0.20	1.32	19.10	18.86	19.02	1.68	1.35	1.33	1.33	1.34
1125	6.69	6.81	6.73	6.62	0.19	1.44	18.70	18.42	18.61	1.75	1.35	1.33	1.33	1.34
1150	6.74	6.85	6.77	6.67	0.19	1.55	18.34	18.01	18.24	1.82	1.36	1.33	1.33	1.34
1175	6.78	6.89	6.81	6.71	0.18	1.62	18.02	17.68	17.92	1.89	1.36	1.34	1.33	1.35
1200	6.81	6.92	6.84	6.75	0.18	1.69	17.73	17.37	17.62	1.95	1.36	1.34	1.33	1.35
1300	6.98	7.07	6.99	6.90	0.17	2.11	16.83	16.31	16.68	2.20	1.39	1.36	1.34	1.37
1400	7.13	7.20	7.11	7.05	0.15	2.51	16.20	15.53	16.01	2.40	1.42	1.38	1.37	1.39
1500	7.27	7.32	7.23	7.19	0.13	2.91	15.71	14.88	15.51	2.58	1.45	1.41	1.40	1.42
1600	7.39	7.42	7.33	7.30	0.12	3.21	15.32	14.33	15.13	2.75	1.48	1.45	1.43	1.45
1700	7.50	7.51	7.42	7.41	0.11	3.56	15.03	13.83	14.83	2.88	1.52	1.49	1.46	1.48
1800	7.61	7.60	7.49	7.50	0.11	3.94	14.78	13.39	14.58	3.01	1.55	1.52	1.49	1.51
1900	7.70	7.67	7.55	7.58	0.14	4.22	14.60	12.98	14.37	3.12	1.58	1.56	1.52	1.54
2000	7.77	7.73	7.59	7.65	0.18	4.57	14.44	12.60	14.21	3.20	1.62	1.59	1.55	1.57
2200	7.93	7.85	7.71	7.82	0.22	5.16	14.13	11.83	13.91	3.41	1.68	1.65	1.61	1.64
2400	8.04	7.92	7.77	7.94	0.27	5.76	13.93	11.15	13.67	3.54	1.72	1.70	1.65	1.69
2500	8.11	7.97	7.83	8.01	0.28	6.07	13.78	10.83	13.54	3.62	1.74	1.72	1.67	1.72

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4C+

100627

Page 2 of 3

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

WP4C+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS ¹				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION			VSWR				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
600	9.69	9.89	9.81	9.62	0.28	1.69	16.24	15.70	16.31	4.03	1.65	1.64	1.63	1.64
625	9.13	9.34	9.25	9.07	0.27	1.62	17.09	16.48	17.16	3.47	1.63	1.62	1.62	1.62
650	8.65	8.85	8.76	8.58	0.27	1.49	18.06	17.38	18.14	3.00	1.61	1.60	1.60	1.60
675	8.23	8.42	8.34	8.16	0.26	1.37	19.14	18.38	19.23	2.61	1.59	1.58	1.58	1.58
700	7.87	8.06	7.98	7.80	0.26	1.27	20.33	19.46	20.47	2.28	1.57	1.56	1.56	1.56
710	7.75	7.94	7.86	7.68	0.25	1.24	20.82	19.92	20.99	2.17	1.56	1.55	1.55	1.55
720	7.64	7.82	7.74	7.57	0.26	1.15	21.33	20.39	21.53	2.07	1.55	1.54	1.54	1.54
730	7.53	7.72	7.63	7.46	0.25	1.17	21.85	20.85	22.08	1.97	1.54	1.53	1.53	1.53
740	7.43	7.62	7.53	7.36	0.25	1.11	22.36	21.33	22.62	1.88	1.53	1.52	1.52	1.52
750	7.34	7.53	7.44	7.27	0.25	1.05	22.89	21.80	23.19	1.80	1.52	1.51	1.51	1.51
760	7.26	7.44	7.36	7.20	0.25	1.00	23.40	22.26	23.74	1.73	1.51	1.50	1.50	1.50
770	7.18	7.37	7.28	7.12	0.25	0.97	23.90	22.72	24.26	1.66	1.50	1.49	1.49	1.49
780	7.12	7.30	7.21	7.05	0.25	0.97	24.36	23.15	24.73	1.59	1.49	1.48	1.48	1.48
790	7.06	7.23	7.15	6.99	0.24	0.95	24.77	23.56	25.16	1.53	1.48	1.47	1.47	1.47
800	7.00	7.17	7.09	6.93	0.24	0.99	25.10	23.92	25.52	1.47	1.47	1.46	1.46	1.46
810	6.95	7.12	7.04	6.88	0.24	0.97	25.35	24.16	25.80	1.43	1.46	1.46	1.46	1.46
820	6.91	7.08	7.00	6.83	0.24	0.98	25.49	24.38	25.96	1.38	1.46	1.45	1.45	1.45
830	6.87	7.04	6.96	6.79	0.24	0.99	25.58	24.52	26.02	1.35	1.45	1.44	1.44	1.44
840	6.83	7.00	6.92	6.76	0.24	1.01	25.57	24.60	25.98	1.31	1.44	1.43	1.43	1.43
850	6.80	6.97	6.89	6.73	0.24	1.04	25.48	24.61	25.85	1.29	1.43	1.42	1.43	1.42
860	6.78	6.94	6.86	6.71	0.23	1.07	25.34	24.55	25.63	1.26	1.43	1.42	1.42	1.42
870	6.75	6.91	6.84	6.69	0.23	1.05	25.13	24.44	25.38	1.24	1.42	1.41	1.41	1.41
880	6.73	6.89	6.81	6.67	0.23	1.09	24.88	24.27	25.08	1.23	1.42	1.40	1.41	1.41
890	6.72	6.87	6.80	6.65	0.23	1.12	24.60	24.04	24.75	1.22	1.41	1.40	1.40	1.40
900	6.70	6.86	6.78	6.64	0.22	1.16	24.27	23.79	24.39	1.23	1.41	1.39	1.39	1.39
910	6.70	6.85	6.77	6.63	0.22	1.22	23.93	23.52	24.04	1.23	1.40	1.39	1.39	1.39
920	6.69	6.84	6.76	6.62	0.22	1.24	23.59	23.24	23.68	1.25	1.40	1.38	1.38	1.38
930	6.68	6.84	6.76	6.62	0.22	1.30	23.25	22.94	23.32	1.26	1.39	1.38	1.38	1.38
940	6.68	6.83	6.75	6.61	0.22	1.38	22.94	22.64	22.97	1.28	1.39	1.38	1.37	1.38
950	6.68	6.83	6.75	6.61	0.22	1.41	22.63	22.37	22.64	1.31	1.39	1.37	1.37	1.37
960	6.68	6.83	6.75	6.61	0.22	1.51	22.33	22.08	22.32	1.33	1.39	1.37	1.37	1.37
970	6.68	6.83	6.75	6.62	0.21	1.53	22.04	21.80	22.01	1.35	1.38	1.37	1.36	1.37
980	6.69	6.83	6.75	6.62	0.21	1.57	21.76	21.53	21.72	1.38	1.38	1.36	1.36	1.37
990	6.69	6.84	6.75	6.62	0.21	1.64	21.49	21.25	21.43	1.40	1.38	1.36	1.36	1.36
1000	6.70	6.83	6.76	6.63	0.20	1.68	21.23	21.00	21.16	1.43	1.38	1.36	1.35	1.36
1025	6.72	6.86	6.77	6.65	0.21	1.81	20.61	20.38	20.54	1.50	1.38	1.35	1.35	1.36
1050	6.75	6.88	6.80	6.68	0.20	1.90	20.06	19.81	19.99	1.57	1.37	1.35	1.34	1.36
1075	6.78	6.91	6.82	6.71	0.20	2.00	19.61	19.32	19.50	1.64	1.37	1.35	1.34	1.36
1100	6.81	6.93	6.85	6.74	0.19	2.12	19.18	18.89	19.07	1.71	1.38	1.35	1.34	1.36
1125	6.85	6.97	6.88	6.78	0.19	2.24	18.78	18.47	18.68	1.78	1.38	1.35	1.34	1.36
1150	6.89	7.00	6.92	6.82	0.18	2.36	18.44	18.08	18.32	1.85	1.38	1.35	1.34	1.36
1175	6.93	7.04	6.96	6.86	0.18	2.44	18.14	17.76	18.01	1.91	1.39	1.36	1.35	1.36
1200	6.96	7.07	6.99	6.89	0.18	2.57	17.87	17.47	17.72	1.97	1.39	1.36	1.35	1.37
1300	7.12	7.21	7.13	7.05	0.16	3.01	16.99	16.44	16.81	2.20	1.42	1.38	1.37	1.39
1400	7.28	7.35	7.26	7.21	0.14	3.41	16.35	15.64	16.16	2.41	1.44	1.41	1.39	1.41
1500	7.42	7.47	7.38	7.34	0.12	3.81	15.86	14.98	15.67	2.59	1.47	1.43	1.41	1.44
1600	7.55	7.57	7.48	7.46	0.11	4.22	15.49	14.42	15.29	2.73	1.51	1.47	1.44	1.47
1700	7.65	7.66	7.56	7.56	0.10	4.62	15.19	13.94	14.99	2.86	1.53	1.50	1.47	1.50
1800	7.75	7.73	7.63	7.66	0.12	5.04	14.95	13.49	14.74	2.96	1.56	1.53	1.49	1.53
1900	7.84	7.81	7.69	7.74	0.15	5.39	14.74	13.07	14.53	3.05	1.59	1.56	1.52	1.56
2000	7.92	7.87	7.74	7.81	0.18	5.76	14.58	12.69	14.36	3.13	1.62	1.59	1.55	1.59
2200	8.07	7.98	7.85	7.97	0.22	6.70	14.28	11.92	14.06	3.29	1.67	1.64	1.60	1.64
2400	8.21	8.08	7.96	8.11	0.25	7.57	14.02	11.23	13.80	3.42	1.71	1.69	1.64	1.68
2500	8.27	8.13	8.00	8.18	0.27	7.98	13.89	10.94	13.67	3.47	1.73	1.71	1.66	1.70

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4C+

100627

Page 3 of 3

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see

